

US-WMTB (29X8) RD CUS - Cable marker



0830012

<https://www.phoenixcontact.com/us/products/0830012>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Cable marker, Card, can be ordered: by card, red (RAL 3001), labeled according to customer specifications, mounting type: Assembly with cable ties, cable diameter: > 13 mm, Number of individual labels: 24, text field height: 8 mm, text field width: 29 mm



Your advantages

- US-WMTB... conductor markers can also be supplied labeled according to customer requirements

Commercial data

Item number	0830012
Packing unit	1 pc
Minimum order quantity	1 pc
Note	Made to order (non-returnable)
Product key	BG8139
GTIN	4046356613514
Weight per piece (including packing)	12.31 g
Weight per piece (excluding packing)	12.31 g
Country of origin	PL

Technical data

Product properties

Product type	Conductor marker
--------------	------------------

Marking

Number of individual labels	24
Number of individual labels per row	6
Identification technology	Thermotransfer

Dimensions

Width	16 mm
Length	29 mm

Text field

Text field width	29 mm
Text field height	8 mm

Material specifications

Color	red (RAL 3001)
Material	PVC
Flammability rating according to UL 94	V0
Base element material	PVC
Components	Silicone-free

Cable/line

External cable diameter	> 13.00 mm
-------------------------	------------

Environmental and real-life conditions

Ambient conditions

Ambient temperature (operation)	-30 °C ... 80 °C
Recommended ambient temperature (storage/transport)	23 °C
Recommended humidity (storage/transport)	50 %

Test for substances that would hinder coating with paint or varnish

Testing for paint wetting impairment substances (LABS-conformity)	VW PV 3.10.7:2005-02
Result	Test passed

UV resistance

Specification	DIN EN ISO 4892-2:2021-11 (following)
Result	Test passed
Test duration	96 h

Wipe resistance of inscriptions

Specification	DIN EN 61010-1 (VDE 0411-01):2020-03
---------------	--------------------------------------

US-WMTB (29X8) RD CUS - Cable marker



0830012

<https://www.phoenixcontact.com/us/products/0830012>

	DIN EN 62208 (VDE 0660-511):2012-06 (in parts)
--	--

Standards and regulations

Wipe resistance	DIN EN 61010-1 (VDE 0411-1)
-----------------	-----------------------------

Mounting

Mounting type	Assembly with cable ties
---------------	--------------------------

US-WMTB (29X8) RD CUS - Cable marker



0830012

<https://www.phoenixcontact.com/us/products/0830012>

Classifications

ECLASS

ECLASS-13.0	27281102
ECLASS-15.0	27281102

ETIM

ETIM 10.0	EC001530
-----------	----------

UNSPSC

UNSPSC 21.0	39131500
-------------	----------

US-WMTB (29X8) RD CUS - Cable marker



0830012

<https://www.phoenixcontact.com/us/products/0830012>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com