

# US-WMTB (29X8) YE CUS - Cable marker



0830014

<https://www.phoenixcontact.com/us/products/0830014>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Cable marker, Card, can be ordered: by card, yellow (RAL 1018), labeled according to customer specifications, mounting type: Assembly with cable ties, cable diameter: > 13 mm, Number of individual labels: 24, text field height: 8 mm, text field width: 29 mm

## Your advantages

- US-WMTB... conductor markers can also be supplied labeled according to customer requirements

## Commercial data

Item number	0830014
Packing unit	1 pc
Minimum order quantity	1 pc
Note	Made to order (non-returnable)
Product key	BG8139
GTIN	4046356613538
Weight per piece (including packing)	12.31 g
Weight per piece (excluding packing)	12.31 g
Country of origin	PL

# US-WMTB (29X8) YE CUS - Cable marker



0830014

<https://www.phoenixcontact.com/us/products/0830014>

## Technical data

### Product properties

Product type	Conductor marker
--------------	------------------

### Marking

Number of individual labels	24
Number of individual labels per row	6
Identification technology	Thermotransfer

### Dimensions

Width	16 mm
Length	29 mm

### Text field

Text field width	29 mm
Text field height	8 mm

### Material specifications

Color	yellow (RAL 1018)
Material	PVC
Flammability rating according to UL 94	V0
Base element material	PVC
Components	Silicone-free

### Cable/line

External cable diameter	> 13.00 mm
-------------------------	------------

### Environmental and real-life conditions

#### Ambient conditions

Ambient temperature (operation)	-30 °C ... 80 °C
Recommended ambient temperature (storage/transport)	23 °C
Recommended humidity (storage/transport)	50 %

#### Test for substances that would hinder coating with paint or varnish

Testing for paint wetting impairment substances (LABS-conformity)	VW PV 3.10.7:2005-02
Result	Test passed

#### UV resistance

Specification	DIN EN ISO 4892-2:2021-11 (following)
Result	Test passed
Test duration	96 h

#### Wipe resistance of inscriptions

Specification	DIN EN 61010-1 (VDE 0411-01):2020-03
---------------	--------------------------------------

# US-WMTB (29X8) YE CUS - Cable marker



0830014

<https://www.phoenixcontact.com/us/products/0830014>

	DIN EN 62208 (VDE 0660-511):2012-06 (in parts)
--	--

## Standards and regulations

Wipe resistance	DIN EN 61010-1 (VDE 0411-1)
-----------------	-----------------------------

## Mounting

Mounting type	Assembly with cable ties
---------------	--------------------------

# US-WMTB (29X8) YE CUS - Cable marker



0830014

<https://www.phoenixcontact.com/us/products/0830014>

## Classifications

### ECLASS

ECLASS-13.0	27281102
ECLASS-15.0	27281102

### ETIM

ETIM 10.0	EC001530
-----------	----------

### UNSPSC

UNSPSC 21.0	39131500
-------------	----------

# US-WMTB (29X8) YE CUS - Cable marker



0830014

<https://www.phoenixcontact.com/us/products/0830014>

## Environmental product compliance

### EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

### EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

### EF3.1 Climate Change

CO2e kg	0.029 kg CO2e
---------	---------------

Phoenix Contact 2026 © - all rights reserved  
<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)