

US-WMTB (44X15) BU CUS - Cable marker



0830023

<https://www.phoenixcontact.com/us/products/0830023>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Cable marker, Card, can be ordered: by card, blue (RAL 5015), labeled according to customer specifications, mounting type: Assembly with cable ties, cable diameter: > 4 mm, Number of individual labels: 12, text field height: 15 mm, text field width: 44 mm



Your advantages

- US-WMTB... conductor markers can also be supplied labeled according to customer requirements

Commercial data

| | |
|--------------------------------------|--------------------------------|
| Item number | 0830023 |
| Packing unit | 1 pc |
| Minimum order quantity | 1 pc |
| Note | Made to order (non-returnable) |
| Product key | BG8139 |
| GTIN | 4046356613620 |
| Weight per piece (including packing) | 12.31 g |
| Weight per piece (excluding packing) | 12.31 g |
| Country of origin | PL |

Technical data

Product properties

| | |
|--------------|------------------|
| Product type | Conductor marker |
|--------------|------------------|

Marking

| | |
|-------------------------------------|----------------|
| Number of individual labels | 12 |
| Number of individual labels per row | 6 |
| Identification technology | Thermotransfer |

Dimensions

| | |
|--------|-------|
| Width | 15 mm |
| Length | 60 mm |

Text field

| | |
|-------------------|-------|
| Text field width | 44 mm |
| Text field height | 15 mm |

Material specifications

| | |
|--|-----------------|
| Color | blue (RAL 5015) |
| Flammability rating according to UL 94 | V0 |
| Base element material | PVC |
| Components | Silicone-free |

Cable/line

| | |
|-------------------------|-----------|
| External cable diameter | > 4.00 mm |
|-------------------------|-----------|

Environmental and real-life conditions

Ambient conditions

| | |
|---|------------------|
| Ambient temperature (operation) | -30 °C ... 80 °C |
| Recommended ambient temperature (storage/transport) | 23 °C |
| Recommended humidity (storage/transport) | 50 % |

Test for substances that would hinder coating with paint or varnish

| | |
|---|----------------------|
| Testing for paint wetting impairment substances (LABS-conformity) | VW PV 3.10.7:2005-02 |
| Result | Test passed |

UV resistance

| | |
|---------------|---------------------------------------|
| Specification | DIN EN ISO 4892-2:2021-11 (following) |
| Result | Test passed |
| Test duration | 96 h |

Wipe resistance of inscriptions

| | |
|---------------|--|
| Specification | DIN EN 61010-1 (VDE 0411-01):2020-03 |
| | DIN EN 62208 (VDE 0660-511):2012-06 (in parts) |

US-WMTB (44X15) BU CUS - Cable marker



0830023

<https://www.phoenixcontact.com/us/products/0830023>

Mounting

Mounting type

Assembly with cable ties

US-WMTB (44X15) BU CUS - Cable marker



0830023

<https://www.phoenixcontact.com/us/products/0830023>

Classifications

ECLASS

| | |
|-------------|----------|
| ECLASS-13.0 | 27281102 |
| ECLASS-15.0 | 27281102 |

ETIM

| | |
|-----------|----------|
| ETIM 10.0 | EC001530 |
|-----------|----------|

UNSPSC

| | |
|-------------|----------|
| UNSPSC 21.0 | 39131500 |
|-------------|----------|

US-WMTB (44X15) BU CUS - Cable marker



0830023

<https://www.phoenixcontact.com/us/products/0830023>

Environmental product compliance

EU RoHS

| | |
|---|--------------------|
| Fulfills EU RoHS substance requirements | Yes, No exemptions |
|---|--------------------|

EU REACH SVHC

| | |
|-------------------------------------|----------------------------|
| REACH candidate substance (CAS No.) | No substance above 0.1 wt% |
|-------------------------------------|----------------------------|

Phoenix Contact 2026 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com