US-EMP (17X15) SR CUS - Snap-in markers

0830027

https://www.phoenixcontact.com/us/products/0830027

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Snap-in markers, Card, can be ordered: by card, labeled according to customer specifications, mounting type: snapped into marker carrier, Number of individual labels: 54, text field height: 15 mm, text field width: 17 mm



The figure shows a version of the product

Your advantages

- All US-EMP ... device markers can also be supplied labeled according to customer requirements

Commercial data

Item number	0830027
Packing unit	1 pc
Minimum order quantity	1 pc
Note	Made to order (non-returnable)
Product key	BG8149
GTIN	4046356613699
Weight per piece (including packing)	14.624 g
Weight per piece (excluding packing)	14.49 g
Country of origin	PL

Technical data

Product properties

Product type	Device marker

Marking

Number of individual labels	54
Number of individual labels per row	6
Identification technology	Thermotransfer

Dimensions

Width	16.90 mm
Height	14.90 mm
Depth	0.50 mm
Length	14.9 mm

Text field

Text field width	17 mm
Text field height	15 mm

Material specifications

Foil strength	500 µm
Color	silver-colored
Material	PVC
	PVC
Flammability rating according to UL 94	V0
Base element material	PVC
Components	Silicone-free

Environmental and real-life conditions

Ambient conditions

Ambient temperature (operation)	-30 °C ... 80 °C
Recommended ambient temperature (storage/transport)	23 °C
Recommended humidity (storage/transport)	50 % (Storage in a dry and dark place in the original packaging is recommended)

Test for substances that would hinder coating with paint or varnish

Testing for paint wetting impairment substances (LABS-conformity)	VW PV 3.10.7:2005-02
Result	Test passed

UV resistance

Specification	DIN EN ISO 4892-2:2021-11 (following)
Result	Test passed
Test duration	96 h

Wipe resistance of inscriptions

Specification	DIN EN 61010-1 (VDE 0411-01):2020-03
	DIN EN 62208 (VDE 0660-511):2012-06 (in parts)

Standards and regulations

Wipe resistance	DIN EN 61010-1 (VDE 0411-1)

Mounting

Mounting type	snapped into marker carrier

Classifications

ECLASS

ECLASS-13.0	27281106
ECLASS-15.0	27281106

ETIM

ETIM 10.0	EC001288

UNSPSC

UNSPSC 21.0	39131700

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%

Phoenix Contact 2026 © - all rights reserved
https://www.phoenixcontact.com

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com