

# US-EMSP (75,6X54) YE CUS - Device marker



0830068

<https://www.phoenixcontact.com/us/products/0830068>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Device marker, Card, can be ordered: by card, yellow (RAL 1018), labeled according to customer specifications, mounting type: screw, rivet, Number of individual labels: 2, text field height: 54 mm, text field width: 75.6 mm



## Your advantages

- The US-EMSP ... UniSheet labeling range includes markers that can be attached using screws or rivets
- The perforated markers and labels are easy to separate and can be easily fitted
- Labeling service: Phoenix Contact can custom-label all UniSheet markers according to your requirements
- The sheets provide space for including function texts

## Commercial data

Item number	0830068
Packing unit	1 pc
Minimum order quantity	1 pc
Note	Made to order (non-returnable)
Product key	BG8149
GTIN	4046356614306
Weight per piece (including packing)	14.534 g
Weight per piece (excluding packing)	14.4 g
Country of origin	PL

## Technical data

### Product properties

Product type	Device marker
--------------	---------------

### Marking

Number of individual labels	2
Number of individual labels per row	1
Identification technology	Thermotransfer, UV-LED-Technologie

### Dimensions

Width	84.95 mm
Height	53.70 mm
Depth	0.50 mm
Length	53.7 mm

### Text field

Text field width	75.6 mm
Text field height	54 mm

### Material specifications

Foil strength	500 µm
Color	yellow (RAL 1018)
Material	PVC
	PVC
Flammability rating according to UL 94	V0
Base element material	PVC
Components	Silicone-free

### Environmental and real-life conditions

#### Ambient conditions

Ambient temperature (operation)	-30 °C ... 80 °C
Recommended ambient temperature (storage/transport)	23 °C
Recommended humidity (storage/transport)	50 % (Storage in a dry and dark place in the original packaging is recommended)

#### Test for substances that would hinder coating with paint or varnish

Testing for paint wetting impairment substances (LABS-conformity)	VW PV 3.10.7:2005-02
Result	Test passed

#### UV resistance

Specification	DIN EN ISO 4892-2:2021-11 (following)
Result	Test passed
Test duration	96 h

# US-EMSP (75,6X54) YE CUS - Device marker



0830068

<https://www.phoenixcontact.com/us/products/0830068>

Procedure	Artificial irradiation.
-----------	-------------------------

## Wipe resistance of inscriptions

Specification	DIN EN 61010-1 (VDE 0411-01):2020-03
	DIN EN 62208 (VDE 0660-511):2012-06 (in parts)

## Standards and regulations

Wipe resistance	DIN EN 61010-1 (VDE 0411-1)
-----------------	-----------------------------

## Mounting

Mounting type	screw, rivet
---------------	--------------

# US-EMSP (75,6X54) YE CUS - Device marker



0830068

<https://www.phoenixcontact.com/us/products/0830068>

## Classifications

### ECLASS

ECLASS-13.0	27281103
ECLASS-15.0	27281103

### ETIM

ETIM 10.0	EC001288
-----------	----------

### UNSPSC

UNSPSC 21.0	39131500
-------------	----------

# US-EMSP (75,6X54) YE CUS - Device marker



0830068

<https://www.phoenixcontact.com/us/products/0830068>

## Environmental product compliance

### EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

### EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

### EF3.1 Climate Change

CO2e kg	0.029 kg CO2e
---------	---------------

Phoenix Contact 2026 © - all rights reserved  
<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)