

# EML-HT (15X15)R CUS - High-temperature label



0830170

<https://www.phoenixcontact.com/us/products/0830170>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



High-temperature label, for thermal transfer printers, round, with 12 mm diameter, resistant for 60 s at up to 300°C, individual month and year identification

## Your advantages

- The EML-HT label is made of an acrylate film that is highly temperature-resistant. It can be used for marking printed circuit boards and in all industrial soldering processes
- Continuous temperature range of -40 °C ... 180 °C, 300 °C for up to 60 seconds
- When combined with the ink ribbon THERMOMARK-RIBBON 110 EML-HT, the marking is highly resistant to high temperatures and chemicals
- The EML-HT ... materials are UL-listed
- Labeling service: Phoenix Contact can custom-label all EML-HT ... markers in accordance with your requirements

## Commercial data

Item number	0830170
Packing unit	1 pc
Minimum order quantity	1 pc
Note	Made to order (non-returnable)
Product key	BG8141
GTIN	4046356628013
Weight per piece (including packing)	1.4 g
Weight per piece (excluding packing)	1.4 g
Country of origin	PL

# EML-HT (15X15)R CUS - High-temperature label



0830170

<https://www.phoenixcontact.com/us/products/0830170>

## Technical data

### Product properties

Product type	Device marker
Product property	Highly resistant to temperature

### Marking

Number of individual labels	4
Number of individual labels per row	4
Identification technology	Thermotransfer

### Dimensions

Width	15.00 mm
Height	15.00 mm
Depth	0.07 mm
Length	15 mm

### Text field

Text field width	15 mm
Text field height	15 mm

### Material specifications

RoHS compliant	yes
Foil strength	50 µm
Adhesive strength	20 µm
Adhesive	Acrylic
Color	white (RAL 9010)
Material	Acrylate
Base element material	Acrylate
Components	free from silicone and halogen

### Environmental and real-life conditions

#### Ambient conditions

Ambient temperature (operation)	-40 °C ... 180 °C
Recommended ambient temperature (storage/transport)	23 °C
Recommended humidity (storage/transport)	50 %

#### Test for substances that would hinder coating with paint or varnish

Testing for paint wetting impairment substances (LABS-conformity)	VDMA 24364-A1-L:2018-05
Result	Test passed

#### Scratch resistance

Specification	EN ISO 1518-1:2023 (following)
---------------	--------------------------------

#### Tesafilm test

# EML-HT (15X15)R CUS - High-temperature label



0830170

<https://www.phoenixcontact.com/us/products/0830170>

Specification	DIN EN ISO 2409:2020-12 (following)
Result	Test passed

## UV resistance

Specification	DIN EN ISO 4892-2:2021-11 (following)
Result	Test passed
Test duration	96 h
Procedure	Artificial irradiation.

## Temperature resistance

Specification	ANSI/UL 969-2018:03 (following)
Test duration	240 h
Rating 125 °C (150 °C)	Test passed

## Wipe resistance of inscriptions

Specification	DIN EN 61010-1 (VDE 0411-1):2011-07 DIN EN 62208 (VDE 0660-511):2012-06 (in parts)
Isopropanol (99%) [67-63-0]	Test passed
n-Hexane [CAS No. 110-54-3]	Test passed
Water + Petroleum ether [CAS No. 64742-82-1]	Test passed
Sodium hydroxide 0.1 mol/l [CAS No. 1310-73-2]	Test passed
Ethanol (99 %) [CAS No. 64-17-5]	Test passed

## Immersion in chemicals, oil & fuel

Specification	ISO 175:2010 (following)
Test duration	168 h
Saltwater (saturated 350 g/l) [CAS No. - ]	Test passed
IRM 901	Test passed
IRM 902	Test passed
IRM 903	Test passed

## Testing in a condensation changing climate in the presence of sulfur dioxide

Specification	DIN EN ISO 22479:2022-08
Result	Test passed
Procedure	Method B
Cycles	2

## Salt spray test

Specification	DIN EN IEC 60068-2-11 (VDE 0468-2-11):2022-10
Result	Test passed
Test duration	96 h

## Standards and regulations

# EML-HT (15X15)R CUS - High-temperature label



0830170

<https://www.phoenixcontact.com/us/products/0830170>

Wipe resistance	DIN EN 61010-1 (VDE 0411-1)
-----------------	-----------------------------

## Mounting

Mounting type	adhesive
---------------	----------

# EML-HT (15X15)R CUS - High-temperature label



0830170

<https://www.phoenixcontact.com/us/products/0830170>

## Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/0830170>



**UL Recognized**

Approval ID: MH48542

# EML-HT (15X15)R CUS - High-temperature label



0830170

<https://www.phoenixcontact.com/us/products/0830170>

## Classifications

### ECLASS

ECLASS-13.0	27281103
ECLASS-15.0	27281103

### ETIM

ETIM 10.0	EC001288
-----------	----------

### UNSPSC

UNSPSC 21.0	39131500
-------------	----------

# EML-HT (15X15)R CUS - High-temperature label



0830170

<https://www.phoenixcontact.com/us/products/0830170>

## Environmental product compliance

### EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

### EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)