

# US-EMP (52,5X15) RD - Snap-in markers



0830312

<https://www.phoenixcontact.com/us/products/0830312>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Snap-in markers, Card, red (RAL 3001), unmarked, can be labeled with: BLUEMARK ID COLOR, BLUEMARK ID, THERMOMARK PRIME, THERMOMARK CARD 2.0, THERMOMARK CARD, THERMOMARK PRIME 2.0, mounting type: latching, Number of individual labels: 16, text field height: 15 mm, text field width: 52.5 mm



## Your advantages

- The markers, which are supplied in uniform sheets, can be labeled quickly, easily, and cost-effectively using the THERMOMARK CARD
- The perforated markers and labels are easy to separate and can be easily fitted
- The sheets provide space for including function texts
- The US-EMP ... UniSheet labeling range includes markers that can be fitted into existing CARRIER EMP ... label frames

## Commercial data

Item number	0830312
Packing unit	10 pc
Minimum order quantity	10 pc
Sales key	BG09
Product key	BG2419
GTIN	4046356715737
Weight per piece (including packing)	15.21 g
Weight per piece (excluding packing)	15.21 g
Customs tariff number	39269097
Country of origin	DE

# US-EMP (52,5X15) RD - Snap-in markers



0830312

<https://www.phoenixcontact.com/us/products/0830312>

## Technical data

### Product properties

Product type	Device marker
--------------	---------------

### Marking

Number of individual labels	16
Number of individual labels per row	2
Identification technology	Thermotransfer

### Dimensions

Width	52.00 mm
Height	14.90 mm
Depth	0.50 mm
Length	15 mm

### Text field

Text field width	52.5 mm
Text field height	15 mm

### Material specifications

RoHS compliant	yes
Foil strength	500 µm
Color	red (RAL 3001)
Material	PVC PVC
Flammability rating according to UL 94	V0
Components	Silicone-free

### Environmental and real-life conditions

#### Ambient conditions

Ambient temperature (operation)	-30 °C ... 80 °C
Recommended ambient temperature (storage/transport)	10 °C
Recommended humidity (storage/transport)	35 % ... 65 %

#### Test for substances that would hinder coating with paint or varnish

Testing for paint wetting impairment substances (LABS-conformity)	VW PV 3.10.7:2005-02
Result	Test passed

#### UV resistance

Specification	ISO 4892-2:2013-03 (following)
Result	Test passed
Test duration	96 h

#### Wipe resistance of inscriptions

# US-EMP (52,5X15) RD - Snap-in markers



0830312

<https://www.phoenixcontact.com/us/products/0830312>

Specification	IEC 61010-1:2010-06
	DIN EN 62208 (VDE 0660-511):2012-06 (in parts)
Isopropanol (99%) [67-63-0]	Test passed
n-Hexane [CAS No. 110-54-3]	Test passed
Water + Petroleum ether [CAS No. 64742-82-1]	Test passed

## Testing in a condensation changing climate in the presence of sulfur dioxide

Specification	DIN 50018:2013-05 (following)
Result	Test passed
Climate level	AHT 1.0 S
Cycles	2

## Salt spray test

Specification	DIN EN 60068-2-11:2000-02
Result	Test passed

## Standards and regulations

Wipe resistance	DIN EN 61010-1 (VDE 0411-1)
-----------------	-----------------------------

## Mounting

Mounting type	latching
---------------	----------

# US-EMP (52,5X15) RD - Snap-in markers



0830312

<https://www.phoenixcontact.com/us/products/0830312>

## Classifications

### ECLASS

ECLASS-13.0

27281106

### ETIM

ETIM 9.0

EC001530

### UNSPSC

UNSPSC 21.0

39131700

# US-EMP (52,5X15) RD - Snap-in markers



0830312

<https://www.phoenixcontact.com/us/products/0830312>

## Environmental product compliance

### EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

### EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)