

# US-EMLP (70X15) YE CUS - Plastic label



0830384

<https://www.phoenixcontact.com/us/products/0830384>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Plastic label, Card, can be ordered: by card, yellow (RAL 1018), labeled according to customer specifications, mounting type: adhesive, Number of individual labels: 8, text field height: 15 mm, text field width: 70 mm



## Your advantages

- PVC material flammability rating V0 in accordance with UL 94

## Commercial data

Item number	0830384
Packing unit	1 pc
Minimum order quantity	1 pc
Note	Made to order (non-returnable)
Product key	BG8149
GTIN	4046356715454
Weight per piece (including packing)	18.18 g
Weight per piece (excluding packing)	18.18 g
Country of origin	PL

## Technical data

### Product properties

Product type	Device marker
--------------	---------------

### Marking

Number of individual labels	8
Number of individual labels per row	1
Identification technology	Thermotransfer

### Dimensions

Width	70.00 mm
Height	14.90 mm
Depth	0.55 mm
Length	15 mm

### Text field

Text field width	70 mm
Text field height	15 mm

### Material specifications

Foil strength	500 µm
Adhesive strength	50 µm
Adhesive	Acrylic
Color	yellow (RAL 1018)
Material	PVC
Flammability rating according to UL 94	V0
Base element material	PVC
Components	Silicone-free

### Environmental and real-life conditions

#### Ambient conditions

Ambient temperature (operation)	-30 °C ... 80 °C
Recommended ambient temperature (storage/transport)	23 °C
Recommended humidity (storage/transport)	50 %

#### Test for substances that would hinder coating with paint or varnish

Testing for paint wetting impairment substances (LABS-conformity)	VW PV 3.10.7:2005-02
Result	Test passed

#### UV resistance

Specification	DIN EN ISO 4892-2:2021-11 (following)
Result	Test passed
Test duration	96 h

# US-EMLP (70X15) YE CUS - Plastic label



0830384

<https://www.phoenixcontact.com/us/products/0830384>

Procedure	Artificial irradiation.
-----------	-------------------------

## Wipe resistance of inscriptions

Specification	DIN EN 61010-1 (VDE 0411-01):2020-03
	DIN EN 62208 (VDE 0660-511):2012-06 (in parts)

## Standards and regulations

Wipe resistance	DIN EN 61010-1 (VDE 0411-1)
-----------------	-----------------------------

## Mounting

Mounting type	adhesive
---------------	----------

# US-EMLP (70X15) YE CUS - Plastic label



0830384

<https://www.phoenixcontact.com/us/products/0830384>

## Classifications

### ECLASS

ECLASS-13.0	27281103
ECLASS-15.0	27281103

### ETIM

ETIM 10.0	EC001288
-----------	----------

### UNSPSC

UNSPSC 21.0	39131500
-------------	----------

# US-EMLP (70X15) YE CUS - Plastic label



0830384

<https://www.phoenixcontact.com/us/products/0830384>

## Environmental product compliance

### EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

### EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)