

WM-CARRIER/B (48X10)LPR - Cable marker carrier



0830423

<https://www.phoenixcontact.com/us/products/0830423>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Cable marker carrier, unmarked, mounting type: Assembly with cable ties, cable diameter: ≥ 6 mm, text field height: 10 mm, text field width: 48 mm



Commercial data

Item number	0830423
Packing unit	100 pc
Minimum order quantity	100 pc
Sales key	BG12
Product key	BG231A
GTIN	4046356716130
Weight per piece (including packing)	0.683 g
Weight per piece (excluding packing)	0.676 g
Customs tariff number	39204910
Country of origin	DK

Technical data

Product properties

Product type	Marker carriers
--------------	-----------------

Dimensions

Width	70 mm
Height	14 mm
Depth	0.36 mm

Text field

Text field width	48 mm
Text field height	10 mm

Material specifications

RoHS compliant	yes
Adhesive	Acrylic
Color	transparent
Material	Polyester
Base element material	Polyester
Components	halogen-free

Cable/line

External cable diameter	≥ 6.00 mm
-------------------------	-----------

Environmental and real-life conditions

Ambient conditions

Ambient temperature (operation)	-10 °C ... 60 °C
Recommended ambient temperature (storage/transport)	23 °C
Recommended humidity (storage/transport)	50 %

Test for substances that would hinder coating with paint or varnish

Testing for paint wetting impairment substances (LABS-conformity)	VW PV 3.10.7:2005-02
Result	Test passed

UV resistance

Specification	DIN EN ISO 4892-2:2021-11 (following)
Result	Test passed
Test duration	96 h

Testing in a condensation changing climate in the presence of sulfur dioxide

Specification	DIN EN ISO 22479:2022-08
Result	Test passed
Procedure	Method B

WM-CARRIER/B (48X10)LPR - Cable marker carrier



0830423

<https://www.phoenixcontact.com/us/products/0830423>

Cycles	2
--------	---

Salt spray test

Specification	DIN EN IEC 60068-2-11 (VDE 0468-2-11):2022-10
Result	Test passed

Standards and regulations

Wipe resistance	DIN EN 61010-1 (VDE 0411-1)
-----------------	-----------------------------

Mounting

Mounting type	Assembly with cable ties
---------------	--------------------------

WM-CARRIER/B (48X10)LPR - Cable marker carrier



0830423

<https://www.phoenixcontact.com/us/products/0830423>

Classifications

ECLASS

ECLASS-13.0	27281105
ECLASS-15.0	27281105

ETIM

ETIM 10.0	EC002248
-----------	----------

UNSPSC

UNSPSC 21.0	39121400
-------------	----------

WM-CARRIER/B (48X10)LPR - Cable marker carrier



0830423

<https://www.phoenixcontact.com/us/products/0830423>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com