

# US-EMLSP (28X10) SR - Markers for sticking on, screwing or riveting



0830329

<https://www.phoenixcontact.com/us/products/0830329>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Markers for sticking on, screwing or riveting, Card, unmarked, can be labeled with: BLUEMARK ID COLOR, BLUEMARK ID, THERMOMARK PRIME, THERMOMARK CARD 2.0, THERMOMARK CARD, THERMOMARK PRIME 2.0, mounting type: adhere, screw, rivet, adhesive, Number of individual labels: 26, text field height: 10 mm, text field width: 28 mm



## Your advantages

- The stick-on UniSheet markers can also be attached with screws or rivets
- The markers, which are supplied in uniform sheets, can be labeled quickly, easily, and cost-effectively using the THERMOMARK CARD
- The perforated markers and labels are easy to separate and can be easily fitted

## Commercial data

Item number	0830329
Packing unit	10 pc
Minimum order quantity	10 pc
Sales key	BG09
Product key	BG2419
GTIN	4046356708197
Weight per piece (including packing)	17.97 g
Weight per piece (excluding packing)	17.27 g
Customs tariff number	39199080
Country of origin	DE

# US-EMLSP (28X10) SR - Markers for sticking on, screwing or riveting



0830329

<https://www.phoenixcontact.com/us/products/0830329>

## Technical data

### Product properties

Product type	Device marker
--------------	---------------

### Marking

Number of individual labels	26
Number of individual labels per row	2
Identification technology	Thermotransfer, UV-LED-Technologie

### Dimensions

Width	40.00 mm
Height	9.50 mm
Depth	0.73 mm

### Text field

Text field width	28 mm
Text field height	10 mm

### Material specifications

RoHS compliant	yes
Foil strength	500 µm
Adhesive strength	250 µm
Adhesive	Acrylic
Color	silver-colored
Material	PVC
Flammability rating according to UL 94	V0
Base element material	PVC
Components	Silicone-free

### Environmental and real-life conditions

#### Ambient conditions

Ambient temperature (operation)	-30 °C ... 80 °C
Recommended ambient temperature (storage/transport)	20 °C
Recommended humidity (storage/transport)	50 %

#### Test for substances that would hinder coating with paint or varnish

Testing for paint wetting impairment substances (LABS-conformity)	VW PV 3.10.7:2005-02
Result	Test passed

#### UV resistance

Specification	DIN EN ISO 4892-2:2021-11 (following)
Result	Test passed

# US-EMLSP (28X10) SR - Markers for sticking on, screwing or riveting



0830329

<https://www.phoenixcontact.com/us/products/0830329>

Test duration	96 h
---------------	------

## Wipe resistance of inscriptions

Specification	DIN EN 61010-1 (VDE 0411-1):2011-07 DIN EN 62208 (VDE 0660-511):2012-06 (in parts)
Isopropanol (99%) [67-63-0]	Test passed
n-Hexane [CAS No. 110-54-3]	Test passed
Water + Petroleum ether [CAS No. 64742-82-1]	Test passed

## Testing in a condensation changing climate in the presence of sulfur dioxide

Specification	DIN EN ISO 22479:2022-08
Result	Test passed
Procedure	Method B
Cycles	2

## Salt spray test

Specification	DIN EN IEC 60068-2-11 (VDE 0468-2-11):2022-10
Result	Test passed
Test duration	96 h

## Standards and regulations

Wipe resistance	DIN EN 61010-1 (VDE 0411-1)
-----------------	-----------------------------

## Mounting

Mounting type	adhere, screw, rivet
---------------	----------------------

# US-EMLSP (28X10) SR - Markers for sticking on, screwing or riveting



0830329

<https://www.phoenixcontact.com/us/products/0830329>

## Classifications

### ECLASS

ECLASS-13.0	27281103
ECLASS-15.0	27281103

### ETIM

ETIM 10.0	EC001288
-----------	----------

### UNSPSC

UNSPSC 21.0	39131500
-------------	----------

# US-EMLSP (28X10) SR - Markers for sticking on, screwing or riveting



0830329

<https://www.phoenixcontact.com/us/products/0830329>

## Environmental product compliance

### EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

### EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved  
<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)