

US-EMP (52,5X15) YE CUS - Snap-in markers



0830358

<https://www.phoenixcontact.com/us/products/0830358>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Snap-in markers, can be ordered: by card, yellow (RAL 1018), labeled according to customer specifications, mounting type: snapped into marker carrier, Number of individual labels: 16, text field height: 15 mm, text field width: 52.5 mm



Your advantages

- All US-EMP ... device markers can also be supplied labeled according to customer requirements

Commercial data

Item number	0830358
Packing unit	1 pc
Minimum order quantity	1 pc
Note	Made to order (non-returnable)
Product key	BG8149
GTIN	4046356715928
Weight per piece (including packing)	14.86 g
Weight per piece (excluding packing)	14.86 g
Country of origin	PL

US-EMP (52,5X15) YE CUS - Snap-in markers



0830358

<https://www.phoenixcontact.com/us/products/0830358>

Technical data

Product properties

Product type	Device marker
--------------	---------------

Marking

Number of individual labels	16
Number of individual labels per row	2
Identification technology	Thermotransfer

Dimensions

Width	52.00 mm
Height	14.90 mm
Depth	0.50 mm
Length	15 mm

Text field

Text field width	52.5 mm
Text field height	15 mm

Material specifications

Foil strength	500 µm
Color	yellow (RAL 1018)
Material	PVC
Flammability rating according to UL 94	V0
Base element material	PVC
Components	Silicone-free

Environmental and real-life conditions

Ambient conditions

Ambient temperature (operation)	-30 °C ... 80 °C
Recommended ambient temperature (storage/transport)	23 °C
Recommended humidity (storage/transport)	50 % (Storage in a dry and dark place in the original packaging is recommended)

Test for substances that would hinder coating with paint or varnish

Testing for paint wetting impairment substances (LABS-conformity)	VW PV 3.10.7:2005-02
Result	Test passed

UV resistance

Specification	DIN EN ISO 4892-2:2021-11 (following)
Result	Test passed
Test duration	96 h

Wipe resistance of inscriptions

US-EMP (52,5X15) YE CUS - Snap-in markers



0830358

<https://www.phoenixcontact.com/us/products/0830358>

Specification	DIN EN 61010-1 (VDE 0411-01):2020-03
	DIN EN 62208 (VDE 0660-511):2012-06 (in parts)

Standards and regulations

Wipe resistance	DIN EN 61010-1 (VDE 0411-1)
-----------------	-----------------------------

Mounting

Mounting type	snapped into marker carrier
---------------	-----------------------------

US-EMP (52,5X15) YE CUS - Snap-in markers



0830358

<https://www.phoenixcontact.com/us/products/0830358>

Classifications

ECLASS

ECLASS-13.0	27281106
ECLASS-15.0	27281106

ETIM

ETIM 10.0	EC001288
-----------	----------

UNSPSC

UNSPSC 21.0	39131700
-------------	----------

US-EMP (52,5X15) YE CUS - Snap-in markers



0830358

<https://www.phoenixcontact.com/us/products/0830358>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

EF3.1 Climate Change

CO2e kg	0.029 kg CO2e
---------	---------------

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com