

US-EMLSP (28X10) CUS - Markers for sticking on, screwing or riveting



0830368

<https://www.phoenixcontact.com/us/products/0830368>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Markers for sticking on, screwing or riveting, Card, can be ordered: by card, white (RAL 9010), labeled according to customer specifications, mounting type: adhere, screw, rivet, adhesive, Number of individual labels: 26, text field height: 10 mm, text field width: 28 mm



Your advantages

- The stick-on UniSheet markers can also be attached with screws or rivets
- The perforated markers and labels are easy to separate and can be easily fitted

Commercial data

Item number	0830368
Packing unit	1 pc
Minimum order quantity	1 pc
Note	Made to order (non-returnable)
Product key	BG8149
GTIN	4046356723527
Weight per piece (including packing)	18.44 g
Weight per piece (excluding packing)	18.44 g
Country of origin	PL

US-EMLSP (28X10) CUS - Markers for sticking on, screwing or riveting



0830368

<https://www.phoenixcontact.com/us/products/0830368>

Technical data

Product properties

Product type	Device marker
--------------	---------------

Marking

Number of individual labels	26
Number of individual labels per row	2
Identification technology	Thermotransfer

Dimensions

Width	40.00 mm
Height	9.50 mm
Depth	0.73 mm
Length	28 mm

Text field

Text field width	28 mm
Text field height	10 mm

Material specifications

Foil strength	500 µm
Adhesive strength	250 µm
Adhesive	Acrylic
Color	white (RAL 9010)
Material	PVC
Flammability rating according to UL 94	V0
Base element material	PVC
Components	Silicone-free

Environmental and real-life conditions

Ambient conditions

Ambient temperature (operation)	-30 °C ... 80 °C
Recommended ambient temperature (storage/transport)	20 °C
Recommended humidity (storage/transport)	50 % (Storage in a dry and dark place in the original packaging is recommended)

Test for substances that would hinder coating with paint or varnish

Testing for paint wetting impairment substances (LABS-conformity)	VW PV 3.10.7:2005-02
Result	Test passed

UV resistance

Specification	DIN EN ISO 4892-2:2021-11 (following)
---------------	---------------------------------------

US-EMLSP (28X10) CUS - Markers for sticking on, screwing or riveting



0830368

<https://www.phoenixcontact.com/us/products/0830368>

Result	Test passed
Test duration	96 h
Procedure	Artificial irradiation.

Wipe resistance of inscriptions

Specification	DIN EN 61010-1 (VDE 0411-01):2020-03
	DIN EN 62208 (VDE 0660-511):2012-06 (in parts)

Standards and regulations

Wipe resistance	DIN EN 61010-1 (VDE 0411-1)
-----------------	-----------------------------

Mounting

Mounting type	adhere, screw, rivet
---------------	----------------------

US-EMLSP (28X10) CUS - Markers for sticking on, screwing or riveting



0830368

<https://www.phoenixcontact.com/us/products/0830368>

Classifications

ECLASS

ECLASS-13.0	27281103
ECLASS-15.0	27281103

ETIM

ETIM 10.0	EC001288
-----------	----------

UNSPSC

UNSPSC 21.0	39131500
-------------	----------

US-EMLSP (28X10) CUS - Markers for sticking on, screwing or riveting



0830368

<https://www.phoenixcontact.com/us/products/0830368>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
-----------------------------------------	--------------------

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com