

PML-W202 (25X25) - Warning label



0830437

<https://www.phoenixcontact.com/us/products/0830437>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Warning label, Sheet, labeled: Lightning flash and print: 230 V, mounting type: adhesive, diameter: 0 mm, Number of individual labels: 16, text field height: 25 mm, text field width: 25 mm



Commercial data

Item number	0830437
Packing unit	5 pc
Minimum order quantity	5 pc
Sales key	BG21
Product key	BG2614
GTIN	4046356717618
Weight per piece (including packing)	5.906 g
Weight per piece (excluding packing)	3.9 g
Customs tariff number	39199080
Country of origin	DE

PML-W202 (25X25) - Warning label



0830437

<https://www.phoenixcontact.com/us/products/0830437>

Technical data

Product properties

Product type	Plant marker
Area of application	Warning labels
	Warning identification according to ISO 7010
Type	Triangle

Marking

Number of individual labels	16
Number of individual labels per row	4
Printing	Lightning flash and print: 230 V
Identification technology	Office laser printing

Dimensions

Width	25 mm
Height	29.6 mm

Text field

Text field width	25 mm
Text field height	25 mm

Material specifications

Foil strength	60 µm
Adhesive strength	25 µm
Adhesive	Acrylic
Color	yellow/black
Base element material	PVC
Components	Silicone-free

Environmental and real-life conditions

Ambient conditions

Ambient temperature (operation)	-40 °C ... 60 °C
Recommended ambient temperature (storage/transport)	22 °C
Recommended humidity (storage/transport)	50 % ... 55 % (Storage in a dry and dark place in the original packaging is recommended)

Test for substances that would hinder coating with paint or varnish

Testing for paint wetting impairment substances (LABS-conformity)	VW PV 3.10.7:2005-02
Result	Test passed

Test for substances that would hinder coating with paint or varnish

Testing for paint wetting impairment substances (LABS-conformity)	VDMA 24364:2018-05
Result	Test passed

PML-W202 (25X25) - Warning label



0830437

<https://www.phoenixcontact.com/us/products/0830437>

Scratch resistance

Specification	DIN EN ISO 1518-1:2019-10 (following)
Requirements	≥ 5 N
Result	Test passed

Tesafilm test

Specification	DIN EN ISO 2409:2013 (following)
Result	Test passed

UV resistance

Specification	DIN EN ISO 4892-2:2021-11 (following)
Result	Test passed
Test duration	96 h
Procedure	Artificial irradiation.

Wipe resistance of inscriptions

Specification	DIN EN 61010-1 (VDE 0411-01):2020-03 DIN EN 62208 (VDE 0660-511):2012-06 (in parts)
Isopropanol (99%) [67-63-0]	Test passed
n-Hexane [CAS No. 110-54-3]	Test passed
Water + Petroleum ether [CAS No. 64742-82-1]	Test passed
Sodium hydroxide 0.1 mol/l [CAS No. 1310-73-2]	Test passed
Ethanol (99 %) [CAS No. 64-17-5]	Test passed

Immersion in chemicals, oil & fuel

Specification	ISO 175:2010 (following)
Test duration	168 h
Saltwater (saturated 350 g/l) [CAS No. -]	Test passed
Diesel [CAS No. 68476-34-6]	Test passed
IRM 901	Test passed
IRM 902	Test passed
IRM 903	Test passed

Testing in a condensation changing climate in the presence of sulfur dioxide

Specification	DIN 50018:2013-05
Result	Test passed
Climate level	AHT 1.0 S
Cycles	2

Salt spray test

Specification	DIN EN 60068-2-11:2000-02
Result	Test passed

PML-W202 (25X25) - Warning label



0830437

<https://www.phoenixcontact.com/us/products/0830437>

Test duration	96 h
---------------	------

Mounting

Mounting type	adhesive
---------------	----------

PML-W202 (25X25) - Warning label



0830437

<https://www.phoenixcontact.com/us/products/0830437>

Classifications

ECLASS

ECLASS-13.0

40200203

ETIM

ETIM 9.0

EC001777

UNSPSC

UNSPSC 21.0

55121700

PML-W202 (25X25) - Warning label



0830437

<https://www.phoenixcontact.com/us/products/0830437>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com