

PML-W301 (105X52) - Warning label



0830463

<https://www.phoenixcontact.com/us/products/0830463>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Warning label, Sheet, Mixed color, labeled: Lightning flash and warning in German, English, mounting type: adhesive, Number of individual labels: 4, text field height: 52 mm, text field width: 105 mm



Commercial data

| | |
|--------------------------------------|---------------|
| Item number | 0830463 |
| Packing unit | 5 pc |
| Minimum order quantity | 5 pc |
| Sales key | BG21 |
| Product key | BG2614 |
| GTIN | 4046356717878 |
| Weight per piece (including packing) | 18.7 g |
| Weight per piece (excluding packing) | 18.43 g |
| Customs tariff number | 39199080 |
| Country of origin | DE |

PML-W301 (105X52) - Warning label



0830463

<https://www.phoenixcontact.com/us/products/0830463>

Technical data

Product properties

| | |
|---------------------|--|
| Product type | Plant marker |
| Area of application | Warning identification according to ISO 7010 |
| Type | Rectangle |

Marking

| | |
|-------------------------------------|--|
| Number of individual labels | 4 |
| Number of individual labels per row | 1 |
| Printing | Lightning flash and warning in German, English |
| Identification technology | Office laser printing |

Dimensions

| | |
|--------|-----------|
| Width | 105.00 mm |
| Height | 52.50 mm |
| Depth | 0.08 mm |

Text field

| | |
|-------------------|--------|
| Text field width | 105 mm |
| Text field height | 52 mm |

Material specifications

| | |
|-----------------------|----------------------|
| Foil strength | 60 µm |
| Adhesive strength | 25 µm |
| Adhesive | Acrylic |
| Color | multicolored (RAL -) |
| | yellow (RAL 1018) |
| | black (RAL 9005) |
| Base element material | PVC |
| Components | Silicone-free |

Environmental and real-life conditions

Ambient conditions

| | |
|---|--|
| Ambient temperature (operation) | -40 °C ... 40 °C |
| Recommended ambient temperature (storage/transport) | 22 °C |
| Recommended humidity (storage/transport) | 50 % ... 55 % (Storage in a dry and dark place in the original packaging is recommended) |

Test for substances that would hinder coating with paint or varnish

| | |
|---|-------------------------|
| Testing for paint wetting impairment substances (LABS-conformity) | VDMA 24364-A1-L:2018-05 |
| Result | Test passed |

Test for substances that would hinder coating with paint or varnish

PML-W301 (105X52) - Warning label



0830463

<https://www.phoenixcontact.com/us/products/0830463>

| | |
|---|----------------------|
| Testing for paint wetting impairment substances (LABS-conformity) | VW PV 3.10.7:2005-02 |
| Result | Test passed |

Scratch resistance

| | |
|---------------|--------------------------------|
| Specification | EN ISO 1518-1:2023 (following) |
| Requirements | ≥ 5 N |
| Result | Test passed |

Tesafilm test

| | |
|---------------|-------------------------------------|
| Specification | DIN EN ISO 2409:2020-12 (following) |
| Result | Test passed |

UV resistance

| | |
|---------------|---------------------------------------|
| Specification | DIN EN ISO 4892-2:2021-11 (following) |
| Result | Test passed |
| Test duration | 96 h |
| Procedure | Artificial irradiation. |

Temperature resistance

| | |
|---------------|---------------------------------|
| Specification | ANSI/UL 969-2018:03 (following) |
| Test duration | 240 h |

Wipe resistance of inscriptions

| | |
|---|--|
| Specification | DIN EN 61010-1 (VDE 0411-01):2020-03 DIN EN 62208 (VDE 0660-511):2012-06 (in parts) |
| Isopropanol (99%) [67-63-0] | Test passed |
| n-Hexane [CAS No. 110-54-3] | Test passed |
| Water + Petroleum ether [CAS No. 64742-82-1] | Test passed |
| Sodium hydroxide 0.1 mol/l [CAS No. 1310-73-2] | Test passed |
| Ethanol (99 %) [CAS No. 64-17-5] | Test passed |

Immersion in chemicals, oil & fuel

| | |
|---|--------------------------|
| Specification | ISO 175:2010 (following) |
| Test duration | 168 h |
| Saltwater (saturated 350 g/l) [CAS No. -] | Test passed |
| Diesel [CAS No. 68476-34-6] | Test passed |
| IRM 901 | Test passed |
| IRM 902 | Test passed |
| IRM 903 | Test passed |

Testing in a condensation changing climate in the presence of sulfur dioxide

| | |
|---------------|----------------------|
| Specification | EN ISO 22479:2022-06 |
|---------------|----------------------|

PML-W301 (105X52) - Warning label



0830463

<https://www.phoenixcontact.com/us/products/0830463>

| | |
|-----------|-------------|
| Result | Test passed |
| Procedure | Method B |
| Cycles | 2 |

Salt spray test

| | |
|---------------|---|
| Specification | DIN EN IEC 60068-2-11 (VDE 0468-2-11):2022-10 |
| Result | Test passed |
| Test duration | 96 h |

Standards and regulations

| | |
|-----------------|-----------------------------|
| Wipe resistance | DIN EN 61010-1 (VDE 0411-1) |
|-----------------|-----------------------------|

Mounting

| | |
|---------------|----------|
| Mounting type | adhesive |
|---------------|----------|

PML-W301 (105X52) - Warning label



0830463

<https://www.phoenixcontact.com/us/products/0830463>

Classifications

ECLASS

| | |
|-------------|----------|
| ECLASS-13.0 | 40200203 |
| ECLASS-15.0 | 40200203 |

ETIM

| | |
|-----------|----------|
| ETIM 10.0 | EC001777 |
|-----------|----------|

UNSPSC

| | |
|-------------|----------|
| UNSPSC 21.0 | 55121700 |
|-------------|----------|

PML-W301 (105X52) - Warning label



0830463

<https://www.phoenixcontact.com/us/products/0830463>

Environmental product compliance

EU RoHS

| | |
|---|--------------------|
| Fulfills EU RoHS substance requirements | Yes, No exemptions |
|---|--------------------|

EU REACH SVHC

| | |
|-------------------------------------|----------------------------|
| REACH candidate substance (CAS No.) | No substance above 0.1 wt% |
|-------------------------------------|----------------------------|

Phoenix Contact 2026 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com