

EMSP-AL (90X60) - Equipment marking



0830504

<https://www.phoenixcontact.com/us/products/0830504>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Equipment marking, Aluminum label, unmarked, can be labeled with: BLUEMARK E.CARD, BLUEMARK ID COLOR, BLUEMARK ID, BLUEMARK CLED, mounting type: screw, rivet, Number of individual labels: 1, text field height: 60 mm, text field width: 90 mm



Product description

Note:
Due to the current challenges of the global procurement market, Phoenix Contact has unfortunately been forced to accept an aluminum alloy material quality that may cause the appearance to deviate from the homogenous surface quality that was previously expected. This has no impact on the quality of the aluminum labels themselves or the durability of the printing. The effect is purely visual.

Your advantages

- The markers can be marked quickly, easily, and cost-effectively with the BLUEMARK printing systems
- Aluminum equipment marking for screwing or riveting
- Identification made from metal, high strength in a lightweight design
- Increased durability due to the decoratively anodized surface

Commercial data

Item number	0830504
Packing unit	15 pc
Minimum order quantity	15 pc
Sales key	BG18
Product key	BG241B
GTIN	4046356719025
Weight per piece (including packing)	13.4 g
Weight per piece (excluding packing)	12.176 g
Customs tariff number	76169990
Country of origin	DE

EMSP-AL (90X60) - Equipment marking



0830504

<https://www.phoenixcontact.com/us/products/0830504>

Technical data

Product properties

Product type	Device marker
--------------	---------------

Marking

Number of individual labels	1
Number of individual labels per row	1
Number of bore holes	4
Identification technology	UV LED technology

Dimensions

Width	100.00 mm
Height	60.00 mm
Depth	0.80 mm

Text field

Text field width	90 mm
Text field height	60 mm

Material specifications

Color	aluminum color
Base element material	Aluminum
Components	free from silicone, halogen, and cadmium

Environmental and real-life conditions

Ambient conditions

Ambient temperature (operation)	-25 °C ... 120 °C (> +80 °C slight changes of the material surface possible)
Recommended ambient temperature (storage/transport)	5 °C
Recommended humidity (storage/transport)	50 % (Storage in a dry and dark place in the original packaging is recommended)

Test for substances that would hinder coating with paint or varnish

Testing for paint wetting impairment substances (LABS-conformity)	VDMA 24364:2018-05
Result	Test passed

Test for substances that would hinder coating with paint or varnish

Testing for paint wetting impairment substances (LABS-conformity)	VW PV 3.10.7:2005-02
Result	Test passed

Scratch resistance

Specification	EN ISO 1518-1:2023 (following)
Requirements	≥ 5 N
Result	Test passed

EMSP-AL (90X60) - Equipment marking



0830504

<https://www.phoenixcontact.com/us/products/0830504>

Tesafilm test

Specification	DIN EN ISO 2409:2020-12 (following)
Result	Test passed

UV resistance

Specification	DIN EN ISO 4892-2:2021-11 (following)
Result	Test passed
Test duration	96 h
Procedure	Artificial irradiation.

Temperature resistance

Specification	ANSI/UL 969-2018:03 (following)
Test duration	240 h
Rating 150 °C (180 °C)	Test passed

Wipe resistance of inscriptions

Specification	DIN EN 61010-1 (VDE 0411-01):2020-03 DIN EN 62208 (VDE 0660-511):2012-06 (in parts)
Isopropanol (99%) [67-63-0]	Test passed
n-Hexane [CAS No. 110-54-3]	Test passed
Water + Petroleum ether [CAS No. 64742-82-1]	Test passed
Sodium hydroxide 0.1 mol/l [CAS No. 1310-73-2]	Test passed
Ethanol (99 %) [CAS No. 64-17-5]	Test passed
Acetone (99 %) [CAS No. 67-64-1]	Test passed

Immersion in chemicals, oil & fuel

Specification	ISO 175:2010 (following)
Test duration	168 h
Saltwater (saturated 350 g/l) [CAS No. -]	Test passed
Ethanol (99 %) [CAS No. 64-17-5]	Test passed
Acetone (99 %) [CAS No. 67-64-1]	Test passed
Methylethylketone (MEK) [CAS No. 78-93-3]	Test passed
Gasoline [CAS No. 64742-49-0]	Test passed
Diesel [CAS No. 68476-34-6]	Test passed
IRM 901	Test passed
IRM 902	Test passed
IRM 903	Test passed

EMSP-AL (90X60) - Equipment marking



0830504

<https://www.phoenixcontact.com/us/products/0830504>

Testing in a condensation changing climate in the presence of sulfur dioxide

Specification	EN ISO 22479:2022-06
Result	Test passed
Procedure	Method B
Cycles	2

Salt spray test

Specification	DIN EN IEC 60068-2-11 (VDE 0468-2-11):2022-10
Result	Test passed
Test duration	96 h

Standards and regulations

Wipe resistance	DIN EN 61010-1 (VDE 0411-1)
-----------------	-----------------------------

Mounting

Mounting type	screw, rivet
---------------	--------------

EMSP-AL (90X60) - Equipment marking



0830504

<https://www.phoenixcontact.com/us/products/0830504>

Classifications

ECLASS

ECLASS-13.0	27281103
ECLASS-15.0	27281103

ETIM

ETIM 10.0	EC001288
-----------	----------

UNSPSC

UNSPSC 21.0	39131500
-------------	----------

EMSP-AL (90X60) - Equipment marking



0830504

<https://www.phoenixcontact.com/us/products/0830504>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com