

# EML-RM (25X8)RL-T - Label, can be removed



0830545

<https://www.phoenixcontact.com/us/products/0830545>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Label, can be removed, Roll, white (RAL 9010), unmarked, can be labeled with: THERMOMARK E.300 (D)/600 (D), THERMOMARK ROLL 2.0, THERMOMARK ROLL, THERMOMARK ROLL X1, THERMOMARK ROLLMASTER 300/600, THERMOMARK X1.2, mounting type: adhesive, Number of individual labels: 10000, text field height: 8 mm, text field width: 25 mm

## Your advantages

- The EML-RM label is ideal for temporary marking
- This label features solid and reliable adhesion, but can also be easily removed again without any leftover residue. Once removed, it cannot be re-used
- When combined with the right ink ribbon, the marking is highly resistant to solvents and mechanical influences
- The EML-RM ... materials are UL-listed
- Labeling service: Phoenix Contact can custom-label all EML-RM ... markers in accordance with your requirements

## Commercial data

Item number	0830545
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	BG16
Product key	BG2411
GTIN	4046356720571
Weight per piece (including packing)	580.8 g
Weight per piece (excluding packing)	580.8 g
Customs tariff number	39269097
Country of origin	DE

# EML-RM (25X8)RL-T - Label, can be removed



0830545

<https://www.phoenixcontact.com/us/products/0830545>

## Technical data

### Product properties

Product type	Device marker
Product property	removable

### Marking

Number of individual labels	10000
Number of individual labels per row	1
Identification technology	Thermotransfer

### Dimensions

Width	25 mm
Length	8 mm

### Text field

Text field width	25 mm
Text field height	8 mm

### Material specifications

Color	white (RAL 9010)
Material	Polyester
Base element material	Polyester
Components	free from silicone and halogen

### Environmental and real-life conditions

#### Ambient conditions

Ambient temperature (operation)	-40 °C ... 120 °C
Recommended ambient temperature (storage/transport)	23 °C
Recommended humidity (storage/transport)	50 % (Storage in a dry and dark place in the original packaging is recommended)

#### Test for substances that would hinder coating with paint or varnish

Testing for paint wetting impairment substances (LABS-conformity)	VW PV 3.10.7:2005-02
Result	Test passed

#### Test for substances that would hinder coating with paint or varnish

Testing for paint wetting impairment substances (LABS-conformity)	VDMA 24364:2018-05
Result	Test passed

#### Scratch resistance

Specification	DIN EN ISO 1518-1:2019-10 (following)
Requirements	≥ 5 N
Result	Test passed

# EML-RM (25X8)RL-T - Label, can be removed



0830545

<https://www.phoenixcontact.com/us/products/0830545>

## Tesa film test

Specification	DIN EN ISO 2409:2013 (following)
Result	Test passed

## UV resistance

Specification	ISO 4892-2:2013-03 (following)
Result	Test passed
Test duration	96 h
Procedure	Artificial irradiation.

## Temperature resistance

Specification	ANSI/UL 969-2018:03 (following)
Test duration	240 h
Rating 150 °C (180 °C)	Test passed

## Wipe resistance of inscriptions

Specification	DIN EN 61010-1 (VDE 0411-01):2020-03 DIN EN 62208 (VDE 0660-511):2012-06 (in parts)
Isopropanol (99%) [67-63-0]	Test passed
n-Hexane [CAS No. 110-54-3]	Test passed
Water + Petroleum ether [CAS No. 64742-82-1]	Test passed
Sodium hydroxide 0.1 mol/l [CAS No. 1310-73-2]	Test passed
Ethanol (99 %) [CAS No. 64-17-5]	Test passed

## Immersion in chemicals, oil & fuel

Specification	ISO 175:2010 (following)
Test duration	168 h
Saltwater (saturated 350 g/l) [CAS No. - ]	Test passed
Ethanol (99 %) [CAS No. 64-17-5]	Test passed
Diesel [CAS No. 68476-34-6]	Test passed
IRM 901	Test passed
IRM 902	Test passed
IRM 903	Test passed

## Testing in a condensation changing climate in the presence of sulfur dioxide

Specification	DIN 50018:2013-05
Result	Test passed
Climate level	AHT 1.0 S
Cycles	2

## Salt spray test

# EML-RM (25X8)RL-T - Label, can be removed



0830545

<https://www.phoenixcontact.com/us/products/0830545>

Specification	DIN EN 60068-2-11:2000-02
Result	Test passed
Test duration	96 h

## Standards and regulations

Wipe resistance	DIN EN 61010-1 (VDE 0411-1)
-----------------	-----------------------------

## Mounting

Mounting type	adhesive
---------------	----------

# EML-RM (25X8)RL-T - Label, can be removed



0830545

<https://www.phoenixcontact.com/us/products/0830545>

## Classifications

### ECLASS

ECLASS-13.0

27281103

### ETIM

ETIM 9.0

EC001288

### UNSPSC

UNSPSC 21.0

39131500

# EML-RM (25X8)RL-T - Label, can be removed



0830545

<https://www.phoenixcontact.com/us/products/0830545>

## Environmental product compliance

### EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

### EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)