

# EML-HA (85X32)R - Label for rough surfaces



0830610

<https://www.phoenixcontact.com/us/products/0830610>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Label for rough surfaces, Roll, white (RAL 9010), unmarked, can be labeled with: THERMOMARK E.300 (D)/600 (D), THERMOMARK ROLL 2.0, THERMOMARK ROLL, THERMOMARK ROLL X1, THERMOMARK ROLLMaster 300/600, THERMOMARK X1.2, mounting type: adhesive, Number of individual labels: 1000, text field height: 32 mm, text field width: 85 mm

## Your advantages

- The EML-HA ... self-adhesive device markers are suitable for identification of various types of equipment in controller, system, and control cabinet building
- The EML-HA features a special adhesive with a very high bonding strength. This means it can be stuck onto rough, textured, and low-energy surfaces
- When combined with the right ink ribbon, the marking is highly resistant to solvents and mechanical influences
- The EML-HA ... materials are UL-listed
- Marking service: Phoenix Contact can custom-mark all EML-HA ... markers according to your requirements

## Commercial data

Item number	0830610
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	BG16
Product key	BG2411
GTIN	4046356719643
Weight per piece (including packing)	685 g
Weight per piece (excluding packing)	33.33 g
Customs tariff number	39269097
Country of origin	PL

# EML-HA (85X32)R - Label for rough surfaces



0830610

<https://www.phoenixcontact.com/us/products/0830610>

## Technical data

### Product properties

Product type	Device marker
Product property	highly adhesive

### Marking

Number of individual labels	1000
Number of individual labels per row	1
Identification technology	Thermotransfer

### Dimensions

Width	85.00 mm
Height	32.00 mm
Depth	0.11 mm

### Text field

Text field width	85 mm
Text field height	32 mm

### Material specifications

RoHS compliant	yes
Foil strength	50 µm
Adhesive	Synthetic elastomer
Color	white (RAL 9010)
Material	Polyester
Base element material	Polyester
Components	free from silicone and halogen

### Environmental and real-life conditions

#### Ambient conditions

Ambient temperature (operation)	-40 °C ... 150 °C
Recommended ambient temperature (storage/transport)	23 °C
Recommended humidity (storage/transport)	50 % (Storage in a dry and dark place in the original packaging is recommended)

#### Test for substances that would hinder coating with paint or varnish

Testing for paint wetting impairment substances (LABS-conformity)	VW PV 3.10.7:2005-02
Result	Test passed

#### Test for substances that would hinder coating with paint or varnish

Testing for paint wetting impairment substances (LABS-conformity)	VDMA 24364-A1-L:2018-05
Result	Test passed

# EML-HA (85X32)R - Label for rough surfaces



0830610

<https://www.phoenixcontact.com/us/products/0830610>

## Scratch resistance

Specification	EN ISO 1518-1:2023 (following)
Requirements	≥ 5 N
Result	Test passed

## Tesafilm test

Specification	DIN EN ISO 2409:2020-12 (following)
Result	Test passed

## UV resistance

Specification	DIN EN ISO 4892-2:2021-11 (following)
Result	Test passed
Test duration	96 h
Procedure	Artificial irradiation.

## Weathering-resistance

Specification	DIN EN ISO 4892-2:2021-11
Result	Test passed
Test duration	4500 h
Procedure	A

## Outdoor exposure

Specification	DIN EN ISO 877-2 (2011-03-00)
Result	Test passed
Test duration	9048 h

## Temperature resistance

Specification	ANSI/UL 969-2018:03 (following)
Test duration	240 h
Rating 125 °C (150 °C)	Test passed

## Wipe resistance of inscriptions

Specification	DIN EN 61010-1 (VDE 0411-01):2020-03 DIN EN 62208 (VDE 0660-511):2012-06 (in parts)
Isopropanol (99%) [67-63-0]	Test passed
n-Hexane [CAS No. 110-54-3]	Test passed
Water + Petroleum ether [CAS No. 64742-82-1]	Test passed
Sodium hydroxide 0.1 mol/l [CAS No. 1310-73-2]	Test passed
Ethanol (99 %) [CAS No. 64-17-5]	Test passed

## Immersion in chemicals, oil & fuel

Specification	ISO 175:2010 (following)
Test duration	168 h

# EML-HA (85X32)R - Label for rough surfaces



0830610

<https://www.phoenixcontact.com/us/products/0830610>

Sodium hydroxide 0.1 mol/l [CAS No. 1310-73-2]	Test passed
Saltwater (saturated 350 g/l) [CAS No. - ]	Test passed
Ethanol (99 %) [CAS No. 64-17-5]	Test passed
Diesel [CAS No. 68476-34-6]	Test passed
IRM 901	Test passed
IRM 902	Test passed
IRM 903	Test passed

## Testing in a condensation changing climate in the presence of sulfur dioxide

Specification	DIN EN ISO 22479:2022-08
Result	Test passed
Procedure	Method B
Cycles	2

## Salt spray test

Specification	DIN EN IEC 60068-2-11 (VDE 0468-2-11):2022-10
Result	Test passed
Test duration	96 h

## Standards and regulations

Wipe resistance	DIN EN 61010-1 (VDE 0411-1)
-----------------	-----------------------------

## Mounting

Mounting type	adhesive
---------------	----------

# EML-HA (85X32)R - Label for rough surfaces



0830610

<https://www.phoenixcontact.com/us/products/0830610>

## Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/0830610>



**CSA**

Approval ID: 70191766



**cULus Recognized**

Approval ID: MH48542

# EML-HA (85X32)R - Label for rough surfaces



0830610

<https://www.phoenixcontact.com/us/products/0830610>

## Classifications

### ECLASS

ECLASS-13.0	27281103
ECLASS-15.0	27281103

### ETIM

ETIM 10.0	EC001288
-----------	----------

### UNSPSC

UNSPSC 21.0	39131500
-------------	----------

# EML-HA (85X32)R - Label for rough surfaces



0830610

<https://www.phoenixcontact.com/us/products/0830610>

## Environmental product compliance

### EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

### EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)