

# WML 22 (35X25)A4 CUS - Cable marker



0830707

<https://www.phoenixcontact.com/us/products/0830707>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Cable marker, Sheet, can be ordered: in sheets, white (RAL 9010), labeled according to customer specifications, cable diameter range: 8 ... 21.3 mm, mounting type: adhesive, cable diameter:  $\leq 21.3$  mm, Number of individual labels: 10, text field height: 25 mm, text field width: 35 mm



## Your advantages

- For indoor applications: high resistance to dirt and abrasion due to the protective laminate
- Firmly defined positioning of labels thanks to the adhesive system
- Broad diameter range with many different applications inside and outside the control cabinet
- The protective foil is wound over the labeling and provides permanent protection against dirt and abrasion
- The wrap-around labels do not create any additional volume, so the cable can also be pulled through cable ducts, for example
- For cylindrical objects, single wires, and cables

## Commercial data

|                                      |                                |
|--------------------------------------|--------------------------------|
| Item number                          | 0830707                        |
| Packing unit                         | 1 pc                           |
| Minimum order quantity               | 1 pc                           |
| Note                                 | Made to order (non-returnable) |
| Product key                          | BG8134                         |
| GTIN                                 | 4046356718912                  |
| Weight per piece (including packing) | 11.718 g                       |
| Weight per piece (excluding packing) | 11 g                           |
| Country of origin                    | PL                             |

## Technical data

### Product properties

|              |                  |
|--------------|------------------|
| Product type | Conductor marker |
|--------------|------------------|

### Marking

|                                     |                       |
|-------------------------------------|-----------------------|
| Number of individual labels         | 10                    |
| Number of individual labels per row | 5                     |
| Slot type                           | Label                 |
| Identification technology           | Office laser printing |

### Dimensions

|        |          |
|--------|----------|
| Width  | 35 mm    |
| Length | 92.25 mm |

### Text field

|                   |       |
|-------------------|-------|
| Text field width  | 35 mm |
| Text field height | 25 mm |

### Material specifications

|                       |                               |
|-----------------------|-------------------------------|
| RoHS compliant        | yes                           |
| Adhesive              | Acrylic                       |
| Color                 | white (RAL 9010)              |
| Material              | Polyester                     |
| Base element material | Polyester                     |
| Components            | Free from halogen and cadmium |

### Cable/line

|                         |                  |
|-------------------------|------------------|
| External cable diameter | ≤ 21.30 mm       |
|                         | 8 mm ... 21.3 mm |

### Environmental and real-life conditions

#### Ambient conditions

|                                                     |                   |
|-----------------------------------------------------|-------------------|
| Ambient temperature (operation)                     | -40 °C ... 150 °C |
| Recommended ambient temperature (storage/transport) | 23 °C             |
| Recommended humidity (storage/transport)            | 50 %              |

#### Test for substances that would hinder coating with paint or varnish

|                                                                   |                      |
|-------------------------------------------------------------------|----------------------|
| Testing for paint wetting impairment substances (LABS-conformity) | VW PV 3.10.7:2005-02 |
| Result                                                            | Test passed          |

#### UV resistance

|               |                                       |
|---------------|---------------------------------------|
| Specification | DIN EN ISO 4892-2:2021-11 (following) |
| Result        | Test passed                           |

# WML 22 (35X25)A4 CUS - Cable marker



0830707

<https://www.phoenixcontact.com/us/products/0830707>

|               |      |
|---------------|------|
| Test duration | 96 h |
|---------------|------|

## Wipe resistance of inscriptions

|               |                                                |
|---------------|------------------------------------------------|
| Specification | DIN EN 61010-1 (VDE 0411-01):2020-03           |
|               | DIN EN 62208 (VDE 0660-511):2012-06 (in parts) |

## Standards and regulations

|                 |                             |
|-----------------|-----------------------------|
| Wipe resistance | DIN EN 61010-1 (VDE 0411-1) |
|-----------------|-----------------------------|

## Mounting

|               |          |
|---------------|----------|
| Mounting type | adhesive |
|---------------|----------|

# WML 22 (35X25)A4 CUS - Cable marker



0830707

<https://www.phoenixcontact.com/us/products/0830707>

## Classifications

### ECLASS

|             |          |
|-------------|----------|
| ECLASS-13.0 | 27281102 |
| ECLASS-15.0 | 27281102 |

### ETIM

|           |          |
|-----------|----------|
| ETIM 10.0 | EC001530 |
|-----------|----------|

### UNSPSC

|             |          |
|-------------|----------|
| UNSPSC 21.0 | 39131500 |
|-------------|----------|

# WML 22 (35X25)A4 CUS - Cable marker



0830707

<https://www.phoenixcontact.com/us/products/0830707>

## Environmental product compliance

### EU RoHS

|                                         |                    |
|-----------------------------------------|--------------------|
| Fulfills EU RoHS substance requirements | Yes, No exemptions |
|-----------------------------------------|--------------------|

### EU REACH SVHC

|                                     |                            |
|-------------------------------------|----------------------------|
| REACH candidate substance (CAS No.) | No substance above 0.1 wt% |
|-------------------------------------|----------------------------|

Phoenix Contact 2026 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)