

# WML-FLAGV 6 (30X10)R CUS - Cable marking flags



0830718

<https://www.phoenixcontact.com/us/products/0830718>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Cable marking flags, Roll, can be ordered: by line, white (RAL 9010), labeled according to customer specifications, mounting type: adhesive, cable diameter:  $\leq 6$  mm, Number of individual labels: 2500, text field height: 10 mm, text field width: 30 mm

## Your advantages

- Self-adhesive conductor marking as a flag
- High-quality marking created by the thermal transfer printer
- Resistant to solvents
- Can be printed on both sides

## Commercial data

Item number	0830718
Packing unit	1 pc
Minimum order quantity	1 pc
Note	Made to order (non-returnable)
Product key	BG8121
GTIN	4046356724623
Weight per piece (including packing)	1.99 g
Weight per piece (excluding packing)	1.99 g
Country of origin	PL

## Technical data

### Product properties

Product type	Conductor marker
--------------	------------------

### Marking

Number of individual labels	2500
Number of individual labels per row	3
Identification technology	Thermotransfer

### Dimensions

Width	10 mm
Length	30 mm

### Text field

Text field width	30 mm
Text field height	10 mm

### Material specifications

Color	white (RAL 9010)
Material	Polyolefine
Base element material	Vinyl film
Components	free from silicone and halogen

### Cable/line

External cable diameter	≤ 6.00 mm
-------------------------	-----------

### Environmental and real-life conditions

#### Ambient conditions

Ambient temperature (operation)	-40 °C ... 60 °C
Recommended ambient temperature (storage/transport)	23 °C
Recommended humidity (storage/transport)	50 % (Storage in a dry and dark place in the original packaging is recommended)

#### UV resistance

Specification	DIN EN ISO 4892-2:2021-11 (following)
---------------	---------------------------------------

#### Wipe resistance of inscriptions

Specification	DIN EN 61010-1 (VDE 0411-01):2020-03
	DIN EN 62208 (VDE 0660-511):2012-06 (in parts)

### Standards and regulations

Wipe resistance	DIN EN 61010-1 (VDE 0411-1)
-----------------	-----------------------------

### Mounting

Mounting type	adhesive
---------------	----------

# WML-FLAGV 6 (30X10)R CUS - Cable marking flags



0830718

<https://www.phoenixcontact.com/us/products/0830718>

## Classifications

### ECLASS

ECLASS-13.0	27281102
ECLASS-15.0	27281102

### ETIM

ETIM 10.0	EC001530
-----------	----------

### UNSPSC

UNSPSC 21.0	39131500
-------------	----------

# WML-FLAGV 6 (30X10)R CUS - Cable marking flags



0830718

<https://www.phoenixcontact.com/us/products/0830718>

## Environmental product compliance

### EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

### EU REACH SVHC

REACH candidate substance (CAS No.)	4-(1,1,3,3-tetramethylbutyl)phenol, ethoxylated(CAS: n/a)
SCIP	46b5f541-a834-480a-b636-881dca7f9207

Phoenix Contact 2026 © - all rights reserved  
<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)