

EML-ESD (25X8)RL-T - Equipment marking



0830581

<https://www.phoenixcontact.com/us/products/0830581>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Equipment marking, Roll, white (RAL 9010), unmarked, can be labeled with: THERMOMARK E. 300 (D)/600 (D), THERMOMARK ROLL 2.0, THERMOMARK ROLL, THERMOMARK ROLL X1, THERMOMARK ROLLMASTER 300/600, THERMOMARK X1.2, mounting type: adhesive, Number of individual labels: 10000, text field height: 8 mm, text field width: 25 mm

Your advantages

- The EML-ESD label is well suited for marking sensitive components on printed-circuit boards
- The label includes an adhesive that dissipates static electricity, which prevents the transmission of electrostatic voltages and protects the component
- When combined with the right ink ribbon, the marking is highly resistant to solvents
- The EML-ESD ... materials are UL-listed
- Labeling service: Phoenix Contact can custom-label all EML-ESD ... markers in accordance with your requirements

Commercial data

Item number	0830581
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	BG16
Product key	BG2411
GTIN	4046356720205
Weight per piece (including packing)	641.2 g
Weight per piece (excluding packing)	641.2 g
Customs tariff number	39269097
Country of origin	DE

EML-ESD (25X8)RL-T - Equipment marking



0830581

<https://www.phoenixcontact.com/us/products/0830581>

Technical data

Notes

General	For the THERMOMARK ROLL and THERMOMARK ROLL 2.0 roll printers, this material can only be processed with an external media hub.
---------	--

Product properties

Product type	Device marker
Product property	ESD safe

Marking

Number of individual labels	10000
Number of individual labels per row	1
Identification technology	Thermotransfer

Dimensions

Width	25 mm
Length	8 mm

Text field

Text field width	25 mm
Text field height	8 mm

Material specifications

RoHS compliant	yes
Foil strength	52 µm
Adhesive strength	24 µm
Adhesive	Acrylic
Color	white (RAL 9010)
Material	Polyester
Base element material	Polyester
Components	free from silicone and halogen

Environmental and real-life conditions

Ambient conditions

Ambient temperature (operation)	-40 °C ... 150 °C
Recommended ambient temperature (storage/transport)	23 °C
Recommended humidity (storage/transport)	50 % (Storage in a dry and dark place in the original packaging is recommended)

Test for substances that would hinder coating with paint or varnish

Testing for paint wetting impairment substances (LABS-conformity)	VDMA 24364-A1-L:2018-05
Result	Test passed

EML-ESD (25X8)RL-T - Equipment marking



0830581

<https://www.phoenixcontact.com/us/products/0830581>

Test for substances that would hinder coating with paint or varnish

Testing for paint wetting impairment substances (LABS-conformity)	VW PV 3.10.7:2005-02
Result	Test passed

Scratch resistance

Specification	DIN EN ISO 1518-1:2019-10 (following)
Requirements	≥ 5 N
Result	Test passed

Tesafilm test

Specification	DIN EN ISO 2409:2013 (following)
Result	Test passed

UV resistance

Specification	ISO 4892-2:2013-03 (following)
Result	Test passed
Test duration	96 h
Procedure	Artificial irradiation.

Temperature resistance

Specification	ANSI/UL 969-2018:03 (following)
Test duration	240 h
Rating 150 °C (180 °C)	Test passed

Wipe resistance of inscriptions

Specification	DIN EN 61010-1 (VDE 0411-01):2020-03 DIN EN 62208 (VDE 0660-511):2012-06 (in parts)
Isopropanol (99%) [67-63-0]	Test passed
n-Hexane [CAS No. 110-54-3]	Test passed
Water + Petroleum ether [CAS No. 64742-82-1]	Test passed
Sodium hydroxide 0.1 mol/l [CAS No. 1310-73-2]	Test passed
Ethanol (99 %) [CAS No. 64-17-5]	Test passed

Immersion in chemicals, oil & fuel

Specification	ISO 175:2010 (following)
Test duration	168 h
Saltwater (saturated 350 g/l) [CAS No. -]	Test passed
Ethanol (99 %) [CAS No. 64-17-5]	Test passed
Diesel [CAS No. 68476-34-6]	Test passed
IRM 901	Test passed

EML-ESD (25X8)RL-T - Equipment marking



0830581

<https://www.phoenixcontact.com/us/products/0830581>

IRM 902	Test passed
IRM 903	Test passed

Testing in a condensation changing climate in the presence of sulfur dioxide

Specification	DIN 50018:2013-05
Result	Test passed
Climate level	AHT 1.0 S
Cycles	2

Salt spray test

Specification	DIN EN 60068-2-11:2000-02
Result	Test passed
Test duration	96 h

Standards and regulations

Wipe resistance	DIN EN 61010-1 (VDE 0411-1)
-----------------	-----------------------------

Mounting

Mounting type	adhesive
---------------	----------

EML-ESD (25X8)RL-T - Equipment marking



0830581

<https://www.phoenixcontact.com/us/products/0830581>

Classifications

ECLASS

ECLASS-13.0

27281103

ETIM

ETIM 9.0

EC001288

UNSPSC

UNSPSC 21.0

39131500

EML-ESD (25X8)RL-T - Equipment marking



0830581

<https://www.phoenixcontact.com/us/products/0830581>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com