

US-EMP (27,9X17,4) - Snap-in markers



0830980

<https://www.phoenixcontact.com/us/products/0830980>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Snap-in markers, Card, white (RAL 9010), unmarked, can be labeled with: BLUEMARK ID COLOR, BLUEMARK ID, THERMOMARK PRIME, THERMOMARK CARD 2.0, THERMOMARK CARD, THERMOMARK PRIME 2.0, mounting type: latching, Number of individual labels: 21, text field height: 17.4 mm, text field width: 27.9 mm



Your advantages

- All US-EMP ... device markers can also be supplied labeled according to customer requirements
- The US-EMP ... UniSheet labeling range includes markers that can be fitted into existing CARRIER EMP ... label frames
- The perforated markers and labels are easy to separate and can be easily fitted
- The sheets provide space for including function texts

Commercial data

Item number	0830980
Packing unit	10 pc
Minimum order quantity	10 pc
Product key	BG2419
GTIN	4046356913515
Weight per piece (including packing)	15.47 g
Weight per piece (excluding packing)	9.99 g
Country of origin	DE

US-EMP (27,9X17,4) - Snap-in markers



0830980

<https://www.phoenixcontact.com/us/products/0830980>

Technical data

Product properties

Product type	Device marker
--------------	---------------

Marking

Number of individual labels	21
Number of individual labels per row	3
Identification technology	Thermotransfer

Dimensions

Width	27.90 mm
Height	17.40 mm
Depth	0.50 mm

Text field

Text field width	27.9 mm
Text field height	17.4 mm

Material specifications

Color	white (RAL 9010)
Flammability rating according to UL 94	V0
Base element material	PVC
Components	Silicone-free

Environmental and real-life conditions

Ambient conditions

Ambient temperature (operation)	-30 °C ... 80 °C
Recommended ambient temperature (storage/transport)	23 °C
Recommended humidity (storage/transport)	50 % (Storage in a dry and dark place in the original packaging is recommended)

Wipe resistance of inscriptions

Specification	DIN EN 61010-1 (VDE 0411-01):2020-03
	DIN EN 62208 (VDE 0660-511):2012-06 (in parts)

Mounting

Mounting type	latching
---------------	----------

US-EMP (27,9X17,4) - Snap-in markers



0830980

<https://www.phoenixcontact.com/us/products/0830980>

Classifications

ECLASS

ECLASS-13.0	27281106
ECLASS-15.0	27281106

ETIM

ETIM 10.0	EC001288
-----------	----------

UNSPSC

UNSPSC 21.0	39131700
-------------	----------

US-EMP (27,9X17,4) - Snap-in markers



0830980

<https://www.phoenixcontact.com/us/products/0830980>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

EF3.1 Climate Change

CO2e kg	0.055 kg CO2e
---------	---------------

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com