

# EML-HA (26,5X12)R CUS - Label for rough surfaces



0830625

<https://www.phoenixcontact.com/us/products/0830625>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Label for rough surfaces, Roll, can be ordered: by line, white (RAL 9010), labeled according to customer specifications, mounting type: adhesive, Number of individual labels: 2, text field height: 12 mm, text field width: 26.5 mm

## Your advantages

- The EML-HA ... self-adhesive device markers are suitable for identification of various types of equipment in controller, system, and control cabinet building
- The EML-HA features a special adhesive with a very high bonding strength. This means it can be stuck onto rough, textured, and low-energy surfaces
- When combined with the right ink ribbon, the marking is highly resistant to solvents and mechanical influences
- The EML-HA ... materials are UL-listed
- Marking service: Phoenix Contact can custom-mark all EML-HA ... markers according to your requirements

## Commercial data

|                                      |                                |
|--------------------------------------|--------------------------------|
| Item number                          | 0830625                        |
| Packing unit                         | 1 pc                           |
| Minimum order quantity               | 1 pc                           |
| Note                                 | Made to order (non-returnable) |
| Product key                          | BG8141                         |
| GTIN                                 | 4046356719797                  |
| Weight per piece (including packing) | 1.99 g                         |
| Weight per piece (excluding packing) | 1.99 g                         |
| Country of origin                    | PL                             |

# EML-HA (26,5X12)R CUS - Label for rough surfaces



0830625

<https://www.phoenixcontact.com/us/products/0830625>

## Technical data

### Product properties

|                  |                 |
|------------------|-----------------|
| Product type     | Device marker   |
| Product property | highly adhesive |

### Marking

|                                     |                |
|-------------------------------------|----------------|
| Number of individual labels         | 2              |
| Number of individual labels per row | 2              |
| Identification technology           | Thermotransfer |

### Dimensions

|        |          |
|--------|----------|
| Width  | 26.50 mm |
| Height | 12.00 mm |
| Depth  | 0.11 mm  |
| Length | 12 mm    |

### Text field

|                   |         |
|-------------------|---------|
| Text field width  | 26.5 mm |
| Text field height | 12 mm   |

### Material specifications

|                       |                                |
|-----------------------|--------------------------------|
| RoHS compliant        | yes                            |
| Foil strength         | 50 µm                          |
| Adhesive              | Synthetic elastomer            |
| Color                 | white (RAL 9010)               |
| Material              | Polyester                      |
| Base element material | Polyester                      |
| Components            | free from silicone and halogen |

### Environmental and real-life conditions

#### Ambient conditions

|   |   |
|---|---|
| Ambient temperature (operation)                     | -40 °C ... 150 °C   |
| Recommended ambient temperature (storage/transport) | 23 °C   |
| Recommended humidity (storage/transport)            | 50 % (Storage in a dry and dark place in the original packaging is recommended) |

#### Test for substances that would hinder coating with paint or varnish

|   |                      |
|---|----------------------|
| Testing for paint wetting impairment substances (LABS-conformity) | VW PV 3.10.7:2005-02 |
| Result  | Test passed          |

#### Test for substances that would hinder coating with paint or varnish

|   |                         |
|---|-------------------------|
| Testing for paint wetting impairment substances (LABS-conformity) | VDMA 24364-A1-L:2018-05 |
| Result  | Test passed             |

# EML-HA (26,5X12)R CUS - Label for rough surfaces



0830625

<https://www.phoenixcontact.com/us/products/0830625>

## Scratch resistance

|               |                                |
|---------------|--------------------------------|
| Specification | EN ISO 1518-1:2023 (following) |
| Requirements  | ≥ 5 N                          |
| Result        | Test passed                    |

## Tesafilm test

|               |                                     |
|---------------|-------------------------------------|
| Specification | DIN EN ISO 2409:2020-12 (following) |
| Result        | Test passed                         |

## UV resistance

|               |                                       |
|---------------|---------------------------------------|
| Specification | DIN EN ISO 4892-2:2021-11 (following) |
| Result        | Test passed                           |
| Test duration | 96 h                                  |
| Procedure     | Artificial irradiation.               |

## Weathering-resistance

|               |                           |
|---------------|---------------------------|
| Specification | DIN EN ISO 4892-2:2021-11 |
| Result        | Test passed               |
| Test duration | 4500 h                    |
| Procedure     | A                         |

## Outdoor exposure

|               |                               |
|---------------|-------------------------------|
| Specification | DIN EN ISO 877-2 (2011-03-00) |
| Result        | Test passed                   |
| Test duration | 9048 h                        |

## Temperature resistance

|                        |                                 |
|------------------------|---------------------------------|
| Specification          | ANSI/UL 969-2018:03 (following) |
| Test duration          | 240 h                           |
| Rating 125 °C (150 °C) | Test passed                     |

## Wipe resistance of inscriptions

|   |  |
|---|--|
| Specification                                     | DIN EN 61010-1 (VDE 0411-01):2020-03<br>DIN EN 62208 (VDE 0660-511):2012-06 (in parts) |
| Isopropanol (99%) [67-63-0]                       | Test passed  |
| n-Hexane<br>[CAS No. 110-54-3]                    | Test passed  |
| Water + Petroleum ether<br>[CAS No. 64742-82-1]   | Test passed  |
| Sodium hydroxide 0.1 mol/l<br>[CAS No. 1310-73-2] | Test passed  |
| Ethanol (99 %)<br>[CAS No. 64-17-5]               | Test passed  |

## Immersion in chemicals, oil & fuel

|               |                          |
|---------------|--------------------------|
| Specification | ISO 175:2010 (following) |
| Test duration | 168 h                    |

# EML-HA (26,5X12)R CUS - Label for rough surfaces



0830625

<https://www.phoenixcontact.com/us/products/0830625>

|   |             |
|---|-------------|
| Sodium hydroxide 0.1 mol/l<br>[CAS No. 1310-73-2] | Test passed |
| Saltwater (saturated 350 g/l)<br>[CAS No. - ]     | Test passed |
| Ethanol (99 %)<br>[CAS No. 64-17-5]               | Test passed |
| Diesel<br>[CAS No. 68476-34-6]                    | Test passed |
| IRM 901   | Test passed |
| IRM 902   | Test passed |
| IRM 903   | Test passed |

## Testing in a condensation changing climate in the presence of sulfur dioxide

|               |                          |
|---------------|--------------------------|
| Specification | DIN EN ISO 22479:2022-08 |
| Result        | Test passed              |
| Procedure     | Method B                 |
| Cycles        | 2                        |

## Salt spray test

|               |   |
|---------------|---|
| Specification | DIN EN IEC 60068-2-11 (VDE 0468-2-11):2022-10 |
| Result        | Test passed                                   |
| Test duration | 96 h  |

## Standards and regulations

|                 |                             |
|-----------------|-----------------------------|
| Wipe resistance | DIN EN 61010-1 (VDE 0411-1) |
|-----------------|-----------------------------|

## Mounting

|               |          |
|---------------|----------|
| Mounting type | adhesive |
|---------------|----------|

# EML-HA (26,5X12)R CUS - Label for rough surfaces



0830625

<https://www.phoenixcontact.com/us/products/0830625>

## Classifications

### ECLASS

|             |          |
|-------------|----------|
| ECLASS-13.0 | 27281103 |
| ECLASS-15.0 | 27281103 |

### ETIM

|           |          |
|-----------|----------|
| ETIM 10.0 | EC001288 |
|-----------|----------|

### UNSPSC

|             |          |
|-------------|----------|
| UNSPSC 21.0 | 39131500 |
|-------------|----------|

# EML-HA (26,5X12)R CUS - Label for rough surfaces



0830625

<https://www.phoenixcontact.com/us/products/0830625>

## Environmental product compliance

### EU RoHS

|   |                    |
|---|--------------------|
| Fulfills EU RoHS substance requirements | Yes, No exemptions |
|---|--------------------|

### EU REACH SVHC

|                                     |                            |
|-------------------------------------|----------------------------|
| REACH candidate substance (CAS No.) | No substance above 0.1 wt% |
|-------------------------------------|----------------------------|

Phoenix Contact 2026 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)