

PMT (10X38) GN - Insert label



0831091

<https://www.phoenixcontact.com/us/products/0831091>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Marking label for conveyed fluids, for equipping CARRIER-PMP (110x38), CARRIER/L-PMP (110x38), and CARRIER-PMP-ENCLOSED (110x38) according to DIN 2403



Commercial data

| | |
|--------------------------------------|---------------|
| Item number | 0831091 |
| Packing unit | 100 pc |
| Minimum order quantity | 100 pc |
| Product key | BG261Z |
| GTIN | 4046356941242 |
| Weight per piece (including packing) | 0.642 g |
| Weight per piece (excluding packing) | 0.642 g |
| Country of origin | DE |

PMT (10X38) GN - Insert label



0831091

<https://www.phoenixcontact.com/us/products/0831091>

Technical data

Product properties

| | |
|---------------------|---|
| Product type | Plant marker |
| Area of application | Identification of flow substances according to DIN 2403 |

Marking

| | |
|-------------------------------------|---|
| Number of individual labels | 1 |
| Number of individual labels per row | 1 |

Dimensions

| | |
|--------|----------|
| Width | 38.00 mm |
| Height | 10.00 mm |
| Depth | 1.00 mm |

Material specifications

| | |
|-----------------------|--------------------------------|
| Color | green (RAL 6021) |
| Base element material | PVC |
| Components | Free from silicone and cadmium |

Environmental and real-life conditions

Ambient conditions

| | |
|---|--|
| Ambient temperature (operation) | -30 °C ... 80 °C |
| Recommended ambient temperature (storage/transport) | 10 °C |
| Recommended humidity (storage/transport) | 40 % ... 70 % (Storage in a dry and dark place in the original packaging is recommended) |

UV resistance

| | |
|---------------|---------------------------------------|
| Specification | DIN EN ISO 4892-2:2021-11 (following) |
| Result | Test passed |
| Test duration | 96 h |
| Procedure | Artificial irradiation. |

Wipe resistance of inscriptions

| | |
|---------------|--|
| Specification | DIN EN 61010-1 (VDE 0411-01):2020-03 |
| | DIN EN 62208 (VDE 0660-511):2012-06 (in parts) |

Mounting

| | |
|---------------|----------|
| Mounting type | latching |
|---------------|----------|

PMT (10X38) GN - Insert label



0831091

<https://www.phoenixcontact.com/us/products/0831091>

Classifications

ECLASS

| | |
|-------------|----------|
| ECLASS-13.0 | 27281104 |
| ECLASS-15.0 | 27281104 |

ETIM

| | |
|-----------|----------|
| ETIM 10.0 | EC001288 |
|-----------|----------|

UNSPSC

| | |
|-------------|----------|
| UNSPSC 21.0 | 39131500 |
|-------------|----------|

PMT (10X38) GN - Insert label



0831091

<https://www.phoenixcontact.com/us/products/0831091>

Environmental product compliance

EU RoHS

| | |
|---|--------------------|
| Fulfills EU RoHS substance requirements | Yes, No exemptions |
|---|--------------------|

EU REACH SVHC

| | |
|-------------------------------------|----------------------------|
| REACH candidate substance (CAS No.) | No substance above 0.1 wt% |
|-------------------------------------|----------------------------|

Phoenix Contact 2026 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com