

# WML 36 (25X38)A4 YE - Cable marker label



0830698

<https://www.phoenixcontact.com/us/products/0830698>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Cable marker label, Sheet, can be ordered: in sheets, yellow (RAL 1018), unmarked, can be labeled with: Office printing systems, CMS-P1-PLOTTER, PLOTMARK, cable diameter range: 12.1 ... 36.4 mm, mounting type: adhesive, cable diameter:  $\leq 36.4$  mm, Number of individual labels: 14, text field height: 38.1 mm, text field width: 25 mm



## Your advantages

- For indoor applications: high resistance to dirt and abrasion due to the protective laminate
- Firmly defined positioning of labels thanks to the adhesive system
- Broad diameter range with many different applications inside and outside the control cabinet
- The protective foil is wound over the labeling and provides permanent protection against dirt and abrasion
- The wrap-around labels do not create any additional volume, so the cable can also be pulled through cable ducts, for example
- For cylindrical objects, single wires, and cables

## Commercial data

Item number	0830698
Packing unit	10 pc
Minimum order quantity	10 pc
Product key	BG2314
GTIN	4046356718820
Weight per piece (including packing)	15.75 g
Weight per piece (excluding packing)	16.56 g
Country of origin	DE

# WML 36 (25X38)A4 YE - Cable marker label



0830698

<https://www.phoenixcontact.com/us/products/0830698>

## Technical data

### Product properties

Product type	Conductor marker
--------------	------------------

### Marking

Number of individual labels	14
Number of individual labels per row	7
Slot type	Label
Identification technology	Office laser printing

### Dimensions

Width	25 mm
Height	152.4 mm
Depth	0.1 mm

### Text field

Text field width	25 mm
Text field height	38.1 mm

### Material specifications

RoHS compliant	yes
Adhesive	Acrylic
Color	yellow (RAL 1018)
Material	Polyester
Base element material	Polyester
Components	Free from halogen and cadmium

### Cable/line

External cable diameter	≤ 36.40 mm
	12.1 mm ... 36.4 mm

### Environmental and real-life conditions

#### Ambient conditions

Ambient temperature (operation)	-40 °C ... 150 °C
Recommended ambient temperature (storage/transport)	23 °C
Recommended humidity (storage/transport)	50 % (Storage in a dry and dark place in the original packaging is recommended)

#### Test for substances that would hinder coating with paint or varnish

Testing for paint wetting impairment substances (LABS-conformity)	VW PV 3.10.7:2005-02
Result	Test passed

#### UV resistance

Specification	DIN EN ISO 4892-2:2021-11 (following)
---------------	---------------------------------------

# WML 36 (25X38)A4 YE - Cable marker label



0830698

<https://www.phoenixcontact.com/us/products/0830698>

Result	Test passed
Test duration	96 h
Procedure	Artificial irradiation.

## Wipe resistance of inscriptions

Specification	DIN EN 61010-1 (VDE 0411-01):2020-03 DIN EN 62208 (VDE 0660-511):2012-06 (in parts)
Isopropanol (99%) [67-63-0]	Test passed
n-Hexane [CAS No. 110-54-3]	Test passed
Water + Petroleum ether [CAS No. 64742-82-1]	Test passed

## Testing in a condensation changing climate in the presence of sulfur dioxide

Specification	DIN EN ISO 22479:2022-08
Result	Test passed
Procedure	Method B
Cycles	2

## Salt spray test

Specification	DIN EN IEC 60068-2-11 (VDE 0468-2-11):2022-10
Result	Test passed

## Standards and regulations

Wipe resistance	DIN EN 61010-1 (VDE 0411-1)
-----------------	-----------------------------

## Mounting

Mounting type	adhesive
---------------	----------

# WML 36 (25X38)A4 YE - Cable marker label



0830698

<https://www.phoenixcontact.com/us/products/0830698>

## Classifications

### ECLASS

ECLASS-13.0	27281102
ECLASS-15.0	27281102

### ETIM

ETIM 10.0	EC001530
-----------	----------

### UNSPSC

UNSPSC 21.0	39131500
-------------	----------

# WML 36 (25X38)A4 YE - Cable marker label



0830698

<https://www.phoenixcontact.com/us/products/0830698>

## Environmental product compliance

### EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

### EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)