
# LS-EMSP-AL (150X80) - Device marker

0831621

https://www.phoenixcontact.com/us/products/0831621

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Device marker, Aluminum label, unmarked, can be labeled with: TOPMARK NEO, TOPMARK LASER, mounting type: screw, rivet, Number of individual labels: 2, text field height: 80 mm, text field width: 150 mm

## Your advantages

- Aluminum equipment marking for screwing or riveting
- Identification made from metal, high strength in a lightweight design
- Increased durability due to the decoratively anodized surface

## Commercial data

| | |
|---|---|
| Item number | 0831621 |
| Packing unit | 5 pc |
| Minimum order quantity | 5 pc |
| Sales key | BG19 |
| Product key | BG241D |
| GTIN | 4046356925709 |
| Weight per piece (including packing) | 138.19 g |
| Weight per piece (excluding packing) | 135.16 g |
| Customs tariff number | 76169990 |
| Country of origin | CN |

# Technical data

## Product properties

| | |
|---|---|
| Product type | Device marker |

### Marking

| | |
|---|---|
| Number of individual labels | 2 |
| Identification technology | Direct laser marking |

## Dimensions

| | |
|---|---|
| Width | 160.00 mm |
| Height | 80.00 mm |
| Depth | 1.50 mm |

### Text field

| | |
|---|---|
| Text field width | 150 mm |
| Text field height | 80 mm |

## Material specifications

| | |
|---|---|
| Color | aluminum color |
| Base element material | Aluminum |
| Components | free from silicone, halogen, and cadmium |

## Environmental and real-life conditions

### Ambient conditions

| | |
|---|---|
| Ambient temperature (operation) | -20 °C ... 225 °C (At temperatures above 80 °C there might be a slight change to the material surface) |
| Recommended ambient temperature (storage/transport) | 23 °C |
| Recommended humidity (storage/transport) | 50 % (Storage in a dry and dark place in the original packaging is recommended) |

### Test for substances that would hinder coating with paint or varnish

| | |
|---|---|
| Testing for paint wetting impairment substances (LABS-conformity) | VDMA 24364:2018-05 |
| Result | Test passed |

### Test for substances that would hinder coating with paint or varnish

| | |
|---|---|
| Testing for paint wetting impairment substances (LABS-conformity) | VW PV 3.10.7:2005-02 |
| Result | Test passed |

### Scratch resistance

| | |
|---|---|
| Specification | EN ISO 1518-1:2023 (following) |
| Requirements | ≥ 5 N |
| Result | Test passed |

### Tesafilm test

| | |
|---|---|
| Specification | DIN EN ISO 2409:2020-12 (following) |
| Result | Test passed |

UV resistance

| | |
|---|---|
| Specification | DIN EN ISO 4892-2:2021-11 (following) |
| Result | Test passed |
| Test duration | 96 h |
| Procedure | Artificial irradiation. |

Temperature resistance

| | |
|---|---|
| Specification | ANSI/UL 969-2018:03 (following) |
| Test duration | 240 h |
| Rating 225 °C (250 °C) | Test passed |

Wipe resistance of inscriptions

| | |
|---|---|
| Specification | DIN EN 61010-1 (VDE 0411-01):2020-03 |
| | DIN EN 62208 (VDE 0660-511):2012-06 (in parts) |
| Isopropanol (99%) [67-63-0] | Test passed |
| n-Hexane<br>[CAS No. 110-54-3] | Test passed |
| Water + Petroleum ether<br>[CAS No. 64742-82-1] | Test passed |
| Sodium hydroxide 0.1 mol/l<br>[CAS No. 1310-73-2] | Test passed |
| Ethanol (99 %)<br>[CAS No. 64-17-5] | Test passed |
| Acetone (99 %)<br>[CAS No. 67-64-1] | Test passed |

Immersion in chemicals, oil & fuel

| | |
|---|---|
| Specification | ISO 175:2010 (following) |
| Test duration | 168 h |
| Saltwater (saturated 350 g/l)<br>[CAS No. - ] | Test passed |
| Ethanol (99 %)<br>[CAS No. 64-17-5] | Test passed |
| Acetone (99 %)<br>[CAS No. 67-64-1] | Test passed |
| Methylethylketone (MEK)<br>[CAS No. 78-93-3] | Test passed |
| IRM 901 | Test passed |
| IRM 902 | Test passed |
| IRM 903 | Test passed |

Testing in a condensation changing climate in the presence of sulfur dioxide

| | |
|---|---|
| Specification | EN ISO 22479:2022-06 |
| Result | Test passed |
| Procedure | Method B |
| Cycles | 2 |

Salt spray test

| | |
|---|---|
| Specification | DIN EN IEC 60068-2-11 (VDE 0468-2-11):2022-10 |
| Result | Test passed |
| Test duration | 96 h |

High pressure test

| | |
|---|---|
| Specification | ISO 20653:2013-02 |
| Result | Test passed |
| IP-Code | IP X9K |

## Standards and regulations

| | |
|---|---|
| Wipe resistance | DIN EN 61010-1 (VDE 0411-1) |

## Mounting

| | |
|---|---|
| Mounting type | screw, rivet |

## Classifications

### ECLASS

| | |
|---|---|
| ECLASS-13.0 | 27281103 |
| ECLASS-15.0 | 27281103 |

### ETIM

| | |
|---|---|
| ETIM 10.0 | EC001288 |

### UNSPSC

| | |
|---|---|
| UNSPSC 21.0 | 39131500 |

## Environmental product compliance

EU RoHS

| | |
|---|---|
| Fulfills EU RoHS substance requirements | Yes, No exemptions |

EU REACH SVHC

| | |
|---|---|
| REACH candidate substance (CAS No.) | No substance above 0.1 wt% |

Phoenix Contact 2026 © - all rights reserved
https://www.phoenixcontact.com

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com