

WMTB-AL (29X8) CUS - Aluminum label



0830807

<https://www.phoenixcontact.com/us/products/0830807>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Aluminum label, Aluminum label, can be ordered: Piece, labeled according to customer specifications, mounting type: Assembly with cable ties, cable diameter: > 2.9 mm, Number of individual labels: 1, text field height: 8 mm, text field width: 29 mm

Product description

Note:
Due to the current challenges of the global procurement market, Phoenix Contact has unfortunately been forced to accept an aluminum alloy material quality that may cause the appearance to deviate from the homogenous surface quality that was previously expected. This has no impact on the quality of the aluminum labels themselves or the durability of the printing. The effect is purely visual.

Your advantages

- Aluminum cable marking for assembly with cable ties
- High-quality appearance
- Suitable for large-surface marking of wires and cables, > 2.9 mm in diameter

Commercial data

Item number	0830807
Packing unit	1 pc
Minimum order quantity	1 pc
Note	Made to order (non-returnable)
Product key	BG813B
GTIN	4046356780834
Weight per piece (including packing)	1.03 g
Weight per piece (excluding packing)	0.708 g
Country of origin	PL

Technical data

Product properties

Product type	Conductor marker
--------------	------------------

Marking

Number of individual labels	1
Identification technology	UV LED technology

Dimensions

Width	8 mm
Length	48 mm

Text field

Text field width	29 mm
Text field height	8 mm

Material specifications

Color	aluminum color
Base element material	Aluminum
Components	free from silicone, halogen, and cadmium

Cable/line

External cable diameter	> 2.90 mm
-------------------------	-----------

Environmental and real-life conditions

Ambient conditions

Ambient temperature (operation)	-25 °C ... 120 °C (> +80 °C slight changes of the material surface possible)
Recommended ambient temperature (storage/transport)	5 °C
Recommended humidity (storage/transport)	50 % (Storage in a dry and dark place in the original packaging is recommended)

Test for substances that would hinder coating with paint or varnish

Testing for paint wetting impairment substances (LABS-conformity)	VDMA 24364:2018-05
Result	Test passed

Test for substances that would hinder coating with paint or varnish

Testing for paint wetting impairment substances (LABS-conformity)	VW PV 3.10.7:2005-02
Result	Test passed

Scratch resistance

Specification	EN ISO 1518-1:2023 (following)
Requirements	≥ 5 N
Result	Test passed

WMTB-AL (29X8) CUS - Aluminum label



0830807

<https://www.phoenixcontact.com/us/products/0830807>

Tesafilem test

Specification	DIN EN ISO 2409:2020-12 (following)
Result	Test passed

UV resistance

Specification	DIN EN ISO 4892-2:2021-11 (following)
Result	Test passed
Test duration	96 h
Procedure	Artificial irradiation.

Temperature resistance

Specification	ANSI/UL 969-2018:03 (following)
Test duration	240 h
Rating 150 °C (180 °C)	Test passed

Wipe resistance of inscriptions

Specification	DIN EN 61010-1 (VDE 0411-01):2020-03 DIN EN 62208 (VDE 0660-511):2012-06 (in parts)
Isopropanol (99%) [67-63-0]	Test passed
n-Hexane [CAS No. 110-54-3]	Test passed
Water + Petroleum ether [CAS No. 64742-82-1]	Test passed
Sodium hydroxide 0.1 mol/l [CAS No. 1310-73-2]	Test passed
Ethanol (99 %) [CAS No. 64-17-5]	Test passed
Acetone (99 %) [CAS No. 67-64-1]	Test passed

Immersion in chemicals, oil & fuel

Specification	ISO 175:2010 (following)
Test duration	168 h
Saltwater (saturated 350 g/l) [CAS No. -]	Test passed
Ethanol (99 %) [CAS No. 64-17-5]	Test passed
Acetone (99 %) [CAS No. 67-64-1]	Test passed
Methylethylketone (MEK) [CAS No. 78-93-3]	Test passed
Gasoline [CAS No. 64742-49-0]	Test passed
Diesel [CAS No. 68476-34-6]	Test passed
IRM 901	Test passed
IRM 902	Test passed
IRM 903	Test passed

WMTB-AL (29X8) CUS - Aluminum label



0830807

<https://www.phoenixcontact.com/us/products/0830807>

Testing in a condensation changing climate in the presence of sulfur dioxide

Specification	EN ISO 22479:2022-06
Result	Test passed
Procedure	Method B
Cycles	2

Salt spray test

Specification	DIN EN IEC 60068-2-11 (VDE 0468-2-11):2022-10
Result	Test passed
Test duration	96 h

Standards and regulations

Wipe resistance	DIN EN 61010-1 (VDE 0411-1)
-----------------	-----------------------------

Mounting

Mounting type	Assembly with cable ties
---------------	--------------------------

WMTB-AL (29X8) CUS - Aluminum label



0830807

<https://www.phoenixcontact.com/us/products/0830807>

Classifications

ECLASS

ECLASS-13.0	27281102
ECLASS-15.0	27281102

ETIM

ETIM 10.0	EC001530
-----------	----------

UNSPSC

UNSPSC 21.0	39131500
-------------	----------

WMTB-AL (29X8) CUS - Aluminum label



0830807

<https://www.phoenixcontact.com/us/products/0830807>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com