

# UM6M-TM (8X12) - Marker for terminal blocks



0830939

<https://www.phoenixcontact.com/us/products/0830939>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Marker for terminal blocks, Strip, white (RAL 9010), unmarked, can be labeled with: BLUEMARK E.CARD, BLUEMARK ID COLOR, BLUEMARK ID, BLUEMARK CLED, THERMOMARK PRIME 2.0, THERMOMARK PRIME, THERMOMARK CARD 2.0, THERMOMARK CARD, TOPMARK NEO, TOPMARK LASER, mounting type: latching, Number of individual labels: 14, text field height: 12 mm, text field width: 8 mm



## Your advantages

- The markers, which are supplied in uniform strips, can be printed onto quickly and easily using the BLUEMARK printing systems
- The UM6M-TM ... UM labeling range includes terminal markers for ABB terminal blocks
- The multi-section marking strips are easy to fit and can be easily separated if required
- The markers support multi-line labeling

## Commercial data

Item number	0830939
Packing unit	10 pc
Minimum order quantity	10 pc
Sales key	BG08
Product key	BGE21C
GTIN	4046356910750
Weight per piece (including packing)	1.99 g
Weight per piece (excluding packing)	1.99 g
Customs tariff number	39269097
Country of origin	PL

# UM6M-TM (8X12) - Marker for terminal blocks



0830939

<https://www.phoenixcontact.com/us/products/0830939>

## Technical data

### Product properties

Product type	Terminal marker
Area of application	ABB

### Marking

Number of individual labels	14
Number of individual labels per row	7
Number of marker strips	2
Slot type	high
Identification technology	UV LED technology

### Dimensions

Width	7.47 mm
Height	11.90 mm
Depth	2.50 mm

### Text field

Text field width	8 mm
Text field height	12 mm

### Material specifications

RoHS compliant	yes
Color	white (RAL 9010)
Flammability rating according to UL 94	V2
Base element material	PC
Components	free from silicone, halogen, and cadmium

### Environmental and real-life conditions

#### Ambient conditions

Ambient temperature (operation)	-40 °C ... 120 °C
Recommended ambient temperature (storage/transport)	23 °C
Recommended humidity (storage/transport)	50 %

#### Test for substances that would hinder coating with paint or varnish

Testing for paint wetting impairment substances (LABS-conformity)	VW PV 3.10.7:2005-02
Result	Test passed

#### UV resistance

Specification	ISO 4892-2:2013-03 (following)
Result	Test passed
Test duration	96 h

#### Wipe resistance of inscriptions

# UM6M-TM (8X12) - Marker for terminal blocks



0830939

<https://www.phoenixcontact.com/us/products/0830939>

Specification	IEC 61010-1:2010-06
	DIN EN 62208 (VDE 0660-511):2012-06 (in parts)
Isopropanol (99%) [67-63-0]	Test passed
n-Hexane [CAS No. 110-54-3]	Test passed
Water + Petroleum ether [CAS No. 64742-82-1]	Test passed

## Testing in a condensation changing climate in the presence of sulfur dioxide

Specification	DIN 50018:2013-05
Result	Test passed
Climate level	AHT 1.0 S
Cycles	2

## Salt spray test

Specification	DIN EN 60068-2-11:2000-02
Result	Test passed

## Mounting

Mounting type	latching
---------------	----------

# UM6M-TM (8X12) - Marker for terminal blocks



0830939

<https://www.phoenixcontact.com/us/products/0830939>

## Classifications

### ECLASS

ECLASS-13.0	27281101
ECLASS-15.0	27281101

### ETIM

ETIM 10.0	EC000761
-----------	----------

### UNSPSC

UNSPSC 21.0	39131500
-------------	----------

# UM6M-TM (8X12) - Marker for terminal blocks



0830939

<https://www.phoenixcontact.com/us/products/0830939>

## Environmental product compliance

### EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
-----------------------------------------	--------------------

### EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

### EF3.1 Climate Change

CO2e kg	0.009 kg CO2e
---------	---------------

Phoenix Contact 2026 © - all rights reserved  
<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)