

PMST (9X38) GN - Insert label



0830961

<https://www.phoenixcontact.com/us/products/0830961>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Insert label, green (RAL 6021), unmarked, mounting type: latching, Number of individual labels:
1



Your advantages

- The medium marking label is used in conjunction with insertable UCT-PMP ... labels in the CARRIER-PMP
- They are used to clearly identify devices and control cabinets
- They are secured in the CARRIER-PMP using rivets

Commercial data

| | |
|--------------------------------------|---------------|
| Item number | 0830961 |
| Packing unit | 100 pc |
| Minimum order quantity | 100 pc |
| Product key | BG261Z |
| GTIN | 4046356912341 |
| Weight per piece (including packing) | 0.537 g |
| Weight per piece (excluding packing) | 0.48 g |
| Country of origin | DE |

PMST (9X38) GN - Insert label



0830961

<https://www.phoenixcontact.com/us/products/0830961>

Technical data

Product properties

| | |
|---------------------|---|
| Product type | Plant marker |
| Area of application | Identification of flow substances according to DIN 2403 |

Marking

| | |
|-------------------------------------|---|
| Number of individual labels | 1 |
| Number of individual labels per row | 1 |

Dimensions

| | |
|--------|-------|
| Width | 9 mm |
| Length | 38 mm |

Material specifications

| | |
|--|------------------|
| Color | green (RAL 6021) |
| Material | PVC |
| Flammability rating according to UL 94 | V0 |
| Components | Silicone-free |

Environmental and real-life conditions

Ambient conditions

| | |
|---|--|
| Ambient temperature (operation) | -30 °C ... 80 °C |
| Recommended ambient temperature (storage/transport) | 10 °C |
| Recommended humidity (storage/transport) | 40 % ... 70 % (Storage in a dry and dark place in the original packaging is recommended) |

UV resistance

| | |
|---------------|--------------------------------|
| Specification | ISO 4892-2:2013-03 (following) |
| Result | Test passed |
| Test duration | 96 h |
| Procedure | Artificial irradiation. |

Standards and regulations

| | |
|-----------------|-----------------------------|
| Wipe resistance | DIN EN 61010-1 (VDE 0411-1) |
|-----------------|-----------------------------|

Mounting

| | |
|---------------|----------|
| Mounting type | latching |
|---------------|----------|

PMST (9X38) GN - Insert label



0830961

<https://www.phoenixcontact.com/us/products/0830961>

Classifications

ECLASS

ECLASS-13.0

27281104

ETIM

ETIM 9.0

EC001288

UNSPSC

UNSPSC 21.0

39131500

PMST (9X38) GN - Insert label



0830961

<https://www.phoenixcontact.com/us/products/0830961>

Environmental product compliance

EU RoHS

| | |
|---|--------------------|
| Fulfills EU RoHS substance requirements | Yes, No exemptions |
|---|--------------------|

EU REACH SVHC

| | |
|-------------------------------------|----------------------------|
| REACH candidate substance (CAS No.) | No substance above 0.1 wt% |
|-------------------------------------|----------------------------|

Phoenix Contact 2026 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com