

US-EMLP-HA (60X30) SR - Plastic label



0830991

<https://www.phoenixcontact.com/us/products/0830991>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Plastic label, Card, unmarked, can be labeled with: BLUEMARK ID COLOR, BLUEMARK ID, THERMOMARK PRIME, THERMOMARK CARD 2.0, THERMOMARK CARD, THERMOMARK PRIME 2.0, mounting type: adhesive, Number of individual labels: 4, text field height: 30 mm, text field width: 60 mm



Your advantages

- The markers, which are supplied as uniform cards, can be labeled quickly, easily, and cost-effectively using the THERMOMARK CARD
- The sheets provide space for including function texts
- The US-EMLP ... UniSheet labeling range includes self-adhesive device markers with good adhesive properties

Commercial data

Item number	0830991
Packing unit	10 pc
Minimum order quantity	10 pc
Sales key	BG09
Product key	BG2419
GTIN	4046356949613
Weight per piece (including packing)	19.1 g
Weight per piece (excluding packing)	17.24 g
Customs tariff number	39199080
Country of origin	DE

US-EMLP-HA (60X30) SR - Plastic label



0830991

<https://www.phoenixcontact.com/us/products/0830991>

Technical data

Product properties

Product type	Device marker
Product property	highly adhesive

Marking

Number of individual labels	4
Number of individual labels per row	1
Identification technology	Thermotransfer, UV-LED-Technologie

Dimensions

Width	59.70 mm
Height	29.80 mm
Depth	0.63 mm

Text field

Text field width	60 mm
Text field height	30 mm

Material specifications

Foil strength	500 µm
Adhesive strength	130 µm
Adhesive	Acrylic
Color	silver-colored
Material	PVC
Flammability rating according to UL 94	V0
Base element material	PVC
Components	Silicone-free

Environmental and real-life conditions

Ambient conditions

Ambient temperature (operation)	-30 °C ... 80 °C
Recommended ambient temperature (storage/transport)	20 °C
Recommended humidity (storage/transport)	50 % (Storage in a dry and dark place in the original packaging is recommended)

Test for substances that would hinder coating with paint or varnish

Testing for paint wetting impairment substances (LABS-conformity)	VDMA 24364-A1-L:2018-05
Result	Test passed

Test for substances that would hinder coating with paint or varnish

Testing for paint wetting impairment substances (LABS-conformity)	VW PV 3.10.7:2005-02
Result	Test passed

US-EMLP-HA (60X30) SR - Plastic label



0830991

<https://www.phoenixcontact.com/us/products/0830991>

Scratch resistance

Specification	EN ISO 1518-1:2023 (following)
Requirements	≥ 5 N
Result	Test passed

Tesafilm test

Specification	DIN EN ISO 2409:2020-12 (following)
Result	Test passed

UV resistance

Specification	DIN EN ISO 4892-2:2021-11 (following)
Result	Test passed
Test duration	96 h
Procedure	Artificial irradiation.

Wipe resistance of inscriptions

Specification	DIN EN 61010-1 (VDE 0411-01):2020-03 DIN EN 62208 (VDE 0660-511):2012-06 (in parts)
Isopropanol (99%) [67-63-0]	Test passed
n-Hexane [CAS No. 110-54-3]	Test passed
Water + Petroleum ether [CAS No. 64742-82-1]	Test passed
Sodium hydroxide 0.1 mol/l [CAS No. 1310-73-2]	Test passed
Ethanol (99 %) [CAS No. 64-17-5]	Test passed

Immersion in chemicals, oil & fuel

Specification	ISO 175:2010 (following)
Test duration	168 h
Sodium hydroxide 0.1 mol/l [CAS No. 1310-73-2]	Test passed
Saltwater (saturated 350 g/l) [CAS No. -]	Test passed
Ethanol (99 %) [CAS No. 64-17-5]	Test passed
IRM 901	Test passed
IRM 902	Test passed
IRM 903	Test passed

Testing in a condensation changing climate in the presence of sulfur dioxide

Specification	DIN EN ISO 22479:2022-08
Result	Test passed
Procedure	Method B
Cycles	2

Salt spray test

US-EMLP-HA (60X30) SR - Plastic label



0830991

<https://www.phoenixcontact.com/us/products/0830991>

Specification	DIN EN IEC 60068-2-11 (VDE 0468-2-11):2022-10
Result	Test passed
Test duration	96 h

Standards and regulations

Wipe resistance	DIN EN 61010-1 (VDE 0411-1)
-----------------	-----------------------------

Mounting

Mounting type	adhesive
---------------	----------

US-EMLP-HA (60X30) SR - Plastic label



0830991

<https://www.phoenixcontact.com/us/products/0830991>

Classifications

ECLASS

ECLASS-13.0	27281103
ECLASS-15.0	27281103

ETIM

ETIM 10.0	EC001288
-----------	----------

UNSPSC

UNSPSC 21.0	39131500
-------------	----------

US-EMLP-HA (60X30) SR - Plastic label



0830991

<https://www.phoenixcontact.com/us/products/0830991>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

EF3.1 Climate Change

CO2e kg	0.346 kg CO2e
---------	---------------

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com