

# UC-PMP (90X38) BU CUS - Insert label




0831051

<https://www.phoenixcontact.com/us/products/0831051>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Insert label, Sheet, blue (RAL 5015), labeled according to customer specifications, mounting type: snapped into marker carrier



## Your advantages

- The UC-PMP ... plant identification family includes markers that can be mounted in existing CARRIER...-PMP... marker carriers
- The wide temperature range means that the labels can be used in control cabinets as well as the field
- The sheets provide space for including function texts
- The format automatically ensures printing with a high degree of positioning accuracy
- Marking service: Phoenix Contact can custom-mark all UniCard markers according to your specifications

## Commercial data

Item number	0831051
Packing unit	10 pc
Minimum order quantity	1 pc
Note	Made to order (non-returnable)
Product key	BG8157
GTIN	4046356940825
Weight per piece (including packing)	99.99 g
Weight per piece (excluding packing)	99.99 g
Country of origin	PL

## Technical data

### Product properties

Product type	Plant marker
--------------	--------------

### Marking

Identification technology	UV LED technology
---------------------------	-------------------

### Dimensions

Width	90.00 mm
Height	38.00 mm
Depth	1.15 mm

### Material specifications

RoHS compliant	yes
Color	blue (RAL 5015)
Flammability rating according to UL 94	V2
Base element material	PA
Temperature index of insulation material (DIN EN 60216-1 (VDE 0304-21))	120 °C
Fire protection for rail vehicles (DIN EN 45545-2) R22	HL 1 - HL 2
Fire protection for rail vehicles (DIN EN 45545-2) R23	HL 1 - HL 2
Fire protection for rail vehicles (DIN EN 45545-2) R24	HL 1 - HL 2
Components	free from silicone and halogen

### Environmental and real-life conditions

#### Ambient conditions

Ambient temperature (operation)	-40 °C ... 120 °C
Recommended ambient temperature (storage/transport)	23 °C
Recommended humidity (storage/transport)	50 %

#### Test for substances that would hinder coating with paint or varnish

Testing for paint wetting impairment substances (LABS-conformity)	VW PV 3.10.7:2005-02
Result	Test passed

#### UV resistance

Specification	ISO 4892-2:2013-03 (following)
Result	Test passed
Test duration	96 h

### Mounting

Mounting type	snapped into marker carrier
---------------	-----------------------------

# UC-PMP (90X38) BU CUS - Insert label



0831051

<https://www.phoenixcontact.com/us/products/0831051>

## Classifications

### ECLASS

ECLASS-13.0

27281104

### ETIM

ETIM 9.0

EC001288

### UNSPSC

UNSPSC 21.0

39131500

# UC-PMP (90X38) BU CUS - Insert label



0831051

<https://www.phoenixcontact.com/us/products/0831051>

## Environmental product compliance

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)