

LS-EML (180X180) BK-WH - Device marker




0831784

<https://www.phoenixcontact.com/us/products/0831784>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Device marker, Sheet, Mixed color, unmarked, can be labeled with: TOPMARK NEO, TOPMARK LASER, mounting type: adhesive, Number of individual labels: 1, text field height: 180 mm, text field width: 180 mm



Your advantages

- Laser foil, for custom label design
- Suitable for large markings of up to 180 x 180 mm
- The user can customize the desired size and form of the labels using the laser marker
- Stick-on device marking

Commercial data

| | |
|--------------------------------------|---------------|
| Item number | 0831784 |
| Packing unit | 10 pc |
| Minimum order quantity | 10 pc |
| Sales key | BG19 |
| Product key | BG241D |
| GTIN | 4046356927154 |
| Weight per piece (including packing) | 9.84 g |
| Weight per piece (excluding packing) | 7.44 g |
| Customs tariff number | 39199080 |
| Country of origin | DE |

LS-EML (180X180) BK-WH - Device marker



0831784

<https://www.phoenixcontact.com/us/products/0831784>

Technical data

Product properties

| | |
|--------------|---------------|
| Product type | Device marker |
|--------------|---------------|

Marking

| | |
|-----------------------------|----------------------|
| Number of individual labels | 1 |
| Identification technology | Direct laser marking |

Dimensions

| | |
|--------|--------|
| Width | 180 mm |
| Length | 180 mm |

Text field

| | |
|-------------------|--------|
| Text field width | 180 mm |
| Text field height | 180 mm |

Material specifications

| | |
|-------------------|--|
| Foil strength | 55 µm |
| Adhesive strength | 28 µm |
| Adhesive | Acrylic |
| Color | multicolored (RAL -) black (RAL 9005) white (RAL 9010) |
| Material | Polyacrylate |
| Components | free from silicone and halogen |

Environmental and real-life conditions

Ambient conditions

| | |
|---|--|
| Ambient temperature (operation) | -40 °C ... 200 °C |
| Recommended ambient temperature (storage/transport) | 15 °C |
| Recommended humidity (storage/transport) | 40 % ... 60 % (Storage in a dry and dark place in the original packaging is recommended) |

Test for substances that would hinder coating with paint or varnish

| | |
|---|----------------------|
| Testing for paint wetting impairment substances (LABS-conformity) | VW PV 3.10.7:2005-02 |
| Result | Test passed |

Test for substances that would hinder coating with paint or varnish

| | |
|---|--------------------|
| Testing for paint wetting impairment substances (LABS-conformity) | VDMA 24364:2018-05 |
| Result | Test passed |

Tesafilm test

| | |
|---------------|----------------------------------|
| Specification | DIN EN ISO 2409:2013 (following) |
|---------------|----------------------------------|

LS-EML (180X180) BK-WH - Device marker



0831784

<https://www.phoenixcontact.com/us/products/0831784>

| | |
|--------|-------------|
| Result | Test passed |
|--------|-------------|

UV resistance

| | |
|---------------|--------------------------------|
| Specification | ISO 4892-2:2013-03 (following) |
| Result | Test passed |
| Test duration | 96 h |
| Procedure | Artificial irradiation. |

Temperature storage

| | |
|-------------------------|-----------------------|
| Specification | IEC 60068-2-2:2007-07 |
| Result | Test passed |
| Procedure | Test Bb |
| Duration | 168 h |
| Temperature for testing | 200 °C |

Temperature resistance

| | |
|------------------------|---------------------------------|
| Specification | ANSI/UL 969-2018:03 (following) |
| Test duration | 240 h |
| Rating 150 °C (180 °C) | Test passed |

Wipe resistance of inscriptions

| | |
|---|---|
| Specification | DIN EN 61010-1 (VDE 0411-1):2011-07 DIN EN 62208 (VDE 0660-511):2012-06 (in parts) |
| Isopropanol (99%) [67-63-0] | Test passed |
| n-Hexane [CAS No. 110-54-3] | Test passed |
| Water + Petroleum ether [CAS No. 64742-82-1] | Test passed |
| Sodium hydroxide 0.1 mol/l [CAS No. 1310-73-2] | Test passed |
| Ethanol (99 %) [CAS No. 64-17-5] | Test passed |
| Acetone (99 %) [CAS No. 67-64-1] | Test passed |

Immersion in chemicals, oil & fuel

| | |
|---|--------------------------|
| Specification | ISO 175:2010 (following) |
| Test duration | 168 h |
| Saltwater (saturated 350 g/l) [CAS No. -] | Test passed |
| IRM 901 | Test passed |
| IRM 902 | Test passed |
| IRM 903 | Test passed |

Testing in a condensation changing climate in the presence of sulfur dioxide

| | |
|---------------|-------------------|
| Specification | DIN 50018:2013-05 |
| Result | Test passed |
| Climate level | AHT 1.0 S |

LS-EML (180X180) BK-WH - Device marker



0831784

<https://www.phoenixcontact.com/us/products/0831784>

| | |
|--------|---|
| Cycles | 2 |
|--------|---|

Salt spray test

| | |
|---------------|---------------------------|
| Specification | DIN EN 60068-2-11:2000-02 |
| Result | Test passed |
| Test duration | 96 h |

Standards and regulations

| | |
|-----------------|-----------------------------|
| Wipe resistance | DIN EN 61010-1 (VDE 0411-1) |
|-----------------|-----------------------------|

Mounting

| | |
|---------------|----------|
| Mounting type | adhesive |
|---------------|----------|

LS-EML (180X180) BK-WH - Device marker



0831784

<https://www.phoenixcontact.com/us/products/0831784>

Classifications

ECLASS

ECLASS-13.0

27281103

ETIM

ETIM 9.0

EC001288

UNSPSC

UNSPSC 21.0

39131500

LS-EML (180X180) BK-WH - Device marker



0831784

<https://www.phoenixcontact.com/us/products/0831784>

Environmental product compliance

EU RoHS

| | |
|---|--------------------|
| Fulfills EU RoHS substance requirements | Yes, No exemptions |
|---|--------------------|

EU REACH SVHC

| | |
|-------------------------------------|----------------------------|
| REACH candidate substance (CAS No.) | No substance above 0.1 wt% |
|-------------------------------------|----------------------------|

Phoenix Contact 2026 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com