

LS-EML (180X180) BK-WH CUS - Device marker



0832070

<https://www.phoenixcontact.com/us/products/0832070>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Device marker, Sheet, can be ordered: Piece, Mixed color, labeled according to customer specifications, mounting type: adhesive, Number of individual labels: 1, text field height: 180 mm, text field width: 180 mm



Your advantages

- Laser foil, for custom label design
- The user can customize the desired size and form of the labels using the laser marker

Commercial data

Item number	0832070
Packing unit	1 pc
Minimum order quantity	1 pc
Note	Made to order (non-returnable)
Product key	BG814D
GTIN	4046356931922
Weight per piece (including packing)	40 g
Weight per piece (excluding packing)	40 g
Country of origin	PL

LS-EML (180X180) BK-WH CUS - Device marker



0832070

<https://www.phoenixcontact.com/us/products/0832070>

Technical data

Product properties

Product type	Device marker
--------------	---------------

Marking

Number of individual labels	1
-----------------------------	---

Dimensions

Width	180 mm
Length	180 mm

Text field

Text field width	180 mm
Text field height	180 mm

Material specifications

Foil strength	60 µm
Adhesive strength	22 µm
Adhesive	Acrylic
Color	multicolored (RAL -)
	black (RAL 9005)
	white (RAL 9010)
Material	Polyacrylate
Base element material	Polyacrylate
Components	free from silicone and halogen

Environmental and real-life conditions

Ambient conditions

Ambient temperature (operation)	-40 °C ... 200 °C
Recommended ambient temperature (storage/transport)	15 °C
Recommended humidity (storage/transport)	40 % ... 60 % (Storage in a dry and dark place in the original packaging is recommended)

Test for substances that would hinder coating with paint or varnish

Testing for paint wetting impairment substances (LABS-conformity)	VW PV 3.10.7:2005-02
Result	Test passed

Test for substances that would hinder coating with paint or varnish

Testing for paint wetting impairment substances (LABS-conformity)	VDMA 24364:2018-05
Result	Test passed

Tesafilm test

Specification	DIN EN ISO 2409:2020-12 (following)
---------------	-------------------------------------

LS-EML (180X180) BK-WH CUS - Device marker



0832070

<https://www.phoenixcontact.com/us/products/0832070>

Result	Test passed
--------	-------------

UV resistance

Specification	DIN EN ISO 4892-2:2021-11 (following)
Result	Test passed
Test duration	96 h
Procedure	Artificial irradiation.

Temperature storage

Specification	IEC 60068-2-2:2007-07
Result	Test passed
Procedure	Test Bb
Duration	168 h
Temperature for testing	200 °C

Temperature resistance

Specification	ANSI/UL 969-2018:03 (following)
Test duration	240 h
Rating 150 °C (180 °C)	Test passed

Wipe resistance of inscriptions

Specification	DIN EN 61010-1 (VDE 0411-1):2011-07 DIN EN 62208 (VDE 0660-511):2012-06 (in parts)
Isopropanol (99%) [67-63-0]	Test passed
n-Hexane [CAS No. 110-54-3]	Test passed
Water + Petroleum ether [CAS No. 64742-82-1]	Test passed
Sodium hydroxide 0.1 mol/l [CAS No. 1310-73-2]	Test passed
Ethanol (99 %) [CAS No. 64-17-5]	Test passed
Acetone (99 %) [CAS No. 67-64-1]	Test passed

Immersion in chemicals, oil & fuel

Specification	ISO 175:2010 (following)
Test duration	168 h
Saltwater (saturated 350 g/l) [CAS No. -]	Test passed
IRM 901	Test passed
IRM 902	Test passed
IRM 903	Test passed

Testing in a condensation changing climate in the presence of sulfur dioxide

Specification	DIN EN ISO 22479:2022-08
Result	Test passed
Procedure	Method B

LS-EML (180X180) BK-WH CUS - Device marker



0832070

<https://www.phoenixcontact.com/us/products/0832070>

Cycles	2
--------	---

Salt spray test

Specification	DIN EN IEC 60068-2-11 (VDE 0468-2-11):2022-10
Result	Test passed
Test duration	96 h

Standards and regulations

Wipe resistance	DIN EN 61010-1 (VDE 0411-1)
-----------------	-----------------------------

Mounting

Mounting type	adhesive
---------------	----------

LS-EML (180X180) BK-WH CUS - Device marker



0832070

<https://www.phoenixcontact.com/us/products/0832070>

Classifications

ECLASS

ECLASS-15.0	27281103
ECLASS-13.0	27281103

ETIM

ETIM 10.0	EC001288
-----------	----------

UNSPSC

UNSPSC 21.0	39131500
-------------	----------

LS-EML (180X180) BK-WH CUS - Device marker



0832070

<https://www.phoenixcontact.com/us/products/0832070>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com