

WMS-2 HF 38,1 (60X60)RL CUS - Shrink sleeve



0833240

<https://www.phoenixcontact.com/us/products/0833240>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Shrink sleeve, white (RAL 9010), cable diameter range: 19.1 ... 38.1 mm: user-defined, Cut, mounting type: slide-on

Your advantages

- The hoses are preassembled for optimal use of the material
- WMS ... shrink sleeves provide permanent and captive conductor and cable marking
- The sleeves remain flexible after shrinking

Commercial data

Item number	0833240
Packing unit	1 pc
Minimum order quantity	1 pc
Note	Made to order (non-returnable)
Product key	BG8126
GTIN	4055626045078
Weight per piece (including packing)	8.8 g
Weight per piece (excluding packing)	8.8 g
Country of origin	PL

WMS-2 HF 38,1 (60X60)RL CUS - Shrink sleeve



0833240

<https://www.phoenixcontact.com/us/products/0833240>

Technical data

Product properties

Product type	Shrink sleeve
Area of application	Railway industry

Marking

Printing	user-defined
----------	--------------

Dimensions

Width	60 mm
Length	60 mm

Material specifications

RoHS compliant	yes
Color	white (RAL 9010)
Material	Polyolefine
Base element material	polyolefine
Shrink rate	2:1
Fire protection for rail vehicles (DIN EN 45545-2) R22	HL 1 - HL 3
Fire protection for rail vehicles (DIN EN 45545-2) R23	HL 1 - HL 3
Fire protection for rail vehicles (DIN EN 45545-2) R24	HL 1 - HL 3
Components	halogen-free

Cable/line

External cable diameter	19.1 mm ... 38.1 mm
-------------------------	---------------------

Environmental and real-life conditions

Ambient conditions

Recommended ambient temperature (storage/transport)	23 °C
Recommended humidity (storage/transport)	50 %

Test for substances that would hinder coating with paint or varnish

Testing for paint wetting impairment substances (LABS-conformity)	VW PV 3.10.7:2005-02
Result	Test passed

UV resistance

Specification	ISO 4892-2:2013-03 (following)
Result	Test passed
Test duration	96 h
Procedure	Artificial irradiation.

Standards and regulations

Wipe resistance	DIN EN 61010-1 (VDE 0411-1)
-----------------	-----------------------------

WMS-2 HF 38,1 (60X60)RL CUS - Shrink sleeve



0833240

<https://www.phoenixcontact.com/us/products/0833240>

Mounting

Mounting type	slide-on
---------------	----------

WMS-2 HF 38,1 (60X60)RL CUS - Shrink sleeve



0833240

<https://www.phoenixcontact.com/us/products/0833240>

Classifications

ECLASS

ECLASS-13.0

27281102

ETIM

ETIM 9.0

EC001530

UNSPSC

UNSPSC 21.0

39131500

WMS-2 HF 38,1 (60X60)RL CUS - Shrink sleeve



0833240

<https://www.phoenixcontact.com/us/products/0833240>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com