NS 35/ 7,5 BLK PERF 2000MM VPE 10 - DIN rail perforated

0843104

https://www.phoenixcontact.com/us/products/0843104

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



DIN rail perforated, Pack of 10 (20 m), acc. to EN 60715, material: Steel, uncoated, Standard profile, color: white aluminum

Commercial data

Item number	0843104
Packing unit	10 m
Minimum order quantity	20 m
Sales key	BE72
Product key	BE7238
GTIN	4046356949057
Weight per piece (including packing)	675 g
Weight per piece (excluding packing)	675 g
Customs tariff number	72166190
Country of origin	DE

NS 35/ 7,5 BLK PERF 2000MM VPE 10 - DIN rail perforated

0843104


https://www.phoenixcontact.com/us/products/0843104

Technical data

Product properties

Product type	DIN rail

Dimensions

Dimensional drawing	
Width	35 mm
Hole width	15 mm
Hole height	6.2 mm
Depth	7.5 mm
Length	2000 mm
Drill hole spacing	25 mm

Material specifications

Color	white aluminium (RAL 9006)
Material	Steel
Coating	uncoated

Standards and regulations

Tests	acc. to EN 60715

Electrical tests

Short-time withstand current

Equivalent E-Cu cross-section	16 mm²
Short-time current resistance 1s	1.92 kA


NS 35/ 7,5 BLK PERF 2000MM VPE 10 - DIN rail perforated

0843104

https://www.phoenixcontact.com/us/products/0843104

Drawings

Dimensional drawing



NS 35/ 7,5 BLK PERF 2000MM VPE 10 - DIN rail perforated

0843104

https://www.phoenixcontact.com/us/products/0843104

Classifications

ECLASS

ECLASS-13.0	27400602
ECLASS-15.0	27400602

ETIM

ETIM 10.0	EC001285

UNSPSC

UNSPSC 21.0	39121700

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions

China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%

EF3.1 Climate Change

CO2e kg	1.706 kg CO2e

Phoenix Contact 2026 © - all rights reserved
https://www.phoenixcontact.com

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com