

# TML (101X9,5)R P8 TR CUS - Marker strip



0852161

<https://www.phoenixcontact.com/us/products/0852161>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Marker strip, Roll, can be ordered: by line, labeled according to customer specifications, can be labeled with: THERMOMARK E.300 (D)/600 (D), THERMOMARK ROLL 2.0, THERMOMARK ROLL, THERMOMARK ROLL X1, THERMOMARK ROLLMASTER 300/600, THERMOMARK X1.2, mounting type: adhesive, for terminal block width: 8 mm, Number of individual labels: 1, text field height: 9.5 mm, text field width: 101 mm

## Your advantages

- The self-adhesive marker strips from the SK marking range mark products without a marker groove, ideal for marking COMBICON connectors
- The TML labeling range offers the option of subsequent labeling of zack marker strip and flat zack marker strip materials using a marking foil
- Labeling service: Phoenix Contact can custom-label all TML ... markers in accordance with your requirements

## Commercial data

Item number	0852161
Packing unit	1 pc
Minimum order quantity	1 pc
Note	Made to order (non-returnable)
Product key	BG8111
GTIN	4046356355360
Weight per piece (including packing)	1.99 g
Weight per piece (excluding packing)	1.99 g
Country of origin	PL

0852161

<https://www.phoenixcontact.com/us/products/0852161>

## Technical data

### Product properties

Product type	Terminal marker
Pitch	8 mm

### Marking

Number of individual labels	1
Number of individual labels per row	1
Slot type	flat
Identification technology	Thermotransfer

### Dimensions

Width	101.00 mm
Height	9.50 mm
Depth	0.05 mm
Pitch	8 mm
Length	101 mm

### Text field

Text field width	101 mm
Text field height	9.5 mm

### Material specifications

Color	transparent
Material	Polyester
Base element material	Polyester
Components	Silicone-free

### Environmental and real-life conditions

#### Ambient conditions

Ambient temperature (operation)	-40 °C ... 150 °C
Recommended ambient temperature (storage/transport)	23 °C
Recommended humidity (storage/transport)	50 % (Storage in a dry and dark place in the original packaging is recommended)

#### UV resistance

Specification	DIN EN ISO 4892-2:2021-11 (following)
---------------	---------------------------------------

#### Wipe resistance of inscriptions

Specification	DIN EN 61010-1 (VDE 0411-01):2020-03
	DIN EN 62208 (VDE 0660-511):2012-06 (in parts)

### Standards and regulations

Wipe resistance	DIN EN 61010-1 (VDE 0411-1)
-----------------	-----------------------------

# TML (101X9,5)R P8 TR CUS - Marker strip



0852161

<https://www.phoenixcontact.com/us/products/0852161>

## Mounting

Mounting type	adhesive
---------------	----------

# TML (101X9,5)R P8 TR CUS - Marker strip



0852161

<https://www.phoenixcontact.com/us/products/0852161>

## Drawings

Schematic diagram



- ① Horizontal
- ② Vertical

# TML (101X9,5)R P8 TR CUS - Marker strip



0852161

<https://www.phoenixcontact.com/us/products/0852161>

## Classifications

### ECLASS

ECLASS-13.0	27281101
ECLASS-15.0	27281101

### ETIM

ETIM 10.0	EC000761
-----------	----------

### UNSPSC

UNSPSC 21.0	39131500
-------------	----------

# TML (101X9,5)R P8 TR CUS - Marker strip



0852161

<https://www.phoenixcontact.com/us/products/0852161>

## Environmental product compliance

### EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

### EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)