

TML (EX9,5)R P5 TR CUS - Marker strip



0852170

<https://www.phoenixcontact.com/us/products/0852170>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Marker strip, Roll, can be ordered: by line, labeled according to customer specifications, can be labeled with: THERMOMARK E.300 (D)/600 (D), THERMOMARK ROLL 2.0, THERMOMARK ROLL, THERMOMARK ROLL X1, THERMOMARK ROLLMASTER 300/600, THERMOMARK X1.2, mounting type: adhesive, for terminal block width: 5 mm, Number of individual labels: 1, text field height: 9.5 mm, text field width: 40000 mm

The figure shows a version of the article

Your advantages

- The self-adhesive marker strips from the SK marking range mark products without a marker groove, ideal for marking COMBICON connectors
- The TML labeling range offers the option of subsequent labeling of zack marker strip and flat zack marker strip materials using a marking foil
- Labeling service: Phoenix Contact can custom-label all TML ... markers in accordance with your requirements

Commercial data

| | |
|--------------------------------------|--------------------------------|
| Item number | 0852170 |
| Packing unit | 1 pc |
| Minimum order quantity | 1 pc |
| Note | Made to order (non-returnable) |
| Product key | BG8111 |
| GTIN | 4046356355575 |
| Weight per piece (including packing) | 1.99 g |
| Weight per piece (excluding packing) | 1.99 g |
| Country of origin | PL |

TML (EX9,5)R P5 TR CUS - Marker strip



0852170

<https://www.phoenixcontact.com/us/products/0852170>

Technical data

Product properties

| | |
|--------------|-----------------|
| Product type | Terminal marker |
| Pitch | 5 mm |

Marking

| | |
|-------------------------------------|----------------|
| Number of individual labels | 1 |
| Number of individual labels per row | 1 |
| Slot type | flat |
| Identification technology | Thermotransfer |

Dimensions

| | |
|--------|----------|
| Width | 50.00 mm |
| Height | 9.50 mm |
| Depth | 0.05 mm |
| Pitch | 5 mm |
| Length | 40 m |

Text field

| | |
|-------------------|----------|
| Text field width | 40000 mm |
| Text field height | 9.5 mm |

Material specifications

| | |
|-----------------------|---------------|
| Color | transparent |
| Material | Polyester |
| Base element material | Polyester |
| Components | Silicone-free |

Environmental and real-life conditions

Ambient conditions

| | |
|---|---|
| Ambient temperature (operation) | -40 °C ... 150 °C |
| Recommended ambient temperature (storage/transport) | 23 °C |
| Recommended humidity (storage/transport) | 50 % (Storage in a dry and dark place in the original packaging is recommended) |

UV resistance

| | |
|---------------|---------------------------------------|
| Specification | DIN EN ISO 4892-2:2021-11 (following) |
|---------------|---------------------------------------|

Wipe resistance of inscriptions

| | |
|---------------|--|
| Specification | DIN EN 61010-1 (VDE 0411-01):2020-03 |
| | DIN EN 62208 (VDE 0660-511):2012-06 (in parts) |

Standards and regulations

| | |
|-----------------|-----------------------------|
| Wipe resistance | DIN EN 61010-1 (VDE 0411-1) |
|-----------------|-----------------------------|

TML (EX9,5)R P5 TR CUS - Marker strip



0852170

<https://www.phoenixcontact.com/us/products/0852170>

Mounting

Mounting type

adhesive

TML (EX9,5)R P5 TR CUS - Marker strip

0852170

<https://www.phoenixcontact.com/us/products/0852170>

Drawings

Schematic diagram



- ① Horizontal
- ② Vertical

TML (EX9,5)R P5 TR CUS - Marker strip



0852170

<https://www.phoenixcontact.com/us/products/0852170>

Classifications

ECLASS

| | |
|-------------|----------|
| ECLASS-13.0 | 27281101 |
| ECLASS-15.0 | 27281101 |

ETIM

| | |
|-----------|----------|
| ETIM 10.0 | EC000761 |
|-----------|----------|

UNSPSC

| | |
|-------------|----------|
| UNSPSC 21.0 | 39131500 |
|-------------|----------|

TML (EX9,5)R P5 TR CUS - Marker strip



0852170

<https://www.phoenixcontact.com/us/products/0852170>

Environmental product compliance

EU RoHS

| | |
|---|--------------------|
| Fulfills EU RoHS substance requirements | Yes, No exemptions |
|---|--------------------|

EU REACH SVHC

| | |
|-------------------------------------|----------------------------|
| REACH candidate substance (CAS No.) | No substance above 0.1 wt% |
|-------------------------------------|----------------------------|

Phoenix Contact 2026 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com