

# E S6 A 200X200X80 - Empty enclosure

0899007

<https://www.phoenixcontact.com/us/products/0899007>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Empty enclosure, material: Stainless steel, 316L/1.4404, surface resistance: brushed, silver-colored, 200 mm x 200 mm x 80 mm, type of locking: Screw-on cover, scope of supply - ATD: Mounting panel, Fixing angle with mounting screws, M12 grounding bolts, affixed externally, Installation notes, Mounting panel

## Your advantages

- Innovative product range of high-quality stainless steel housings as the basis for individual terminal boxes
- Reduced assembly and approval effort thanks to ready-equipped terminal boxes
- Flange plates possible on four sides of the housing, including seal protection
- Housing adjustments using threads, bore holes, and rectangular cutouts with consideration given to normative specifications

## Commercial data

Item number	0899007
Packing unit	1 pc
Minimum order quantity	1 pc
Note	Made to order (non-returnable)
Sales key	BH91
Product key	BH9112
GTIN	4046356927659
Weight per piece (including packing)	2.373 kg
Weight per piece (excluding packing)	2.373 kg
Customs tariff number	94032080
Country of origin	DE

# E S6 A 200X200X80 - Empty enclosure

0899007

<https://www.phoenixcontact.com/us/products/0899007>

## Technical data

### Product properties

Product type	Terminal box
Scope of supply	Mounting panel
	Fixing angle with mounting screws
	M12 grounding bolts, affixed externally
	Installation notes


### Insulation characteristics

Protection class	I
------------------	---

### Electrical properties

Maximum power dissipation	8 W (T6 up to 40 °C)
	5 W (T6 up to 55 °C)
	3 W (T6 up to 65 °C)
	11 W (T5 up to 40 °C)
	8 W (T5 up to 55 °C)
	6 W (T5 up to 65 °C)
	13 W (T4 up to 40 °C)
	6.3 W (T4 up to 55 °C)
8 W (T4 up to 65 °C)	

### Dimensions

Dimensional drawing	
Width	200 mm
Height	200 mm
Depth	80 mm
Clearance width, maximum DIN rail length	144 mm
Max. material thickness	1.5 mm

### Material specifications

Color	silver-colored
Material	Stainless steel, 316L/1.4404
Seal material	Silicon
Surface characteristics	brushed
Note	240 grain

# E S6 A 200X200X80 - Empty enclosure



0899007

<https://www.phoenixcontact.com/us/products/0899007>

## Mechanical properties

### General

Type of locking (GRP)

Screw-on cover Allen screws

## Environmental and real-life conditions

### Degree of protection (IP code)

Degree of protection

IP66

### Ambient conditions

Ambient temperature (operation)

-55 °C ... 135 °C

## Mounting

Assembly note

External fixing clips

# E S6 A 200X200X80 - Empty enclosure




0899007

<https://www.phoenixcontact.com/us/products/0899007>

## Drawings

Dimensional drawing



# E S6 A 200X200X80 - Empty enclosure

0899007

<https://www.phoenixcontact.com/us/products/0899007>



Schematic diagram



# E S6 A 200X200X80 - Empty enclosure



0899007

<https://www.phoenixcontact.com/us/products/0899007>

## Classifications

### ECLASS

ECLASS-13.0	27180101
ECLASS-15.0	27180101

### ETIM

ETIM 10.0	EC000261
-----------	----------

### UNSPSC

UNSPSC 21.0	31261500
-------------	----------

# E S6 A 200X200X80 - Empty enclosure



0899007

<https://www.phoenixcontact.com/us/products/0899007>

## Environmental product compliance

### EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

### China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

### EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved  
<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)