

LS-EMLP-AL (85,6X54) GN CUS - Device marker




0831897

<https://www.phoenixcontact.com/us/products/0831897>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Device marker, Aluminum label, can be ordered: Piece, green (RAL 6021), labeled according to customer specifications, mounting type: adhesive, Number of individual labels: 6, text field height: 54 mm, text field width: 85.6 mm



Your advantages

- Aluminum equipment marking for sticking on
- Identification made from metal, high strength in a lightweight design
- Increased durability due to the decoratively anodized surface

Commercial data

Item number	0831897
Packing unit	1 pc
Minimum order quantity	1 pc
Note	Made to order (non-returnable)
Product key	BG814D
GTIN	4046356930390
Weight per piece (including packing)	116.3 g
Weight per piece (excluding packing)	6.19 g
Country of origin	PL

Technical data

Product properties

Product type	Device marker
--------------	---------------

Marking

Number of individual labels	6
Identification technology	Direct laser marking

Dimensions

Width	85.00 mm
Height	53.70 mm
Depth	1.05 mm
Length	54 mm

Text field

Text field width	85.6 mm
Text field height	54 mm

Material specifications

Foil strength	800 µm
Adhesive strength	250 µm
Adhesive	Acrylic
Color	green (RAL 6021)
Material	Aluminum
Base element material	Aluminum
Components	free from silicone, halogen, and cadmium

Environmental and real-life conditions

Ambient conditions

Ambient temperature (operation)	-20 °C ... 125 °C
Recommended ambient temperature (storage/transport)	23 °C
Recommended humidity (storage/transport)	50 % (Storage in a dry and dark place in the original packaging is recommended)

Test for substances that would hinder coating with paint or varnish

Testing for paint wetting impairment substances (LABS-conformity)	VW PV 3.10.7:2005-02
Result	Test passed

Test for substances that would hinder coating with paint or varnish

Testing for paint wetting impairment substances (LABS-conformity)	VDMA 24364:2018-05
Result	Test passed

Scratch resistance

Specification	EN ISO 1518-1:2023 (following)
Requirements	≥ 5 N
Result	Test passed

Tesa film test

Specification	DIN EN ISO 2409:2020-12 (following)
Result	Test passed

UV resistance

Specification	DIN EN ISO 4892-2:2021-11 (following)
Result	Test passed
Test duration	96 h
Procedure	Artificial irradiation.

Temperature resistance

Note	The information does not apply to the color fastness of the material.
Specification	ANSI/UL 969-2018:03 (following)
Test duration	240 h
Rating 125 °C (150 °C)	Test passed

Wipe resistance of inscriptions

Specification	DIN EN 61010-1 (VDE 0411-01):2020-03 DIN EN 62208 (VDE 0660-511):2012-06 (in parts)
Isopropanol (99%) [67-63-0]	Test passed
n-Hexane [CAS No. 110-54-3]	Test passed
Water + Petroleum ether [CAS No. 64742-82-1]	Test passed
Sodium hydroxide 0.1 mol/l [CAS No. 1310-73-2]	Test passed
Ethanol (99 %) [CAS No. 64-17-5]	Test passed
Acetone (99 %) [CAS No. 67-64-1]	Test passed

Immersion in chemicals, oil & fuel

Specification	ISO 175:2010 (following)
Test duration	168 h
Saltwater (saturated 350 g/l) [CAS No. -]	Test passed
Ethanol (99 %) [CAS No. 64-17-5]	Test passed
Acetone (99 %) [CAS No. 67-64-1]	Test passed
Methylethylketone (MEK) [CAS No. 78-93-3]	Test passed
Gasoline [CAS No. 64742-49-0]	Test passed

0831897

<https://www.phoenixcontact.com/us/products/0831897>

Diesel [CAS No. 68476-34-6]	Test passed
IRM 901	Test passed
IRM 902	Test passed
IRM 903	Test passed

Testing in a condensation changing climate in the presence of sulfur dioxide

Specification	EN ISO 22479:2022-06
Result	Test passed
Procedure	Method B
Cycles	2

Salt spray test

Specification	DIN EN IEC 60068-2-11 (VDE 0468-2-11):2022-10
Result	Test passed
Test duration	96 h

High pressure test

Specification	ISO 20653:2013-02
Result	Test passed
IP-Code	IP X9K

Standards and regulations

Wipe resistance	DIN EN 61010-1 (VDE 0411-1)
-----------------	-----------------------------

Mounting

Mounting type	adhesive
---------------	----------

0831897

<https://www.phoenixcontact.com/us/products/0831897>

Classifications

ECLASS

ECLASS-13.0	27281103
ECLASS-15.0	27281103

ETIM

ETIM 10.0	EC001288
-----------	----------

UNSPSC

UNSPSC 21.0	39131500
-------------	----------

LS-EMLP-AL (85,6X54) GN CUS - Device marker



0831897

<https://www.phoenixcontact.com/us/products/0831897>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements

Yes, No exemptions

EU REACH SVHC

REACH candidate substance (CAS No.)

No substance above 0.1 wt%

Phoenix Contact 2026 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com