

SAC-3P-M 8MS/20,0-PVC BK VA - Sensor/actuator cable



1002004

<https://www.phoenixcontact.com/us/products/1002004>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Sensor/actuator cable, 3-position, PVC, black RAL 9005, Plug straight M8, coding: A, on free cable end, cable length: 20 m, High-grade steel knurl

As shown in the illustration but with a black handle

Your advantages

- Easy and safe: 100 % electrically tested plug-in components

Commercial data

Item number	1002004
Packing unit	1 pc
Minimum order quantity	25 pc
Note	Made to order (non-returnable)
Product key	AF1BBA
GTIN	4055626463629
Weight per piece (including packing)	500.2 g
Weight per piece (excluding packing)	500.2 g
Country of origin	PL

SAC-3P-M 8MS/20,0-PVC BK VA - Sensor/actuator cable



1002004

<https://www.phoenixcontact.com/us/products/1002004>

Technical data

Product properties

Product type	Sensor/actuator cable
Application	Standard
Number of positions	3
No. of cable outlets	1
Shielded	no
Coding	A

Material specifications

Material of grip body	TPU, hardly inflammable, self-extinguishing
Contact material	CuSn
Contact surface material	Ni/Au
Contact carrier material	TPU GF
Material for screw connection	Stainless steel

Electrical properties

Insulation resistance	$\geq 100 \text{ M}\Omega$
Nominal voltage U_N	48 V AC
	60 V DC
Nominal current I_N	4 A

Mechanical properties

Mechanical data

Insertion/withdrawal cycles	≥ 100
-----------------------------	------------

Signaling

Status display	no
Status display present	no

Connector

Connection 1

Type	Plug straight M8
Number of positions	3
Coding type	A

Connection 2

Type	free cable end
------	----------------

Cable/line

Cable length	20 m
--------------	------


PVC black [PVC]

SAC-3P-M 8MS/20,0-PVC BK VA - Sensor/actuator cable



1002004

<https://www.phoenixcontact.com/us/products/1002004>

Dimensional drawing	
Cable weight	29 kg/km
Number of positions	3
Shielded	no
Cable type	PVC black [PVC]
Conductor structure signal line	14x 0.15 mm
AWG signal line	24
Conductor cross-section	3x 0.25 mm ² (Signal line)
Wire diameter incl. insulation	1.17 mm ±0.05 mm
External cable diameter	4.20 mm ±0.15 mm
Outer sheath, material	PVC
External sheath, color	black RAL 9005
Conductor material	Bare Cu litz wires
Material wire insulation	PVC
Single wire, color	brown, blue, black
Thickness, insulation	≥ 0.23 mm (Core insulation)
Thickness, outer sheath	≥ 0.76 mm
Overall twist	3 wires, twisted
Max. conductor resistance	max. 79 Ω/km (at 20 °C)
Insulation resistance	≥ 100 MΩ*km (at 20 °C)
Nominal voltage, cable	≥ 300 V
Test voltage	≤ 3000 V
Smallest bending radius, fixed installation	13 mm
Flame resistance	As per UL-Style 2464
Resistance to oil	EN 60811-2-1
Ambient temperature (operation)	-25 °C ... 80 °C (cable, fixed installation) -10 °C ... 80 °C (Cable, flexible installation)

Environmental and real-life conditions

Ambient conditions

Degree of protection	IP65 IP67
Ambient temperature (operation) (male connector/female connector)	-25 °C ... 90 °C (Plug / socket)

Standards and regulations

SAC-3P-M 8MS/20,0-PVC BK VA - Sensor/actuator cable



1002004

<https://www.phoenixcontact.com/us/products/1002004>

M8

Standard designation	M8 connector
Standards/specifications	IEC 61076-2-104

SAC-3P-M 8MS/20,0-PVC BK VA - Sensor/actuator cable

1002004

<https://www.phoenixcontact.com/us/products/1002004>

Drawings

Dimensional drawing



M8 x 1 male plug, straight version

Schematic diagram



Pin assignment M8 plug, 3-pos., view male side


SAC-3P-M 8MS/20,0-PVC BK VA - Sensor/actuator cable



1002004

<https://www.phoenixcontact.com/us/products/1002004>

Circuit diagram



Contact assignment of the M8 plug

SAC-3P-M 8MS/20,0-PVC BK VA - Sensor/actuator cable




1002004

<https://www.phoenixcontact.com/us/products/1002004>

Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/1002004>

 UL Listed Approval ID: FILE E 221474				
	Nominal voltage U_N	Nominal current I_N	Cross section AWG	Cross section mm^2
keine				
	60 V	4 A	-	-

 cUL Listed Approval ID: FILE E 221474				
	Nominal voltage U_N	Nominal current I_N	Cross section AWG	Cross section mm^2
keine				
	60 V	4 A	-	-

SAC-3P-M 8MS/20,0-PVC BK VA - Sensor/actuator cable



1002004

<https://www.phoenixcontact.com/us/products/1002004>

Classifications

ECLASS

ECLASS-13.0	27060311
ECLASS-15.0	27060311

ETIM

ETIM 10.0	EC001855
-----------	----------

UNSPSC

UNSPSC 21.0	26121600
-------------	----------

SAC-3P-M 8MS/20,0-PVC BK VA - Sensor/actuator cable



1002004

<https://www.phoenixcontact.com/us/products/1002004>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com