

# CSD-SL 300 WH 8X8 - Signal light



1002733

<https://www.phoenixcontact.com/us/products/1002733>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Signal light, 24 V DC, IALA white, optimum, emission angle (vertical/Horizontal): 8 °/8 °, diameter: 272 mm, degree of protection: IP65/IP67, Communication interface

## Product description

The signal lights for maritime use can be used for the reliable and energy-efficient operation of light-signal systems, such as locks. Only components that conform to the industry standard are used for the monitoring functions. The signal light 300 is available in various light colors in accordance with major standards (e.g. IALA recommendation E200-1 and CIE 1931). The fieldbus communication provides the user with a large amount of diagnostic and status information.

## Your advantages

- Developed in accordance with EN 12966-1, IALA recommendation E200-1, and CIE 1931
- Failsafe function
- 400 m connection to the control unit via fieldbus
- Diagnostic capability
- High light and color intensity
- Application-specific programming supported
- Particularly economical thanks to energy-efficient LED technology and an LED service life of at least 50000 h
- Durable and energy-saving LED technology
- Fieldbus communication
- Emission angle: 8° x 8°

## Commercial data

Item number	1002733
Packing unit	1 pc
Minimum order quantity	1 pc
Product key	DRL122
GTIN	4055626465203
Weight per piece (including packing)	4,200 g
Weight per piece (excluding packing)	3,860 g
Country of origin	DE

# CSD-SL 300 WH 8X8 - Signal light



1002733

<https://www.phoenixcontact.com/us/products/1002733>

## Technical data

### Notes

#### Note on application

Note on application	Only for industrial use
---------------------	-------------------------

### Product properties

Product type	Signaling light
Application	Maritime navigation Transportation infrastructure
Design	Operating hours counter
Special properties	Communication interface
Diagnostics messages	LEDs; temperature, current, voltage, etc. yes Mains failure, communication failure Failsafe
Light color	IALA white, optimum

### Electrical properties

#### General

Inrush current	max. 36 A (μ-sec-pulse)
----------------	-------------------------

#### Supply: Module electronics

Connection method	M17 hybrid connectors with SPEEDCON locking system
Number of positions	8
Supply voltage	24 V DC (DC)
Current consumption	max. 2.51 A (white LEDs)
Power consumption	max. 70 W (white LEDs)

### Connection data

Connection method	M17 hybrid connectors with SPEEDCON locking system
-------------------	--

### Signaling

#### Light properties

Source of light type	LED
Number of LEDs	30 (in accordance with IALA recommendation E200-1 and CIE 1931)
Color temperature	5000 K ±1000 K
Color class	C2 (EN 12966)
Luminance	L3 (EN 12966)
Luminance ratio	R3 (EN 12966)
Phantom light class	5 (EN 12368)
Luminous intensity	175429 Cd
Can be dimmed	Yes, in 256 steps
Emission angle	8 °

# CSD-SL 300 WH 8X8 - Signal light



1002733

<https://www.phoenixcontact.com/us/products/1002733>

	8 °
--	-----

## Diagnostic messages

Diagnostics	LEDs; temperature, current, voltage, etc.
Message	yes

## Diagnostic messages

Diagnostics	Mains failure, communication failure
Message	Failsafe

## Dimensions

Depth	68 mm
Diameter	272 mm

## Material specifications

Color	black (RAL 9005)
Material	gray
Material	Aluminum die-cast in accordance with DIN EN 1706
	Glass

## Environmental and real-life conditions

### Ambient conditions

Ambient temperature (operation)	-25 °C ... 55 °C
Degree of protection	IP65/IP67 (When installed)
Air pressure (operation)	70 hPa ... 106 kPa (up to 3000 m above sea level)
Air pressure (storage/transport)	70 hPa ... 106 kPa (up to 3000 m above sea level)
Ambient temperature (storage/transport)	-25 °C ... 85 °C

## Mounting

Mounting type	Screw/snap-on assembly
Assembly note	Use of stainless steel fittings (corrosion-resistant)

# CSD-SL 300 WH 8X8 - Signal light



1002733

<https://www.phoenixcontact.com/us/products/1002733>

## Classifications

### ECLASS

ECLASS-13.0

27110201

### ETIM

ETIM 9.0

EC002750

### UNSPSC

UNSPSC 21.0

39111800

# CSD-SL 300 WH 8X8 - Signal light



1002733

<https://www.phoenixcontact.com/us/products/1002733>

## Environmental product compliance

### EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

### China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

### EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved  
<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)