

# CK1,6-ER-2,50ST OIC AG - Crimp contact



1004365

<https://www.phoenixcontact.com/us/products/1004365>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Crimp contact, series: HC-M-12, Pin, rolled, contact diameter: 1.6 mm, connection cross section: 1.5 mm<sup>2</sup> ... 2.5 mm<sup>2</sup>, AWG 16...14, contact material: Cu alloy

## Commercial data

Item number	1004365
Packing unit	100 pc
Minimum order quantity	100 pc
Sales key	BF65
Product key	AF7AIB
GTIN	4055626472553
Weight per piece (including packing)	0.36 g
Weight per piece (excluding packing)	0.36 g
Customs tariff number	85366990
Country of origin	TR

# CK1,6-ER-2,50ST OIC AG - Crimp contact



1004365

<https://www.phoenixcontact.com/us/products/1004365>

## Technical data

### Product properties

Product type	Crimp contact
Series	HC-M-12
	HC-M-EMV
	HC-D
	HC-DD
	VC-D
	HC-M-03/04
	HC-M-17
	HC-K
	HC-Q
	HC-COM
	HC-M-42
	HC-M-08-MBIT
Contact material type	rolled

### Connection data

#### Connection technology

Contact connection type	Pin
Connection method	Crimp connection


#### Conductor connection

Stripping length	4 mm
Connection cross section	1.5 mm <sup>2</sup> ... 2.5 mm <sup>2</sup>
Connection cross section AWG	16 ... 14

### Material specifications

Material Contact	Cu alloy (nickel-plated)
Material Contact surface	Ag

### Dimensions

Dimensional drawing	
Length [l]	24.5 mm
Diameter (Contact diameter)	1.6 mm

### Mechanical properties

#### Mechanical data

Insertion/withdrawal cycles	≥ 500
-----------------------------	-------

# CK1,6-ER-2,50ST OIC AG - Crimp contact



1004365

<https://www.phoenixcontact.com/us/products/1004365>

## Environmental and real-life conditions

### Ambient conditions

Ambient temperature (operation)
---------------------------------

-40 °C ... 125 °C
-------------------

# CK1,6-ER-2,50ST OIC AG - Crimp contact




1004365

<https://www.phoenixcontact.com/us/products/1004365>

## Drawings

Dimensional drawing



Dimensional drawing

# CK1,6-ER-2,50ST OIC AG - Crimp contact



1004365

<https://www.phoenixcontact.com/us/products/1004365>

## Classifications

### ECLASS

ECLASS-13.0	27440204
ECLASS-15.0	27440204

### ETIM

ETIM 10.0	EC000796
-----------	----------

### UNSPSC

UNSPSC 21.0	39121500
-------------	----------

# CK1,6-ER-2,50ST OIC AG - Crimp contact



1004365

<https://www.phoenixcontact.com/us/products/1004365>

## Environmental product compliance

### EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

### China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

### EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

### EF3.1 Climate Change

CO2e kg	0.039 kg CO2e
---------	---------------

Phoenix Contact 2026 © - all rights reserved  
<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)