

FL EPA 2 - Wireless module



1005955

<https://www.phoenixcontact.com/us/products/1005955>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Combined Ethernet wireless module with Bluetooth and Wi-Fi, internal antenna, Wi-Fi: AP and client, 2.4 and 5 GHz, Bluetooth: 2.1+EDR/4.0, PAN up to 7 connections, IP65, 9 ... 30 V DC, M12 connection, WEB, AT commands and mode button

Your advantages

- Combined wireless module for WLAN and Bluetooth
- Protocol-transparent communication on Layer 2
- Degree of protection IP65
- Integrated antenna

Commercial data

Item number	1005955
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	DN26
Product key	DNN2B1
GTIN	4055626476568
Weight per piece (including packing)	152.4 g
Weight per piece (excluding packing)	166 g
Customs tariff number	85176200
Country of origin	LT

Technical data

Notes

Note on application

Note on application	Only for industrial use
---------------------	-------------------------

Product properties

Product type	Wireless module
Application	Ethernet
Type	Stand-alone

Wireless card

Number	1
Assembly note	Permanently installed

Electrical properties

Maximum power dissipation for nominal condition	1.7 W
---	-------

Supply: Module electronics

Connection technology	M12 connector
Connection method	M12 connector, A-coded (male)
Supply voltage	24 V DC
Supply voltage range	9 V DC ... 30 V DC
Supply current	typ. 54 mA (at 24 V DC)
Current consumption	max. 190 mA (at 9 V DC)

Input data

Digital:

Number of inputs	1
------------------	---

Connection data

Power supply input

Connection method	M12 connector, A-coded (male)
pluggable	yes

Interfaces

Ethernet

Interface	Ethernet
Number	1
Connection method	M12 connector, D-coded (female)

Functions

Operating modes	Access point/client adapter for WLAN and Bluetooth
-----------------	--

FL EPA 2 - Wireless module



1005955

<https://www.phoenixcontact.com/us/products/1005955>

Configuration	Web interface, MODE button, AT commands (TCP/IP), SSC
Security	802.11i
	WPA PSK (preshared key)
	WPA2
	AES
	TKIP
	PIN
	Non-discoverable
Wireless licenses	Europe, USA, Canada, additional countries in the e-shop
	RED (Radio Equipment Directive)
	FCC 47 CFR part 15, subpart B
Country support	Belgium
	Bulgaria
	China
	Denmark
	Germany
	Estonia
	Finland
	France
	Greece
	Great Britain
	Ireland
	Iceland
	Italy
	Japan
	Canada
	Croatia
	Latvia
	Liechtenstein
	Lithuania
	Luxembourg
	Malta
	Netherlands
	Norway
	Austria
	Poland
	Portugal
Romania	
Sweden	
Switzerland	
Slovakia	
Slovenia	
Spain	
South Korea	

FL EPA 2 - Wireless module



1005955

<https://www.phoenixcontact.com/us/products/1005955>

	Thailand
	Czech Republic
	Hungary
	USA
	Cyprus (rep.)

10/100 Mbps Ethernet

Number of interfaces	1
Connection method	M12 connector, D-coded (female)
Note on the connection method	Auto negotiation and autocrossing
Transmission speed	10/100 Mbps
Transmission physics	Copper
Transmission length	100 m (per segment)

Wireless

Designation	Bluetooth / WLAN
Antenna connection method	(Internal)
Frequency range	2.402 GHz ... 2.48 GHz (Bluetooth) 2.4095 GHz ... 2.4645 GHz (WLAN) 5.17 GHz ... 5.25 GHz (WLAN-AP) 5.17 GHz ... 5.71 GHz (WLAN-Client)
Frequency band	2.4 GHz 5 GHz
Wireless standard	Bluetooth 2.1 + EDR WLAN IEEE 802.11 a b g n
Transmission power	max. 16 dBm (Bluetooth: 10 dBm)
Number of wireless interfaces	1 IEEE 802.11 a/b/g/n, Bluetooth 2.1+EDR, Bluetooth LE 4.0
Wireless modules that can be connected	7 (BT 2.1+EDR, NAP-Mode)
Profiles supported	PAN (NAP, PANU) GATT (central)

Dimensions

Width	67.8 mm
Height	92.7 mm
Depth	33.2 mm
Note on dimensions	Without M12 connections

Environmental and real-life conditions

Ambient conditions

Degree of protection	IP65
----------------------	------

FL EPA 2 - Wireless module



1005955

<https://www.phoenixcontact.com/us/products/1005955>

Ambient temperature (operation)	-40 °C ... 65 °C
Ambient temperature (storage/transport)	-40 °C ... 85 °C
Permissible humidity (operation)	5 % ... 93 % (non-condensing)
Permissible humidity (storage/transport)	non-condensing

EMC data

Electrostatic discharge

Standards/regulations	EN 61000-4-2
-----------------------	--------------

Electromagnetic HF field

Standards/regulations	EN 61000-4-3
-----------------------	--------------

Fast transients (burst)

Standards/regulations	EN 61000-4-4
-----------------------	--------------

Surge current load (surge)

Standards/regulations	EN 61000-4-5
-----------------------	--------------

Conducted interference

Standards/regulations	EN 61000-4-6
-----------------------	--------------

Emitted interference

Standards/regulations	EN 55022
-----------------------	----------

Mounting

Mounting type	Panel mounting
Assembly note	Internal antenna

FL EPA 2 - Wireless module



1005955

<https://www.phoenixcontact.com/us/products/1005955>


Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/1005955>

 **UL Listed**
Approval ID: E238705

 **cUL Listed**
Approval ID: E238705

 **cUL Listed**
Approval ID: E196811

 **UL Listed**
Approval ID: E196811

FL EPA 2 - Wireless module



1005955

<https://www.phoenixcontact.com/us/products/1005955>

Classifications

ECLASS

ECLASS-13.0	19170101
ECLASS-15.0	19170101

ETIM

ETIM 10.0	EC000515
-----------	----------

UNSPSC

UNSPSC 21.0	43201400
-------------	----------

FL EPA 2 - Wireless module



1005955

<https://www.phoenixcontact.com/us/products/1005955>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes
Exemption	6(c), 7(a), 7(c)-I

China RoHS

Environment friendly use period (EFUP)	EFUP-50
	An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.

EU REACH SVHC

REACH candidate substance (CAS No.)	Lead(CAS: 7439-92-1)
SCIP	4ae8c8ac-962c-4938-8b41-b7138bb0e907

EF3.1 Climate Change

CO2e kg	9.687 kg CO2e
---------	---------------

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com