

SAC-2P-M12MST/0,515-PUR PI - Power cable



1007664

<https://www.phoenixcontact.com/us/products/1007664>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Power cable, 2-position, PUR halogen-free, black-gray RAL 7021, Plug straight M12 SPEEDCON, coding: T, on free cable end, cable length: 0.515 m, Customer version

Commercial data

Item number	1007664
Packing unit	1 pc
Minimum order quantity	50 pc
Product key	AF1CCP
GTIN	4055626480046
Weight per piece (including packing)	58.7 g
Weight per piece (excluding packing)	52 g
Country of origin	DE

SAC-2P-M12MST/0,515-PUR PI - Power cable



1007664

<https://www.phoenixcontact.com/us/products/1007664>

Technical data

Product properties

Product type	Power cable
Application	Energy supply
Number of positions	2
No. of cable outlets	1
Shielded	no
Coding	T

Material specifications

Flammability rating according to UL 94	V2
Seal material	Silicon
Material of grip body	PP
Contact material	CuZn
Contact surface material	Ni/Au
Contact carrier material	TPU GF
Material for screw connection	Zinc die-cast, nickel-plated

Electrical properties

Nominal voltage U_N	24 V AC
	63 V DC
Nominal current I_N	3 A

Connector

Connection 1

Type	Plug straight M12 SPEEDCON
Locking type	SPEEDCON
Coding type	T (Power)

Connection 2

Type	free cable end
------	----------------

Cable/line

Cable length	0.515 m
--------------	---------

PUR halogen-free black [PUR]

Cable weight	57 kg/km
UL AWM Style	20233 / 10493 (80°C/300 V)
Number of positions	2
Cable type	PUR halogen-free black [PUR]
Conductor structure signal line	78x 0.15 mm
AWG signal line	16
Conductor cross-section	2x 1.5 mm ²

SAC-2P-M12MST/0,515-PUR PI - Power cable



1007664

<https://www.phoenixcontact.com/us/products/1007664>

Wire diameter incl. insulation	2.25 mm ±0.05 mm
External cable diameter	6.40 mm ±0.2 mm
Outer sheath, material	PUR
External sheath, color	black-gray RAL 7021
Conductor material	Bare Cu litz wires
Material wire insulation	PP
Single wire, color	brown, blue
Thickness, outer sheath	≥ 0.76 mm
Max. conductor resistance	≤ 14.5 Ω/km (at 20 °C)
Insulation resistance	≥ 1 GΩ*km (at 20 °C)
Nominal voltage, cable	≤ 300 V AC
Test voltage	≥ 3000 V AC (Spark test)
Minimum bending radius, fixed installation	5 x D
Minimum bending radius, flexible installation	10 x D
Smallest bending radius, fixed installation	32 mm
Smallest bending radius, movable installation	64 mm
Halogen-free	in accordance with DIN VDE 0472 part 815 in accordance with DIN EN 50267-2-1
Flame resistance	According to UL 758/1581 (Cable Flame) according to UL 758/1581 FT1 According to DIN EN 60332-1-2 (60 s)
Concentration of fumes	Degree of transmission < 60 %
Resistance to oil	According to DIN EN 60811-2-1, 168 h at 100°C
Other resistance	hydrolysis and microbe resistant Resistant to salt water Low adhesion abrasion-resistant
Special properties	flexible
Ambient temperature (operation)	-50 °C ... 80 °C (cable, fixed installation) -30 °C ... 80 °C (Cable, flexible installation)

Environmental and real-life conditions

Ambient conditions

Degree of protection	IP67
Ambient temperature (operation) (male connector/female connector)	-25 °C ... 85 °C (Plug / socket)

SAC-2P-M12MST/0,515-PUR PI - Power cable




1007664

<https://www.phoenixcontact.com/us/products/1007664>


Drawings

Dimensional drawing



Plug, M12 x 1, straight, shielded

Schematic diagram




Pin assignment for M12 plug, 4-pos., T-coded, view of plug side

SAC-2P-M12MST/0,515-PUR PI - Power cable



1007664

<https://www.phoenixcontact.com/us/products/1007664>



Base curve

SAC-2P-M12MST/0,515-PUR PI - Power cable



1007664

<https://www.phoenixcontact.com/us/products/1007664>

Classifications

ECLASS

ECLASS-13.0	27060327
ECLASS-15.0	27060327

SAC-2P-M12MST/0,515-PUR PI - Power cable



1007664

<https://www.phoenixcontact.com/us/products/1007664>

Environmental product compliance

China RoHS

Environment friendly use period (EFUP)	EFUP-50
	An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com