


FP 1,27/ 16-FWL-10/.../... - Preassembled IDC female connector



1010258

<https://www.phoenixcontact.com/us/products/1010258>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



The figure shows a 12-pos. version with 12 contacts

Assembled IDC female connector, rated current: 1.2 A, cable length: Free input (0.05 ... 0.95 m), Cable type: Flat cable, For preassembled samples, see the "Accessories" tab., product range: FR 1,27/...-Cabling

Your advantages

- Gold-plated contacts ensure transfer quality remains stable over the long term
- Compact, high-position board-to-board or wire-to-board connectors for space-saving device designs
- Can be ordered pre-assembled: IDC female connectors with flat-ribbon cable enable immediate use in the device

Commercial data

Item number	1010258
Packing unit	50 pc
Minimum order quantity	100 pc
Note	Made to order (non-returnable)
Sales key	AA24
Product key	AAXPAA
Customs tariff number	85444290
Country of origin	DE

FP 1,27/ 16-FWL-10/.../... - Preassembled IDC female connector



1010258

<https://www.phoenixcontact.com/us/products/1010258>

Technical data

Product properties

Product type	Assembled IDC female connector
Product family	FR 1,27/...-Cabling
Number of positions	16
Pitch	1.27 mm
Number of rows	2

Electrical properties

Properties

Nominal current I_N	1.2 A IEC 60512-5-2:2002-02 (at 20°C 50-pos.)
Contact resistance	10 mΩ
Test voltage	500 V AC IEC 60512-4-1:2003-05

Notes

Note on application	Please observe the application note on self-assembly in the download area.
Note regarding documentation	Current documents such as 3D models, products family drawings, data sheets or packaging drawings are available in the Download Center.
Notes on operation	The permissible voltage during operation depends on the application, taking into consideration the air clearances and creepage distances within the scope of insulation requirements in accordance with IEC 60664-1.

Dimensions

Pitch	1.27 mm
-------	---------

Application

Center offset	± 0.7 mm in longitudinal and transverse direction
Angular tolerance	± 4 ° in longitudinal direction
	± 2 ° in transverse direction

Mechanical tests

Insertion and withdrawal forces

Result	Test passed
No. of cycles	500
Insertion strength per pos. approx.	0.5 N
Withdraw strength per pos. approx.	0.5 N

Electrical tests

Thermal test | Test group C

FP 1,27/ 16-FWL-10/.../... - Preassembled IDC female connector



1010258

<https://www.phoenixcontact.com/us/products/1010258>

Specification	IEC 60512-5-2:2002-02
Tested number of positions	50

Insulation resistance

Specification	IEC 60512-3-1:2002-02
Insulation resistance, neighboring positions	≥ 10 GΩ

Environmental and real-life conditions

Durability test

Specification	IEC 60512-9-1:2010-03 (following)
Impulse withstand voltage at sea level	0.8 kV
Contact resistance R ₁	10 mΩ
Contact resistance R ₂	10 mΩ
Insertion/withdrawal cycles	500
Insulation resistance, neighboring positions	≥ 10 GΩ

Climatic test

Specification	IEC 60512-11-7:2003-05
Corrosive stress	Method 1, 10 days
Power-frequency withstand voltage	500 V AC

Vibration test

Specification	IEC 60068-2-6:2007-12
Frequency	10 - 2000 - 10 Hz
Sweep speed	1 octave/min
Amplitude	1.5 mm (10 Hz ... 60.1 Hz)
Acceleration	20g (60.1 Hz ... 2000 Hz)
Test duration per axis	2.5 h
Test directions	X-, Y- and Z-axis

Shocks

Specification	IEC 60068-2-27:2008-02
Pulse shape	Semi-sinusoidal
Acceleration	50g
Shock duration	11 ms
Test directions	X-, Y- and Z-axis (pos. and neg.)

Ambient conditions

Ambient temperature (storage/transport)	-40 °C ... 70 °C
Relative humidity (storage/transport)	30 % ... 70 %
Ambient temperature (assembly)	-5 °C ... 100 °C
Ambient temperature (operation)	-55 °C ... 125 °C

Ambient conditions

Ambient temperature (operation)	-55 °C ... 125 °C
---------------------------------	-------------------

FP 1,27/ 16-FWL-10/.../... - Preassembled IDC female connector



1010258

<https://www.phoenixcontact.com/us/products/1010258>

Ambient temperature (storage/transport)	-40 °C ... 70 °C
Relative humidity (storage/transport)	30 % ... 70 %
Ambient temperature (assembly)	-5 °C ... 100 °C

Connector

Connection 1

Insulating material	LCP
CTI according to IEC 60112	175

Cable/line

Cable length	Free input (0.05 ... 0.95 m)
--------------	------------------------------

Flat cable [PVC]

Note	Coded wire: red
UL AWM Style	2678
Shielded	no
Cable type	Flat cable [PVC]
Conductor structure	16 x 7 x 0.102 mm
Conductor structure signal line	7x 0.10 mm
AWG signal line	30
Conductor cross-section	0.06 mm ²
Wire diameter incl. insulation	0.66 mm
External sheath, color	gray
Conductor material	Tin-plated Cu litz wires
Material wire insulation	PVC
Pitch	0.635 mm
Max. conductor resistance	≤ 354 Ω/m
Insulation resistance	≥ 20 MΩ*km
Test voltage Core/Core	1500 V
Flame resistance	UL VW-1
Ambient temperature (mobile installation)	-10 °C ... 105 °C
Ambient temperature (installation)	-30 °C ... 105 °C

FP 1,27/ 16-FWL-10/.../... - Preassembled IDC female connector



1010258

<https://www.phoenixcontact.com/us/products/1010258>

Classifications

ECLASS

ECLASS-13.0	27460202
ECLASS-15.0	27460202

UNSPSC

UNSPSC 21.0	39121400
-------------	----------

FP 1,27/ 16-FWL-10/.../... - Preassembled IDC female connector



1010258

<https://www.phoenixcontact.com/us/products/1010258>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com