

NS 35/ 7,5 PERF 2000MM VPE 10 - DIN rail perforated



0843103

<https://www.phoenixcontact.com/us/products/0843103>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



DIN rail perforated, Pack of 10 (20 m), acc. to EN 60715, material: Steel, galvanized, passivated with a thick layer, Standard profile, color: silver

Commercial data

| | |
|--------------------------------------|---------------|
| Item number | 0843103 |
| Packing unit | 10 m |
| Minimum order quantity | 20 m |
| Sales key | BE72 |
| Product key | BE7244 |
| GTIN | 4046356949040 |
| Weight per piece (including packing) | 670 g |
| Weight per piece (excluding packing) | 670 g |
| Customs tariff number | 72166190 |
| Country of origin | DE |

NS 35/ 7,5 PERF 2000MM VPE 10 - DIN rail perforated

0843103

<https://www.phoenixcontact.com/us/products/0843103>

Technical data

Product properties

| | |
|--------------|----------|
| Product type | DIN rail |
|--------------|----------|

Dimensions

| | |
|---------------------|--|
| Dimensional drawing |  |
| Width | 35 mm |
| Hole width | 15 mm |
| Hole height | 6.2 mm |
| Depth | 7.5 mm |
| Length | 2000 mm |
| Drill hole spacing | 25 mm |

Material specifications

| | |
|----------|---|
| Color | silver-colored |
| Material | Steel |
| Coating | galvanized, passivated with a thick layer |

Standards and regulations

| | |
|----------------------------------|------------------|
| Connection in acc. with standard | IEC / EN |
| Tests | acc. to EN 60715 |

Electrical tests

Short-time withstand current


| | |
|----------------------------------|--------------------|
| Equivalent E-Cu cross-section | 16 mm ² |
| Short-time current resistance 1s | 1.92 kA |

NS 35/ 7,5 PERF 2000MM VPE 10 - DIN rail perforated

0843103

<https://www.phoenixcontact.com/us/products/0843103>

Drawings



NS 35/ 7,5 PERF 2000MM VPE 10 - DIN rail perforated



0843103

<https://www.phoenixcontact.com/us/products/0843103>

Classifications

ECLASS

| | |
|-------------|----------|
| ECLASS-13.0 | 27400602 |
| ECLASS-15.0 | 27400602 |

ETIM

| | |
|-----------|----------|
| ETIM 10.0 | EC001285 |
|-----------|----------|

UNSPSC

| | |
|-------------|----------|
| UNSPSC 21.0 | 39121700 |
|-------------|----------|

NS 35/ 7,5 PERF 2000MM VPE 10 - DIN rail perforated



0843103

<https://www.phoenixcontact.com/us/products/0843103>

Environmental product compliance

China RoHS

| | |
|--|--|
| Environment friendly use period (EFUP) | EFUP-E |
| | No hazardous substances above the limits |

EU REACH SVHC

| | |
|-------------------------------------|----------------------------|
| REACH candidate substance (CAS No.) | No substance above 0.1 wt% |
|-------------------------------------|----------------------------|

EF3.1 Climate Change

| | |
|---------|--------------|
| CO2e kg | 1.46 kg CO2e |
|---------|--------------|

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com