

NS 35/15 WH PERF(5,2X25)2000MM-VPE 10 - DIN rail perforated



0843114

<https://www.phoenixcontact.com/us/products/0843114>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



DIN rail perforated, Pack of 10 (20 m), similar to EN 60715, material: Steel, galvanized, white passivated, Standard profile, color: silver-colored

Commercial data

| | |
|--------------------------------------|---------------|
| Item number | 0843114 |
| Packing unit | 10 m |
| Minimum order quantity | 20 m |
| Sales key | BE72 |
| Product key | BE7238 |
| GTIN | 4046356949156 |
| Weight per piece (including packing) | 1,305 g |
| Weight per piece (excluding packing) | 1,305 g |
| Customs tariff number | 72166190 |
| Country of origin | DE |

NS 35/15 WH PERF(5,2X25)2000MM-VPE 10 - DIN rail perforated



0843114


<https://www.phoenixcontact.com/us/products/0843114>

Technical data

Product properties

| | |
|--------------|----------|
| Product type | DIN rail |
|--------------|----------|

Dimensions

| | |
|---------------------|---|
| Dimensional drawing |  |
| Width | 35 mm |
| Hole width | 25 mm |
| Hole height | 5.2 mm |
| Depth | 15 mm |
| Length | 2000 mm |
| Drill hole spacing | 36 mm |

Material specifications

| | |
|----------|------------------------------|
| Color | silver-colored |
| Material | Steel |
| Coating | galvanized, white passivated |

Standards and regulations

| | |
|----------------------------------|---------------------|
| Connection in acc. with standard | IEC / EN |
| Tests | similar to EN 60715 |

Electrical tests

Short-time withstand current

| | |
|----------------------------------|--------------------|
| Equivalent E-Cu cross-section | 25 mm ² |
| Short-time current resistance 1s | 3 kA |

NS 35/15 WH PERF(5,2X25)2000MM-VPE 10 - DIN
rail perforated





0843114

<https://www.phoenixcontact.com/us/products/0843114>

Drawings

Dimensional drawing



NS 35/15 WH PERF(5,2X25)2000MM-VPE 10 - DIN rail perforated



0843114

<https://www.phoenixcontact.com/us/products/0843114>

Classifications

ECLASS

| | |
|-------------|----------|
| ECLASS-15.0 | 27400602 |
| ECLASS-13.0 | 27400602 |

ETIM

| | |
|-----------|----------|
| ETIM 10.0 | EC001285 |
|-----------|----------|

UNSPSC

| | |
|-------------|----------|
| UNSPSC 21.0 | 39121700 |
|-------------|----------|

NS 35/15 WH PERF(5,2X25)2000MM-VPE 10 - DIN rail perforated



0843114

<https://www.phoenixcontact.com/us/products/0843114>

Environmental product compliance

EU RoHS

| | |
|---|--------------------|
| Fulfills EU RoHS substance requirements | Yes, No exemptions |
|---|--------------------|

China RoHS

| | |
|--|--|
| Environment friendly use period (EFUP) | EFUP-E |
| | No hazardous substances above the limits |

EU REACH SVHC

| | |
|-------------------------------------|----------------------------|
| REACH candidate substance (CAS No.) | No substance above 0.1 wt% |
|-------------------------------------|----------------------------|

EF3.1 Climate Change

| | |
|---------|---------------|
| CO2e kg | 2.718 kg CO2e |
|---------|---------------|

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com