

# TML (101X4,2)R P12 TR CUS - Marker strip



0852151

<https://www.phoenixcontact.com/us/products/0852151>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Marker strip, Roll, can be ordered: by line, labeled according to customer specifications, can be labeled with: THERMOMARK E.300 (D)/600 (D), THERMOMARK ROLL 2.0, THERMOMARK ROLL, THERMOMARK ROLL X1, THERMOMARK ROLLMASTER 300/600, THERMOMARK X1.2, mounting type: adhesive, for terminal block width: 12 mm, Number of individual labels: 1, text field height: 4.2 mm, text field width: 101 mm

## Your advantages

- The self-adhesive marker strips from the SK marking range mark products without a marker groove, ideal for marking COMBICON connectors
- The TML labeling range offers the option of subsequent labeling of zack marker strip and flat zack marker strip materials using a marking foil
- Labeling service: Phoenix Contact can custom-label all TML ... markers in accordance with your requirements

## Commercial data

|                                      |                                |
|--------------------------------------|--------------------------------|
| Item number                          | 0852151                        |
| Packing unit                         | 1 pc                           |
| Minimum order quantity               | 1 pc                           |
| Note                                 | Made to order (non-returnable) |
| Product key                          | BG8111                         |
| GTIN                                 | 4046356355254                  |
| Weight per piece (including packing) | 1.99 g                         |
| Weight per piece (excluding packing) | 1.99 g                         |
| Country of origin                    | PL                             |

# TML (101X4,2)R P12 TR CUS - Marker strip



0852151

<https://www.phoenixcontact.com/us/products/0852151>

## Technical data

### Product properties

|              |                 |
|--------------|-----------------|
| Product type | Terminal marker |
| Pitch        | 12 mm           |

### Marking

|                                     |                |
|-------------------------------------|----------------|
| Number of individual labels         | 1              |
| Number of individual labels per row | 1              |
| Slot type                           | flat           |
| Identification technology           | Thermotransfer |

### Dimensions

|        |           |
|--------|-----------|
| Width  | 101.00 mm |
| Height | 4.20 mm   |
| Depth  | 0.10 mm   |
| Pitch  | 12 mm     |
| Length | 101 mm    |

### Text field

|                   |        |
|-------------------|--------|
| Text field width  | 101 mm |
| Text field height | 4.2 mm |

### Material specifications

|                       |               |
|-----------------------|---------------|
| Color                 | transparent   |
| Material              | Polyester     |
| Base element material | Polyester     |
| Components            | Silicone-free |

### Environmental and real-life conditions

#### Ambient conditions

|   |   |
|---|---|
| Ambient temperature (operation)                     | -40 °C ... 150 °C   |
| Recommended ambient temperature (storage/transport) | 23 °C   |
| Recommended humidity (storage/transport)            | 50 % (Storage in a dry and dark place in the original packaging is recommended) |

#### UV resistance

|               |                                       |
|---------------|---------------------------------------|
| Specification | DIN EN ISO 4892-2:2021-11 (following) |
|---------------|---------------------------------------|

#### Wipe resistance of inscriptions

|               |  |
|---------------|--|
| Specification | DIN EN 61010-1 (VDE 0411-01):2020-03           |
|               | DIN EN 62208 (VDE 0660-511):2012-06 (in parts) |

### Standards and regulations

|                 |                             |
|-----------------|-----------------------------|
| Wipe resistance | DIN EN 61010-1 (VDE 0411-1) |
|-----------------|-----------------------------|

# TML (101X4,2)R P12 TR CUS - Marker strip



0852151

<https://www.phoenixcontact.com/us/products/0852151>

## Mounting

Mounting type

adhesive

# TML (101X4,2)R P12 TR CUS - Marker strip



0852151

<https://www.phoenixcontact.com/us/products/0852151>

## Drawings

Schematic diagram



- ① Horizontal
- ② Vertical

# TML (101X4,2)R P12 TR CUS - Marker strip



0852151

<https://www.phoenixcontact.com/us/products/0852151>

## Classifications

### ECLASS

|             |          |
|-------------|----------|
| ECLASS-13.0 | 27281101 |
| ECLASS-15.0 | 27281101 |

### ETIM

|           |          |
|-----------|----------|
| ETIM 10.0 | EC000761 |
|-----------|----------|

### UNSPSC

|             |          |
|-------------|----------|
| UNSPSC 21.0 | 39131500 |
|-------------|----------|

# TML (101X4,2)R P12 TR CUS - Marker strip



0852151

<https://www.phoenixcontact.com/us/products/0852151>

## Environmental product compliance

### EU RoHS

|   |                    |
|---|--------------------|
| Fulfills EU RoHS substance requirements | Yes, No exemptions |
|---|--------------------|

### EU REACH SVHC

|                                     |                            |
|-------------------------------------|----------------------------|
| REACH candidate substance (CAS No.) | No substance above 0.1 wt% |
|-------------------------------------|----------------------------|

Phoenix Contact 2026 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)