

SAC-2P-M8Y/2X 0,4-PVC/BI-1L180 - Sensor/actuator cable



1012546

<https://www.phoenixcontact.com/us/products/1012546>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Sensor/actuator cable, 3-position, PVC, black, Valve connector BI (11 mm), with 1 LED, on Valve connector BI (11 mm), with 1 LED and Valve connector BI (11 mm), with 1 LED, cable length: 0.4 m

Commercial data

Item number	1012546
Packing unit	1 pc
Minimum order quantity	100 pc
Product key	AF1BOA
GTIN	4055626491219
Weight per piece (including packing)	70.5 g
Weight per piece (excluding packing)	70.5 g
Country of origin	PL

SAC-2P-M8Y/2X 0,4-PVC/BI-1L180 - Sensor/actuator cable



1012546

<https://www.phoenixcontact.com/us/products/1012546>

Technical data

Product properties

Product type	Distributor with cable
Application	Standard
Number of positions	3
No. of cable outlets	2
Shielded	no
Coding	A

Insulation characteristics

Overvoltage category	III
Degree of pollution	3

Material specifications

Flammability rating according to UL 94	V0
Seal material	NBR
Material housing valve plug	TPU
Contact material	CuSn
Contact surface material	Ni/Au
Contact carrier material	TPU GF
Contact material	CuSn
Valve plug contact insert material	PA 6.6
Contact surface material	Sn
Material for screw connection	Zinc die-cast, nickel-plated

Electrical properties

Insulation resistance	$\geq 100 \text{ M}\Omega$
Nominal voltage U_N	48 V AC
	60 V DC
Nominal current I_N	4 A

Signaling

Status display	1 LED
Status display present	yes

Connector

Connection 1

Type	Valve connector BI (11 mm)
------	----------------------------

Connection 2

Type	Valve connector BI (11 mm)
Material	CuSn (Contact)
	Sn (Contact surface)

SAC-2P-M8Y/2X 0,4-PVC/BI-1L180 - Sensor/actuator cable



1012546


<https://www.phoenixcontact.com/us/products/1012546>

	PA 6.6 (Contact carrier)
	TPU (Housing)
Connection 3	
Type	Valve connector BI (11 mm)
Material	CuSn (Contact)
	Sn (Contact surface)
	PA 6.6 (Contact carrier)
	TPU (Housing)

Cable/line

Cable length	0.4 m
--------------	-------

PVC black [PVC]

Dimensional drawing	
Cable weight	34.9 kg/km
UL AWM Style	2464
Number of positions	2
Shielded	no
Cable type	PVC black [PVC]
Conductor structure signal line	16x 0.20 mm
AWG signal line	20
Conductor cross-section	2x 0.5 mm ²
Wire diameter incl. insulation	1.5 mm ±0.05 mm
External cable diameter	4.80 mm ±0.2 mm
Outer sheath, material	PVC
External sheath, color	black
Conductor material	Bare Cu litz wires
Material wire insulation	PVC
Single wire, color	brown, blue
Max. conductor resistance	39 Ω/km (at 20 °C)
Insulation resistance	≥ 20 MΩ*km
Nominal voltage, cable	300 V
Test voltage	1200 V
Minimum bending radius, fixed installation	5 x D
Smallest bending radius, fixed installation	24 mm
Flame resistance	according to DIN VDE 0482
	According to DIN EN 50265-2-1

SAC-2P-M8Y/2X 0,4-PVC/BI-1L180 - Sensor/actuator cable



1012546

<https://www.phoenixcontact.com/us/products/1012546>

Resistance to oil	largely oil-resistant
Ambient temperature (operation)	-40 °C ... 80 °C (cable, fixed installation)
	-5 °C ... 80 °C (Cable, flexible installation)

Environmental and real-life conditions

Ambient conditions

Degree of protection	IP65
	IP67
Ambient temperature (operation) (Valve connector)	-20 °C ... 85 °C (Valve connector)
Ambient temperature (operation) (Cable, fixed installation)	-40 °C ... 80 °C (cable, fixed installation)
Ambient temperature (operation) (flexible installation)	-15 °C ... 80 °C (Cable, flexible installation)

Standards and regulations

M8

Standard designation	M8 connector
Standards/specifications	IEC 61076-2-104

SAC-2P-M8Y/2X 0,4-PVC/BI-1L180 - Sensor/actuator cable

1012546

<https://www.phoenixcontact.com/us/products/1012546>


Drawings

Dimensional drawing



Plug M8 x 1, Y distributor

Dimensional drawing



Valve connector, type BI

SAC-2P-M8Y/2X 0,4-PVC/BI-1L180 - Sensor/actuator cable

1012546


<https://www.phoenixcontact.com/us/products/1012546>

Schematic diagram



Pin assignment M8 plug, 4-pos., view male side

Schematic diagram



Valve connector pin assignment, type BI

SAC-2P-M8Y/2X 0,4-PVC/BI-1L180 - Sensor/actuator cable



1012546

<https://www.phoenixcontact.com/us/products/1012546>

Classifications

ECLASS

ECLASS-13.0	27060313
ECLASS-15.0	27060313

UNSPSC

UNSPSC 21.0	26121600
-------------	----------

SAC-2P-M8Y/2X 0,4-PVC/BI-1L180 - Sensor/actuator cable



1012546

<https://www.phoenixcontact.com/us/products/1012546>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes
Exemption	6(c)

China RoHS

Environment friendly use period (EFUP)	EFUP-50
	An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.

EU REACH SVHC

REACH candidate substance (CAS No.)	Lead(CAS: 7439-92-1)
-------------------------------------	----------------------

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com