

S 10 A/380 V - Fuse insert

0913045

<https://www.phoenixcontact.com/us/products/0913045>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Fuse insert, nom. voltage: 400 V, nominal current: 10 A, diameter: 11 mm, color: red



Your advantages

- Colored indicating pins on the butt contact show the operating state
- Safe shutoff of impermissible overcurrents and short-circuit currents up to the nominal shutoff current
- Contains no lead, cadmium, chromium 6 (RoHS-compliant)
- NEOZED® fuse-links with gG characteristic for protecting lines and equipment

Commercial data

| | |
|--------------------------------------|---------------|
| Item number | 0913045 |
| Packing unit | 1 pc |
| Sales key | BE19 |
| Product key | BE1Z4X |
| GTIN | 4017918008147 |
| Weight per piece (including packing) | 6.86 g |
| Weight per piece (excluding packing) | 6.86 g |
| Customs tariff number | 85361010 |
| Country of origin | HU |

S 10 A/380 V - Fuse insert



0913045

<https://www.phoenixcontact.com/us/products/0913045>

Technical data

Product properties

| | |
|--------------|------|
| Product type | Fuse |
|--------------|------|

Electrical properties

| | |
|-----------------------|---|
| Nominal current I_N | 10 A |
| Fuse | 10 A gL/gK NEOZED (without fault display) |

Connection data

| | |
|-----------------|---------------------|
| Nominal current | 10 A |
| Nominal voltage | 400 V AC (250 V DC) |

Dimensions

| | |
|----------|-------|
| Diameter | 11 mm |
|----------|-------|

Material specifications

| | |
|-------|-----|
| Color | red |
|-------|-----|

Environmental and real-life conditions

Ambient conditions

| | |
|--|---|
| Ambient temperature (operation) | -60 °C ... 85 °C |
| Ambient temperature (storage/transport) | -25 °C ... 55 °C (for a short time, not exceeding 24 h, -60 °C to +70 °C) |
| Ambient temperature (assembly) | -5 °C ... 70 °C |
| Ambient temperature (actuation) | -5 °C ... 70 °C |
| Permissible humidity (storage/transport) | 30 % ... 70 % |

S 10 A/380 V - Fuse insert

0913045

<https://www.phoenixcontact.com/us/products/0913045>



Classifications

UNSPSC

| | |
|-------------|----------|
| UNSPSC 21.0 | 39121600 |
|-------------|----------|

S 10 A/380 V - Fuse insert



0913045

<https://www.phoenixcontact.com/us/products/0913045>

Environmental product compliance

EU RoHS

| | |
|---|--------------------|
| Fulfills EU RoHS substance requirements | Yes, No exemptions |
|---|--------------------|

China RoHS

| | |
|--|--|
| Environment friendly use period (EFUP) | EFUP-E |
| | No hazardous substances above the limits |

EU REACH SVHC

| | |
|-------------------------------------|----------------------------|
| REACH candidate substance (CAS No.) | No substance above 0.1 wt% |
|-------------------------------------|----------------------------|

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com