

# US-PML-P100 (D50) CUS - Prohibition sign



1014219

<https://www.phoenixcontact.com/us/products/1014219>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Prohibition sign, can be ordered: by card, Mixed color, labeled according to customer specifications: Diagonal bar, mounting type: adhesive, diameter: 50 mm, Number of individual labels: 4, text field height: 50 mm, text field width: 50 mm



## Your advantages

- UniSheet - stick-on prohibition signs, color preprinted without symbol

## Commercial data

Item number	1014219
Packing unit	1 pc
Minimum order quantity	1 pc
Note	Made to order (non-returnable)
Product key	BG8159
GTIN	4046356786768
Weight per piece (including packing)	5 g
Weight per piece (excluding packing)	5 g
Country of origin	PL

## Technical data

### Product properties

Product type	Plant marker
Area of application	Prohibition marking according to ISO 7010
Type	circular

### Marking

Number of individual labels	4
Number of individual labels per row	2
Printing	Diagonal bar
Identification technology	Thermal transfer

### Dimensions

Width	50.00 mm
Height	50.00 mm
Depth	0.08 mm

### Text field

Text field width	50 mm
Text field height	50 mm

### Material specifications

Foil strength	60 µm
Adhesive strength	25 µm
Adhesive	Acrylic
Color	multicolored (RAL -)
	red (RAL 3001)
	white (RAL 9010)
Material	PVC
Base element material	PVC
Components	Silicone-free

### Environmental and real-life conditions

#### Ambient conditions

Ambient temperature (operation)	-40 °C ... 90 °C
Recommended ambient temperature (storage/transport)	22 °C
Recommended humidity (storage/transport)	50 % ... 55 % (Storage in a dry and dark place in the original packaging is recommended)

#### Scratch resistance

Specification	EN ISO 1518-1:2023 (following)
Requirements	≥ 5 N
Result	Test passed

# US-PML-P100 (D50) CUS - Prohibition sign



1014219

<https://www.phoenixcontact.com/us/products/1014219>

## Tesafilm test

Specification	DIN EN ISO 2409:2020-12 (following)
Result	Test passed

## UV resistance

Specification	DIN EN ISO 4892-2:2021-11 (following)
Result	Test passed
Test duration	96 h
Procedure	Artificial irradiation.

## Temperature resistance

Specification	ANSI/UL 969-2018:03 (following)
Test duration	240 h
Rating 125 °C (150 °C)	Test passed

## Wipe resistance of inscriptions

Specification	DIN EN 61010-1 (VDE 0411-01):2020-03 DIN EN 62208 (VDE 0660-511):2012-06 (in parts)
Isopropanol (99%) [67-63-0]	Test passed
n-Hexane [CAS No. 110-54-3]	Test passed
Water + Petroleum ether [CAS No. 64742-82-1]	Test passed
Sodium hydroxide 0.1 mol/l [CAS No. 1310-73-2]	Test passed
Ethanol (99 %) [CAS No. 64-17-5]	Test passed

## Immersion in chemicals, oil & fuel

Specification	ISO 175:2010 (following)
Test duration	168 h
Saltwater (saturated 350 g/l) [CAS No. - ]	Test passed
Diesel [CAS No. 68476-34-6]	Test passed
IRM 901	Test passed
IRM 902	Test passed
IRM 903	Test passed

## Testing in a condensation changing climate in the presence of sulfur dioxide

Specification	EN ISO 22479:2022-06
Result	Test passed
Procedure	Method B
Cycles	2

## Standards and regulations

Wipe resistance	DIN EN 61010-1 (VDE 0411-1)
-----------------	-----------------------------

# US-PML-P100 (D50) CUS - Prohibition sign



1014219

<https://www.phoenixcontact.com/us/products/1014219>

## Mounting

Mounting type	adhesive
---------------	----------

# US-PML-P100 (D50) CUS - Prohibition sign



1014219

<https://www.phoenixcontact.com/us/products/1014219>

## Classifications

### ECLASS

ECLASS-15.0	40200202
ECLASS-13.0	40200202

### ETIM

ETIM 10.0	EC001777
-----------	----------

### UNSPSC

UNSPSC 21.0	55121700
-------------	----------

# US-PML-P100 (D50) CUS - Prohibition sign



1014219

<https://www.phoenixcontact.com/us/products/1014219>

## Environmental product compliance

### EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

### EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)